



ZVN4424G

SOT223 N-CHANNEL ENHANCEMENT MODE VERTICAL DMOSFET

Product Summary

BV _{DSS}	Max R _{DS(ON)}	Max I _D T _A = +25°C
240V	5.5Ω @ V _{GS} = 10V	500mA

Description and Applications

This MOSFET is designed to minimize the on-state resistance (RDS(ON)) and yet maintain superior switching performance, making it ideal for high efficiency power management applications.

- · Earth Recall and Dialing Switches
- Electronic Hook Switches
- Battery Powered Equipment
- Telecoms and High Voltage DC-DC Convertors

Features and Benefits

- 240 Volt BVDS
- Extremely Low R_{DS(ON)}=4.3Ω
- Low Threshold and Fast Switching
- Lead-Free Finish; RoHS Compliant (Notes 1& 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)


Mechanical Data

- Case: SOT223
- Case Material: Molded Plastic, "Green" Molding Compound;
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals Connections: See Diagram Below
- Terminals: Finish Matte Tin Annealed over Copper Leadframe;
 Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.112 grams (Approximate)


SOT223 (Type DN)







Pin Out Top-View



Equivalent Circuit


Ordering Information (Note 5)

Part Number	Compliance	Case	Packaging
ZVN4424GTA	Standard	SOT223 (Type DN)	1,000
ZVN4424GQTA	Automotive	SOT223 (Type DN)	1,000

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. Automotive products are AEC-Q101 qualified and are PPAP capable. Automotive, AEC-Q101 and standard products are electrically and thermally the same, except where specified. For more information, please refer to https://www.diodes.com/quality/.
- 5. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



ZVN 4424 = Product Type Marking Code YWW = Date Code Marking Y or \overline{Y} = Last Digit of Year (ex: 8 = 2018) WW or $\overline{W}W$ = Week Code (01 to 53)



Maximum Ratings (@ $T_A = +25$ °C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Drain-Source Voltage	V_{DSS}	240	V
Gate-Source Voltage	V_{GS}	±40	V
Continuous Drain Current	Ι _D	500	mA
Pulsed Drain Current	I _{DM}	1.5	A

Thermal Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Power Dissipation at T _A = +25°C	P _{TOT}	2.5	W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Cumbal	Min	T. m	Max	I Imit	Toot Condition	
Symbol	WIIN	тур	wax	Unit	Test Condition	
OFF CHARACTERISTICS						
BV _{DSS}	240	_	_	V	$I_D = 1mA$, $V_{GS} = 0V$	
lann	_	_	10	μA	V _{DS} = 240V, V _{GS} = 0V	
DSS			100		$V_{DS} = 190V, V_{GS} = 0V, T_A = +125^{\circ}C$	
IGSS	_	_	100	nA	$V_{GS} = \pm 40V$, $V_{DS} = 0V$	
V _{GS(TH)}	0.8	1.3	1.8	V	$I_D = 1mA$, $V_{DS} = V_{GS}$	
ON CHARACTERISTICS						
I _{D(ON)}	0.8	1.4	_	Α	$V_{DS} = 10V, V_{GS} = 10V$	
R _{DS(ON)}	_	4	5.5	Ω	$V_{GS} = 10V, I_D = 500mA$	
	_	4.3	6		$V_{GS} = 2.5V, I_D = 500mA$	
g fs	0.4	0.75	_	S	$V_{DS} = 10V, I_D = 0.5A$	
C _{iss}	_	110	200	pF	V _{DS} = 25V, V _{GS} = 0V -f = 1MHz	
Coss	_	15	25	pF		
Crss	_	3.5	15	pF		
t _{D(ON)}	_	2.5	5	ns		
t _R	_	5	8	ns	$V_{DD} = 50V, V_{GEN} = 10V$ $I_{D} = 0.25A$	
t _{D(OFF)}	_	40	60	ns		
t _F	_	16	25	ns		
	IDSS IGSS VGS(TH) ID(ON) RDS(ON) Gfs Ciss Coss Crss tD(ON) tR tD(OFF)	BVDSS 240 IDSS	BVDSS 240 —	BVDSS 240 IDSS 100 IGSS 100 VGS(TH) 0.8 1.3 1.8 ID(ON) 0.8 1.4 RDS(ON) 4.3 6 Gfs 0.4 0.75 Ciss 110 200 Coss 15 25 Crss 3.5 15 tD(ON) 2.5 5 tR 5 8 tD(OFF) 40 60	BVDSS 240	

Notes:


^{6.} Measured under pulsed conditions. Width=300µs. Duty cycle ≤ 2%.

^{7.} Sample test.

^{8.} Switching times measured with 50Ω source impedance and <5ns rise time on a pulse generator.




Typical Characteristics





Typical Characteristics (Cont.)






Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT223 (Type DN)




SOT223 (Type DN)					
Dim	Min	Max	Тур		
Α		1.70			
A1	0.01	0.15			
A2	1.50	1.68	1.60		
b	0.60	0.80	0.70		
b2	2.90	3.10			
С	0.20	0.32			
D	6.30	6.70			
Е	6.70	7.30			
E1	3.30	3.70			
е			2.30		
e1			4.60		
Ĺ	0.85				
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT223 (Type DN)



Dimensions	Value (in mm)
С	2.30
C1	6.40
Х	1.20
X1	3.30
Υ	1.60
Y1	1.60
C2	8 00

October 2018



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com