

NOT RECOMMENDED FOR NEW DESIGN USE AH3323

AH3373



HIGH VOLTAGE HIGH SENSITIVITY HALL EFFECT UNIPOLAR SWITCH

Description

The AH3373 is a high voltage high sensitivity Hall Effect Unipolar switch IC designed for proximity, position and level sensing in industrial and consumer home appliances and personal care applications. To support wide range of demanding applications, the design has been optimized to operate over the supply range of 3.0V to 28V. With chopper stabilized architecture and an internal bandgap regulator to provide temperature compensated supply for internal circuits, the AH3372 provides a reliable solution over the whole operating range. For robustness and protection, the device has a reverse blocking diode with a Zener clamp on the supply. The output has an over current limit and a Zener clamp.


The single open drain output can be switched on with South pole of sufficient strength. When the magnetic flux density (**B**) perpendicular to the package is larger than the operate point (**Bop**) the output is switched on (pulled low) and is held on until magnetic flux density B is lower than the release point (**Brp**). The output remains switched off for North pole fields to or no magnetic fields.

The magnetic operating and release polarity is opposite for SOT23 and SC59 packages. SOT23 and SIP-3 (Ammo Pack), SIP-3 (Bulk Pack) packages require south pole to the part marking side to operate while SC59 requires south pole to the non-part marking side.

Features

- · Unipolar Operation
- High Sensitivity: BOP and BRP of +55G and +35G Typical
- · Single Open Drain Output with Over Current Limit
- 3.0V to 28V Operating Voltage Range
- Chopper Stabilized Design Provides
 - Superior Temperature Stability
 - o Minimal Switch Point Drift
 - Enhanced Immunity to Stress
- Good RF Noise Immunity
- Reverse Blocking Diode
- Zener Clamp on Supply and Output Pins
- -40°C to +125°C Operating Temperature
- ESD: HBM > 6kV
- Industry Standard SC59, SOT23 and SIP-3 (Ammo Pack), SIP-3 (Bulk Pack) Packages
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)

Pin Assignments





Applications


- Position and Proximity Sensing in Consumer Home Appliances, Building Automation, Office Equipments and Industrial Applications
- · Open and Close Detect
- Position Detect
- · Level Detect
- · Flow Meters
- Contact-less switches

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



Typical Applications Circuit



Note:


4. C_{IN} is for power stabilization and to strengthen the noise immunity, the recommended capacitance is 10nF \sim 100nF R_L is the pull-up resistor.

Pin Descriptions

Package: SC59, SOT23 and SIP-3 (Ammo Pack), SIP-3 (Bulk Pack)

Pin Number	Pin Name	Function
1	V _{DD}	Power Supply Input
2	GND	Ground
3	OUTPUT	Output Pin

Functional Block Diagram





Absolute Maximum Ratings (Note 5 & 6) (@TA = +25°C, unless otherwise specified.)

Symbol	Characteristic		Value	Unit
V_{DD}	Supply Voltage (Note 6)		32	V
V_{DDR}	Reverse Supply Voltage (Note 6)		-32	V
Vout_max	Output Off Voltage (Note 6)		32	V
Іоит	Continuous Output Current		60	mA
lout_r	Reverse Output Current	-50	mA	
В	Magnetic Flux Density		Unlimited	
PD	Package Power Dissipation	SIP-3(Ammo Pack), SIP-3(Bulk Pack)	550	mW
		SC59 and SOT23	230	
Ts	Storage Temperature Range	-65 to +165	ç	
TJ	Maximum Junction Temperature	+150	°C	
ESD HBM	Electros Static Discharge Withstand - Human Body Model (HMB)		6	kV

Notes:

- 5. Stresses greater than the 'Absolute Maximum Ratings' specified above may cause permanent damage to the device. These are stress ratings only; functional operation of the device at these or any other conditions exceeding those indicated in this specification is not implied. Device reliability may be affected by exposure to absolute maximum rating conditions for extended periods of time.
- 6. The absolute maximum VDD of 32V is a transient stress rating and is not meant as a functional operating condition. It is not recommended to operate the device at the absolute maximum rated conditions for any period of time.

Recommended Operating Conditions (@TA = -40°C to +125°C, unless otherwise specified.)

Symbol	Parameter		Condition	1	Rating	Unit
VDD	Supply Voltage	Operating			3.0 to 28	V
TA	Operating Temperature Range	Operating			-40 to +125	°C

Electrical Characteristics (Note 7 & 8) (@TA = -40°C to +125°C, VDD = 3V to 28V, unless otherwise specified.)

Symbol	Parameter	Condition	Min	Тур	Max	Unit
Vout_on	Output ON Voltage	IOUT = 20mA, B > Bop	-	0.2	0.4	V
ILKG	Output Leakage Current (When output is off)	Vout = 28V, B < B _{RP} , Output off	ı	<0.1	10	μΑ
loo	Supply Current	Output open, T _A = +25°C	-	3	3.5	mA
I _{DD}	Supply Current	Iout = 20mA, B > Bop Vout = 28V, B < BRP, Output off Output open, TA = +25°C Output open, TA = -40 to +125°C VDD = -18V, TA = -40 to +125°C VDD = -28V, TA = -40 to +125°C	ı	-	4	mA
I _{DD R}	Reverse Supply Current	$V_{DD} = -18V$, $T_A = -40$ to $+125$ °C	1	-0.01	1	mA
א_טטי_ג	Reverse Supply Current	V _{DD} = -28V, T _A = -40 to +125°C	-	-0.01	1.5	mA
t _{P_ON}	Device Power-On Time (Start-up time)	V _{DD} >= 3V, B > B _{OP} (Note 7)	-	10	-	μs
fc	Chopping Frequency		-	800	-	kHz
to	Response Time Delay (Time from magnetic threshold reached to the start of the output rise or fall)	(Note 9)	-	3.75	-	μs
tR	Output Rising Time (External pull-up resistor R∟and load capacitance dependent)	$R_L = 1k\Omega$, $C_L = 20pF$	-	0.2	1	μs
tF	Output Falling Time (Internal switch resistance and load capacitance dependent)	$R_L = 1k\Omega$, $C_L = 20pF$	-	0.1	1	μs
locL	Output Current Limit	B > Bop, (Note 10)	30	-	55	mA
Vz	Zener Clamp Voltage	$I_{DD} = 5mA$	28	-	-	V

Notes:

- 7. When power is initially turned on, Vob must be within its correct operating range (3.0V to 28V) to guarantee the output sampling. The output state is valid after the start-up time of 10µs typical from the operating voltage reaching 3V.
- 8. Typical values are defined at T_A = +25°C, V_{DD} = 12V. Maximum and minimum values over the operating temperature range is not tested in production but guaranteed by design, process control and characterization.

 9. Guaranteed by design, process control and characterization, Not tested in production.
- 10. The device will limit the output current I_{OUT} to current limit of I_{OCL}



Symbol

side for SOT23 and SIP-3 (Ammo Pack),

South pole to the non-part marking side

for SC59 package. See diagram below) BRPS (South pole to the part marking

side for SOT23 and SIP-3 (Ammo Pack),

South pole to the non-part marking side

for SC59 package. See diagram below)

BOPS (South pole to the part marking

SIP-3 (Bulk Pack) packages;

SIP-3 (Bulk Pack) packages;

B_{HY} (|B_{OPX}|-|B_{RPX}|)

Magnetic Characteristics (Note 11 &12) (T_A = -40°C to +125°C, V_{DD} = 3.0V to 28V, unless otherwise specified)

Parameter

Operation Point

Release Point

Hysteresis (Note 13)

	(1mT=10 Gauss)								
Min	Тур	Max	Unit						
-	55	-							
38	55	72							
-	35	-	Gauss						

50

26

20

11. When power is initially turned on, VDD must be within its correct operating range (3.0V to 28V) to guarantee the output sampling. The output state is valid after the start-up time of 10us typical from the operating voltage reaching 3V.

Condition

 $V_{DD} = 12V, T_A = +25^{\circ}C$

 $T_A = -40$ °C to +125°C

 $V_{DD} = 12V, T_A = +25^{\circ}C$


 $T_A = -40^{\circ}C$ to $+125^{\circ}C$

 $V_{DD} = 12V, T_A = +25^{\circ}C$

 $T_A = -40$ °C to +125°C

- 12. Typical values are defined at T_A = +25°C, V_{DD} = 12V. Maximum and minimum values over the operating temperature range is not tested in production but guaranteed by design, process control and characterization


 13. Maximum and minimum hysteresis is guaranteed by design, process control and characterization.






Typical Operating Characteristics


Output Switch Operate and Release Points (Magnetic Thresholds) - Bops and Brps








Switch Points \mathbf{B}_{OPS} and \mathbf{B}_{RPS} vs Temperature




Switch Points \mathbf{B}_{OPS} and \mathbf{B}_{RPS} vs Temperature




Switch Points \mathbf{B}_{OPS} and \mathbf{B}_{RPS} vs Temperature

Supply Current



Supply Current vs Supply Voltage




Supply Current vs Supply Voltage




Typical Operating Characteristics (Cont.)

Supply Reverse Current




Reverse Supply Current vs Supply Voltage




Reverse Supply Current vs Temperature

Output Switch On Voltage




Output ON Voltage vs Supply Voltage




Output ON Voltage vs Temperature

Output Switch Leakage Current



Output Leakage Current vs Supply Voltage





Output Leakage Current vs Temperature




Typical Operating Characteristics (Cont.)

Output Current Limit








Output CurrentLimit vs Temperature



Thermal Performance Characteristics

(1) Package type: SC59 and SOT23

T _A (°C)	25	50	60	70	80	85	90	100	105	110	120	125	130	140	150
P _D (mW)	230	184	166	147	129	120	110	92	83	74	55	46	37	18	0




(2) Package type: SIP-3 (Ammo Pack), SIP-3 (Bulk Pack)

T _A (°C)	25	50	60	70	80	85	90	100	105	110	120	125	130	140	150
P _D (mW)	550	440	396	362	308	286	264	220	198	176	132	110	88	44	0




Power Dissipation Curve





Ordering Information




Paakaga			Bulk		7" Tape an	d Reel	Ammo Box	
Part Number	Package Code	Packaging	Quantity	Part Number Suffix	Quantity	Part Number Suffix	Quantity	Part Number Suffix
AH3373-P-A	Р	SIP-3(Ammo Pack)	NA	NA	NA	NA	4000/Box	-A
AH3373-P-B	Р	SIP-3(Bulk Pack)	1000	-B	NA	NA	NA	NA
AH3373-SA-7	SA	SOT23	NA	NA .	3000/Tape & Reel	-7	NA	NA
AH3373-W-7	W	SC59	NA	NA 🗼	3000/Tape & Reel	-7	NA	NA

 Ammo Box is for SIP-3 (Ammo Pack) Spread Lead.
 Bulk is for SIP-3 (Bulk Pack) Straight Lead. Notes:


Marking Information

(1) Package Type: SC59 and SOT23



Part Number	Package	Identification Code
AH3373	SC59	DT
AH3373	SOT23	MT

(2) Package Type: SIP-3 (Ammo Pack), SIP-3 (Bulk Pack)




Part Number	Package	Identification Code		
AH3373	SIP-3 (Ammo Pack)	3373		
AH3373	SIP-3 (Bulk Pack)	3373		




Package Outline Dimensions (All dimensions in mm.)

Please see http://www.diodes.com/package-outlines.html for the latest version.

(1) Package Type: SC59



	SC	59	
Dim	Min	Max	Тур
Α	0.35	0.50	0.38
В	1.50	1.70	1.60
С	2.70	3.00	2.80
D	-	-	0.95
G	-	-	1.90
Н	2.90	3.10	3.00
J	0.013	0.10	0.05
K	1.00	1.30	1.10
L	0.35	0.55	0.40
М	0.10	0.20	0.15
N	0.70	0.80	0.75
α	0°	8°	-
ΔII	Dimens	ions in	mm







Package Outline Dimensions (Cont.) (All dimensions in mm.)

Please see http://www.diodes.com/package-outlines.html for the latest version.

(2) Package Type: SOT23



SOT23									
Dim	Min	Max	Тур						
Α	0.37	0.51	0.40						
В	1.20	1.40	1.30						
С	2.30	2.50	2.40						
D	0.89	1.03	0.915						
F	0.45	0.60	0.535						
G	1.78	2.05	1.83						
Н	2.80	3.00	2.90						
7	0.013	0.10	0.05						
K	0.890	1.00	0.975						
K1	0.903	1.10	1.025						
L	0.45	0.61	0.55						
1	0.25	0.55	0.40						
M	0.085	0.150	0.110						
а	0°	8°							
All [Dimensi	ons in i	mm						






Package Outline Dimensions (Cont.) (All dimensions in mm.)

Please see http://www.diodes.com/package-outlines.html for the latest version.

(3) Package Type: SIP-3 (Bulk Pack)



SIP-3

Max

1.60

0.43

0.52

0.41

4.30

3.20

1.30

2.90

0.20

1.75

3.00

0.84

2.62 REF

Тур

1.50

0.38

0.46

0.38

4.10

3.00

1.27

2.65

13.90

1.65

2.50

0.74

5°

5°

45°


3°



Package Outline Dimensions (cont.) (All dimensions in mm.)

Please see http://www.diodes.com/package-outlines.html for the latest version.

(4) Package Type: SIP-3 (Ammo Pack)




Sensor Location



Suggested Pad Layout


Please see http://www.diodes.com/package-outlines.html for the latest version.

(1) Package Type: SC59



Dimensions	Value (in mm)
Z	3.4
Х	0.8
Y	1.0
С	2.4
Е	1.35

(2) Package Type: SOT23



Dimensions	Value (in mm)
С	2.0
Х	0.8
X1	1.35
Υ	0.9
V4	2.0



IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners.

© 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com

AH3373 15 of 15
Document number: DS38918 Rev. 3 - 3 www.diodes.com