

ZXMS6008FF

60V N-CHANNEL SELF PROTECTED ENHANCEMENT MODE INTELLIFET MOSFET

Product Summary

- Continuous Drain Source Voltage: VDS = 60V
- On-State Resistance: 700mΩ
- Nominal Load Current (VIN = 5V): 1.1A
- Clamping Energy: 90mJ

Description

The DIODES™ ZXMS6008FF is a self-protected low-side IntelliFET® MOSFET with logic level input. It integrates overtemperature, overcurrent, overvoltage (active clamp), and ESD-protected logic level functionality. The ZXMS6008FF is ideal as a general purpose switch driven from 3.3V or 5V microcontrollers in harsh environments where standard MOSFETs are not rugged enough.

Applications

- Especially suited for loads with a high inrush current, such as lamps and motors
- All types of resistive, inductive and capacitive loads in switching applications
- µC compatible power switch for 12V and 24V DC applications
- Replaces electromechanical relays and discrete circuits
- Linear mode capability: the current-limiting protection circuitry is designed to deactivate at low VDS to minimize on-state power dissipation. The maximum DC operating current is therefore determined by the thermal capability of the package/board combination, rather than by the protection circuitry. This does not compromise the product's ability to self-protect at low VDS.

Features and Benefits

- **Compact High Power Dissipation Package**
- Low Input Current
- Logic Level Input (3.3V and 5V)
- Short Circuit Protection with Auto Restart
- Overvoltage Protection (Active Clamp)
- Thermal Shutdown with Auto Restart
- **Overcurrent Protection**
- Input Protection (ESD)
- High Continuous Current Rating
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e.: parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please refer to the related automotive grade (Q-suffix) part. A listing can be found at

https://www.diodes.com/products/automotive/automotiveproducts/.

This part is gualified to JEDEC standards (as references in AEC-Q) for High Reliability.


https://www.diodes.com/quality/product-definitions/

Mechanical Data

- Package: SOT23F
- Package Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020

S

- Terminals: Matte Tin Finish (3)
- Weight: 0.012 grams (Approximate)



Ordering Information (Note 4)

Part Number	Package Marking Reel Size (inches) Tape Width (mm)				Packing		
Part Number	Part Number Package	Marking	Reel Size (inches)	Tape width (mm)	Qty.	Carrier	
ZXMS6008FF-7	SOT23F	1K8	7	8	3,000	Reel	

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.


4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

IntelliFET® is a registered trademark of Diodes Incorporated.

Notes:




Marking Information



1K8 <u>=</u> Product Type Marking Code Y or Y : Year: 0~9 W or W: Week: A-Z: 1~26 a-z: 27~52 z: Represents 52 & 53 Week

Functional Block Diagram





Absolute Maximum Ratings (@ T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Continuous Drain-Source Voltage	V _{DS}	60	V
Drain-Source Voltage for Short Circuit Protection	V _{DS(SC)}	36	V
Continuous Input Voltage	V _{IN}	-0.5 to +6	V
Continuous Input Current @ $-0.2V \le V_{IN} \le 6V$ Continuous Input Current @ $V_{IN} < -0.2V$ or $V_{IN} > 6V$	lin	No Limit I _{IN} ≤2	mA
Pulsed Drain Current @VIN = 3.3V	I _{DM}	1.4	A
Pulsed Drain Current @V _{IN} = 5V	I _{DM}	1.8	A
Continuous Source Current (Body Diode) (Note 5)	ls	0.7	A
Pulsed Source Current (Body Diode)	lsм	4	А
Unclamped Single Pulse Inductive Energy, $T_J = +25^{\circ}C$, $I_D = 0.5A$, $V_{DD} = 24V$	Eas	90	mJ
Electrostatic Discharge (Human Body Model)	V _{ESD}	4000	V
Charged Device Model	V _{CDM}	1000	V

Thermal Resistance

Characteristic	Symbol	Value	Unit
Power Dissipation at $T_A = +25^{\circ}C$ (Note 5) Linear Derating Factor	PD	0.81 6.54	W mW/°C
Power Dissipation at $T_A = +25^{\circ}C$ (Note 6) Linear Derating Factor	PD	1.5 12	W mW/°C
Thermal Resistance, Junction to Ambient (Note 5)	Reja	153	°C/W
Thermal Resistance, Junction to Ambient (Note 6)	R _{0JA}	83	°C/W
Thermal Resistance, Junction to Lead (Note 7)	Rejc	65	°C/W
Operating Temperature Range	TJ	-40 to +150	°C
Storage Temperature Range	Tstg	-55 to +150	°C

Notes: 5. For a device surface mounted on 15mm x 15mm single sided 1oz weight copper on 1.6mm FR-4 board, in still air conditions.

6. For a device surface mounted on 50mm x 50mm single sided 2oz weight copper on 1.6mm FR-4 board, in still air conditions.

7. Thermal resistance between junction and the mounting surfaces of drain and source pins.


Recommended Operating Conditions

The ZXMS6008FF is optimized for use with μC operating from 3.3V and 5V supplies.

Characteristic	Symbol	Min	Max	Unit
Input Voltage Range	VIN	0	5.5	V
Ambient Temperature Range	TA	-40	+125	°C
High Level Input Voltage for MOSFET to be on	VIH	3	5.5	V
Low Level Input Voltage for MOSFET to be off	VIL	0	0.7	V
Peripheral Supply Voltage (Voltage to Which Load is Referred)	VP	0	36	V



Thermal Characteristics



Notes: 5. For a device surface mounted on 15mm x 15mm single sided 1oz weight copper on 1.6mm FR-4 board, in still air conditions. 6. For a device surface mounted on 50mm x 50mm single sided 2oz weight copper on 1.6mm FR-4 board, in still air conditions.



Notes:

Electrical Characteristics (@ TA = +25°C, unless otherwise stated.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Static Characteristics						
Drain-Source Clamp Voltage	VDS(AZ)	60	65	70	V	I _D = 10mA
Off Olists Daris Original		_	_	0.5	μA	$V_{DS} = 12V, V_{IN} = 0V$
Off State Drain Current	IDSS		_	1		$V_{DS} = 36V, V_{IN} = 0V$
Input Threshold Voltage	VIN(TH)	0.7	1.2	1.5	V	V _{DS} = V _{GS} , I _D = 1mA
lanut Ourrent		_	60	100	μA	V _{IN} = 3V
Input Current	lin	_	120	200		$V_{IN} = 5V$
Input Current While Over Temperature Active	_		—	350	μA	V _{IN} = 5V
Statia Drain Course On State Desistance		_	550	800	mΩ	V _{IN} = 3V, I _D = 0.5A
Static Drain-Source On-State Resistance	R _{DS(ON)}		500	700		$V_{IN} = 5V, I_D = 0.5A$
Continuous Drain Quarant (Note 5)	– I _D	0.6	_		A	V _{IN} = 3V, T _A = +25°C
Continuous Drain Current (Note 5)		0.7	_			V _{IN} = 5V, T _A = +25°C
Continuous Drain Current (Note C)		0.8	_			$V_{IN} = 3V, T_A = +25^{\circ}C$
Continuous Drain Current (Note 6)		0.9	_			$V_{IN} = 5V, T_A = +25^{\circ}C$
Current Limit (Note 9)	ID(LIM)	0.5	1.2		A	$V_{IN} = 3V$
Current Limit (Note 8)		0.7	1.6	_		$V_{IN} = 5V$
Dynamic Characteristics				•		
Turn On Delay Time	tD(ON)	_	5		- µs	V _{DD} = 12V, I _D = 0.5A,
Rise Time	tR	_	10			
Turn Off Delay Time	tD(OFF)	_	45			VGS = 5V
Fall Time	tF	_	15			
Overtemperature Protection	•		•			
Thermal Overload Trip Temperature (Note 9)	TJT	+150	+175		°C	—
Thermal Hysteresis (Note 9)	_	_	+10	—	°C	_


5. For a device surface mounted on 15mm x 15mm single sided 1oz weight copper on 1.6mm FR-4 board, in still air conditions.

 For a device surface mounted on 50mm x50mm single sided 2oz weight copper on 1.6mm FR-4 board, in still air conditions.
The drain current is restricted only when the device is in saturation (see graph 'typical output characteristic'). This allows the device to be used in the fully on state without interference from the current limit. The device is fully protected at all drain currents, as the low power dissipation generated outside saturation makes current limit unnecessary.

9. Overtemperature protection is designed to prevent device destruction under fault conditions. Fault conditions are considered as "outside" normal operating range, so this part is not designed to withstand overtemperature for extended periods.





Typical Characteristics





Typical Characteristics (continued)








Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.




	SOT23F					
Dim	Min	Max	Тур			
Α	0.80	1.00	0.90			
A1	0.00	0.10	0.01			
b	0.35	0.50	0.44			
С	0.10	0.20	0.16			
D	2.80	3.00	2.90			
е	0.95 REF					
e1	1.90 REF					
Е	2.30	2.50	2.40			
E1	1.50	1.70	1.65			
k	1.20	-	-			
L	0.30	0.65	0.50			
L1	0.30	0.50	0.40			
R	0.05	0.15	-			
A	All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23F



Dimensions	Value		
Dimensions	(in mm)		
С	0.95		
Х	0.80		
Y	1.110		
Y1	3.000		

SOT23F



IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5 Diodes' provided to Diodes' Standard Terms and Conditions of Sale products are subject (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

DIODES is a trademark of Diodes Incorporated in the United States and other countries. The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. © 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com