



150V PNP HIGH VOLTAGE TRANSISTOR IN SOT23

Description

This Bipolar Junction Transistor (BJT) is designed to meet the stringent requirements of automotive applications.

Features and Benefits

- $BV_{CEO} > -150V$
- Maximum Continuous Collector Current I_C = -600mA
- Excellent hFE Characteristics up to I_C = -50mA
- Low Saturation Voltages
- Complementary part number: ZXTN5551FLQ
- Totally Lead-Free & Fully RoHS compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The ZXTP5401FLQ is suitable for automotive applications requiring specific change control; this part is AEC-Q101 qualified, PPAP capable, and manufactured in IATF16949 certified facilities.

https://www.diodes.com/quality/product-definitions/


Mechanical Data

- Package: SOT23
- UL Flammability Rating 94V-0
- Case material: molded Plastic.
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Matte Tin Finish; Solderable per MIL-STD-202, Method 208 @3
- Weight: 0.008 grams (Approximate)


SOT23



Top View



Device Symbol



Top View Pin-Out

Ordering Information (Note 4)

Ī	Product	Compliance	Marking	Reel size (inches)	Tape width (mm)	Quantity per reel
	ZXTP5401FLQTA	Automotive	P01	7	8	3,000

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + CI) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information

SOT23

P01 = Product Type Marking Code

YM = Date Code Marking Y or \overline{Y} = Year (ex: I = 2021)

M = Month (ex: 9 = September)

Date Code Key

Date Code Key												
Year	2021	2022	2023	2024	2025	2026	2027	2028	2029	2030	2031	2032
Code	ı	J	K	L	М	N	0	Р	R	S	T	J
		1	ı			1			_	_		
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
	• • • • • • • • • • • • • • • • • • • •			, .p.	ay	o a	3	,				



Absolute Maximum Ratings @TA = 25°C unless otherwise specified


Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V_{CBO}	-160	V
Collector-Emitter Voltage	$V_{\sf CEO}$	-150	V
Emitter-Base Voltage	V_{EBO}	-5	V
Continuous Collector Current	Ic	-600	mA
Peak Pulse Current	I _{CM}	-1	А


Thermal Characteristics @ T_A = 25°C unless otherwise specified

Characteristic		Symbol	Value	Unit	
Collector Power Dissipation	(Note 5)	6	310		
Collector Power Dissipation	(Note 6)	P _D	350	mW	
Thermal Desigtance, Junction to Ambient	(Note 5)	0	403	°C/W	
Thermal Resistance, Junction to Ambient	(Note 6)	$R_{\theta JA}$	357	-C/VV	
Thermal Resistance, Junction to Leads	$R_{ heta JL}$	350	°C/W		
Operating and Storage Temperature Range		T _J , T _{STG}	-55 to +150	°C	

Notes:

- 5. For the device mounted on minimum recommended pad layout FR4 PCB with high coverage of single sided 1oz copper in still air condition.
- 6. Same as Note 5, expect the device is mounted on 15mm x 15mm x 1.6mm FR4 PCB.
- 7. Thermal resistance from junction to solder-point (at the end of the collector lead).





Derating Curve

Transient Thermal Impedance

Pulse Power Dissipation




Electrical Characteristics @ TA = 25°C unless otherwise specified

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Collector-Base Breakdown Voltage	BV _{CBO}	-160	-270	-	V	$I_{C} = -100 \mu A$
Collector-Emitter Breakdown Voltage (Note 8)	BV _{CEO}	-150	-240	-	V	$I_C = -1mA$
Emitter-Base Breakdown Voltage	BV _{EBO}	-5	-8.1	-	V	I _E = -100μA
Collector Cutoff Current	I _{CBO}	-	< -1 -	-50 -50	nΑ μΑ	V _{CB} = -120V V _{CB} = -120V, T _{amb} = 100°C
Static Forward Current Transfer Ratio (Note 8)	h _{FE}	50 60 50	135 135 130	- 240 -	i	$I_C = -1mA$, $V_{CE} = -5V$ $I_C = -10mA$, $V_{CE} = -5V$ $I_C = -50mA$, $V_{CE} = -5V$
Collector-Emitter Saturation Voltage (Note 8)	V _{CE(sat)}	1 1	-50 -70	-200 -500	mV	$I_C = -10mA$, $I_B = -1mA$ $I_C = -50mA$, $I_B = -5mA$
Base-Emitter Saturation Voltage (Note 8)	V _{BE(sat)}	1	-700 -750	-1000 -1000	mV	$I_C = -10\text{mA}, I_B = -1\text{mA}$ $I_C = -50\text{mA}, I_B = -5\text{mA}$
Output Capacitance	C_obo	-	-	10	pF	$V_{CB} = -10V$, $f = 1MHz$
Transition Frequency	f _T	-	100	-	MHz	$V_{CE} = -10V$, $I_{C} = -10mA$, $f = 100MHz$
Delay Time	t _d	-	386	-	ns	
Rise Time	t _r	-	202	-	ns	$V_{CC} = -50V, I_{C} = -100mA,$
Storage Time	ts	-	1720	-	ns	$I_{B1} = -I_{B2} = -10 \text{mA}$
Fall Time	t _f	-	275	-	ns	

Notes: 8. Measured under pulsed conditions. Pulse width ≤ 300 µs. Duty cycle ≤ 2%

Typical Electrical Characteristics @ TA = 25°C unless otherwise specified






Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23




SOT23							
Dim	Min	Max	Тур				
Α	0.37	0.51	0.40				
В	1.20	1.40	1.30				
С	2.30	2.50	2.40				
D	0.89	1.03	0.915				
F	0.45	0.60	0.535				
G	1.78	2.05	1.83				
Н	2.80	3.00	2.90				
J	0.013	0.10	0.05				
K	0.890	1.00	0.975				
K1	0.903	1.10	1.025				
L	0.45	0.61	0.55				
L1	0.25	0.55	0.40				
M	0.085	0.150	0.110				
а	0°	8°					
All Dimensions in mm							

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23



Dimensions	Value (in mm)
С	2.0
Х	0.8
X1	1.35
Y	0.9
Y1	2.9



IMPORTANT NOTICE

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- products provided subject to Diodes' Standard Terms and Conditions of Sale Diodes are (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

www.diodes.com