



KBP2005G-KBP210G

2.0A GLASS PASSIVATED BRIDGE RECTIFIER

Features and Benefits

- Glass Passivated Die Construction
- High Case Dielectric Strength of 1,500 V_{RMS}
- Low Reverse Leakage Current
- Surge Overload Rating to 65A Peak
- Ideal for Printed Circuit Board Applications
- UL Listed Under Recognized Component Index, File Number E94661
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)

Mechanical Data

- Case: KBP
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Tin Plated Leads. Solderable per MIL-STD-202, Method 208 (2)
- Polarity: Marked on Body
- Marking: Type Number
- Weight: 1.52 grams (Approximate)

KBP



Ordering Information (Note 3)


Part Number	Compliance	Case	Packaging		
KBP2005G	Commercial	KBP	35 Pieces per Tube		
KBP201G	Commercial	KBP	35 Pieces per Tube		
KBP202G	Commercial	KBP	35 Pieces per Tube		
KBP204G	Commercial	KBP	35 Pieces per Tube		
KBP206G	Commercial	KBP	35 Pieces per Tube		
KBP208G	Commercial	KBP	35 Pieces per Tube		
KBP210G	Commercial	KBP	35 Pieces per Tube		

Notes: 1. EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. All applicable RoHS exemptions applied.

 See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

Marking Information





Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Single phase, half wave, 60Hz, resistive or inductive load. a load darata ront by 200

Characteristic	Symbol	KBP2005G	KBP201G	KBP202G	KBP204G	KBP206G	KBP208G	KBP210G	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _{RWM} V _{RM}	50	100	200	400	600	800	1,000	v
RMS Reverse Voltage	V _{R(RMS)}	35	70	140	280	420	560	700	V
Average Rectified Output Current @T _C = +105°C	lo				2.0				А
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half Sine-Wave Superimposed on Rated Load	I _{FSM}				65				A
$I^{2}t$ Rating for Fusing (3ms \leq t \leq 8.3ms)	l ² t				17.5				A ² s

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Typical Thermal Resistance, Junction to Case (Note 4)	R _{0JC}	14	°C/W
Typical Thermal Resistance, Junction to Lead	R _{θJL}	18	°C/W
Typical Thermal Resistance, Junction to Ambient	R _{θJL}	40	°C/W
Operating and Storage Temperature Range	TJ, TSTG	-65 to +150	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min		Тур	Max	Unit	Test Condition	
Reverse Breakdown Voltage (Note 5)	V(BR)R	KBP210G KBP208G KBP206G KBP204G KBP202G KBP201G KBP2005G	1,000 800 600 400 200 100 50	_	_	V	Ι _R = 5μΑ	
Forward Voltage Drop per Element	VF	—		—	1.1	V	I _F = 2A, T _J = +25°C	
Leakage Current (Note 5)	I _R	—		—	5 500	μA	$V_R = V_{RRM}, T_C = +25^{\circ}C$ $V_R = V_{RRM}, T_C = +125^{\circ}C$	
Total Capacitance per Element	Ст	_		25	—	pF	$V_R = 4.0V_{DC}$, f = 1MHz	

Thermal resistance from junction to case per element. Device mounted on 75mm x 75mm x 1.6mm Cu Plate Heatsink.
Short duration pulse test used to minimize self-heating effect.



2.0 1.5 1.5 0 0 0 0 0 0 50 100 150






Fig. 3 Maximum Non-Repetitive Surge Current






Fig. 5 Typical Reverse Characteristics



KBP2005G-KBP210G

V_R, REVERSE VOLTAGE (V) Fig. 4 Typical Total Capacitance, Per Element








Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.



KBP							
Dim	Min	Тур					
Α	3.35	3.65	-				
A3	0.80	1.10	-				
b	0.76	0.86	-				
b2	1.22	1.42	-				
С	0.35	0.55	-				
D	14.25	14.75	-				
E	10.20	10.60	-				
е	3.56	4.06	-				
L	14.25	14.73	-				
L1	1.80	2.20	-				
z	1.40	1.70	-				
а	-	-	3°				
a1	-	-	2°				
All Dimensions in mm							



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2017, Diodes Incorporated

www.diodes.com