

SOT223 NPN SILICON PLANAR HIGH VOLTAGE TRANSISTOR

BSP20


ISSUE 3 – FEBRUARY 1996

FEATURES

- * High V_{CEO}
- * Low saturation voltage

COMPLEMENTARY TYPE – BSP15

PARTMARKING DETAIL – BSP20



ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	VALUE	UNIT
Collector-Base Voltage	V_{CBO}	300	V
Collector-Emitter Voltage	V_{CEO}	250	V
Emitter-Base Voltage	V_{EBO}	5	V
Peak Pulse Current	I_{CM}	1	A
Continuous Collector Current	I_C	0.5	A
Power Dissipation at $T_{amb}=25^{\circ}C$	P_{tot}	2	W
Operating and Storage Temperature Range	$T_j; T_{stg}$	-55 to +150	$^{\circ}C$

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}C$ unless otherwise stated).

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	CONDITIONS.
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	300			V	$I_C=100\mu A$
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	250			V	$I_C=10mA^*$
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	5			V	$I_E=100\mu A$
Collector Cut-Off Current	I_{CBO}			20	nA	$V_{CB}=300V$
Emitter Cut-Off Current	I_{EBO}			50	nA	$V_{EB}=5V$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$			0.5	V	$I_C=50mA, I_B=4mA^*$
Base-Emitter Saturation Voltage	$V_{BE(sat)}$			1.3	V	$I_C=50mA, I_B=4mA^*$
Base-Emitter Turn-On Voltage	$V_{BE(on)}$			2.0	V	$I_C=100mA, V_{CE}=10V^*$
Static Forward Current Transfer Ratio	h_{FE}	40 30		200		$I_C=20mA, V_{CE}=10V^*$ $I_C=30mA, V_{CE}=10V^*$
Transition Frequency	f_T	40		200	MHz	$I_C=10mA, V_{CE}=20V$ $f = 20MHz$
Output Capacitance	C_{obo}			6	pF	$V_{CB}=20V, f=1MHz$

*Measured under pulsed conditions. Pulse width=300 μs . Duty cycle $\leq 2\%$
For typical characteristics graphs see FMMTA42 datasheet.