






DUAL PNP SMALL SIGNAL SURFACE MOUNT TRANSISTOR


Features

- **Epitaxial Planar Die Construction**
- Ideal for Low Power Amplification and Switching
- Ultra-Small Surface Mount Package
- Lead Free By Design/RoHS Compliant (Note 1)
- Qualified to AEC-Q101 Standards for High Reliability
- "Green" Device (Note 4 and 5)


Mechanical Data

- Case: SOT-563
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020C
- Terminal Connections: See Diagram
- Terminals: Finish Matte Tin annealed over Alloy 42 leadframe. Solderable per MIL-STD-202, Method 20
- Terminals: Lead bearing terminal plating available. See Ordering information Page 3
- Marking & Type Code Information: See Page 3
- Ordering Information: See Page 3
- Weight: 0.003 grams (approximate)









SOT-563									
Dim	Min	Max	Тур						
Α	0.15	0.30	0.25						
В	1.10	1.25	1.20						
С	1.55	1.60							
D	0.50								
G	0.90	1.10	1.00						
Н	1.50	1.60							
K	0.56	0.60	0.60						
L	0.10	0.30	0.20						
М	0.10	0.18	0.11						
All Dimensions in mm									

Maximum Ratings @TA = 25°C unless otherwise specified

Characteristic	Symbol	Value	Unit	
Collector-Base Voltage	V_{CBO}	-40	V	
Collector-Emitter Voltage	V _{CEO}	-40	V	
Emitter-Base Voltage	V_{EBO}	-5.0	V	
Collector Current - Continuous	Ic	-200	mA	

Thermal Characteristics

Characteristic		Symbol	Value	Unit	
Power Dissipation	(Note 3) @ T _A = 25°C	P_d	150	mW	
Thermal Resistance, Junction to Ambient	(Note 3) @ T _A = 25°C	$R_{ hetaJA}$	833	°C/W	
Operating and Storage Temperature Range		T _j , T _{STG}	-55 to +150	°C	


- 1. No purposefully added lead.
- 2. Package is non-polarized. Parts may be on reel in orientation illustrated, 180° rotated, or mixed (both ways).
- 3. Device mounted on FR-4 PCB, 1 inch x 0.85 inch x 0.062 inch; pad layout as shown on Diodes Inc. suggested pad layout document AP02001, which can be found on our website at http://www.diodes.com/datasheets/ap02001.pdf.
- Diodes Inc.'s "Green" policy can be found on our website at http://www.diodes.com/products/lead_free/index.php.
- Product manufactured with Date Code UO (week 40, 2007) and newer are built with Green Molding Compound. Product manufactured prior to Date Code UO are built with Non-Green Molding Compound and may contain Halogens or Sb2O3 Fire Retardants.




Electrical Characteristics @TA = 25°C unless otherwise specified


Characteristic	Symbol	Symbol Min Max Uni		Unit	Test Condition		
OFF CHARACTERISTICS (Note 6)				•			
Collector-Base Breakdown Voltage	V _{(BR)CBO}	-40		V	$I_C = -10\mu A, I_E = 0$		
Collector-Emitter Breakdown Voltage	V _{(BR)CEO}	-40		V	$I_C = -1.0 \text{mA}, I_B = 0$		
Emitter-Base Breakdown Voltage	V _{(BR)EBO}	-5.0		V	$I_E = -10\mu A$, $I_C = 0$		
Collector Cutoff Current	I _{CEX}		-50	nA	$V_{CE} = -30V, V_{EB(OFF)} = -3.0V$		
Base Cutoff Current	I _{BL}		-50	nA	$V_{CE} = -30V, V_{EB(OFF)} = -3.0V$		
ON CHARACTERISTICS (Note 6)							
DC Current Gain	h _{FE}	60 80 100 60 30	 300 	_	$\begin{split} I_{C} &= -100 \mu A, V_{CE} = -1.0 V \\ I_{C} &= -1.0 m A, V_{CE} = -1.0 V \\ I_{C} &= -10 m A, V_{CE} = -1.0 V \\ I_{C} &= -50 m A, V_{CE} = -1.0 V \\ I_{C} &= -100 m A, V_{CE} = -1.0 V \end{split}$		
Collector-Emitter Saturation Voltage	V _{CE(SAT)}		-0.25 -0.40	V	$I_C = -10$ mA, $I_B = -1.0$ mA $I_C = -50$ mA, $I_B = -5.0$ mA		
Base-Emitter Saturation Voltage	V _{BE(SAT)}	-0.65 —	-0.85 -0.95	٧	$I_C = -10$ mA, $I_B = -1.0$ mA $I_C = -50$ mA, $I_B = -5.0$ mA		
SMALL SIGNAL CHARACTERISTICS							
Output Capacitance	C_{obo}		4.5	pF	$V_{CB} = -5.0V$, $f = 1.0MHz$, $I_E = 0$		
Input Capacitance	C _{ibo}	_	10	pF	$V_{EB} = -0.5V$, $f = 1.0MHz$, $I_C = 0$		
Input Impedance	h _{ie}	2.0	12	kΩ			
Voltage Feedback Ratio	h _{re}	0.1	10	x 10 ⁻⁴	V _{CE} = 10V, I _C = 1.0mA,		
Small Signal Current Gain	h _{fe}	100	400		f = 1.0kHz		
Output Admittance	h _{oe}	3.0	60	μS			
Current Gain-Bandwidth Product	f _T	250	_	MHz	$V_{CE} = -20V, I_C = -10mA,$ f = 100MHz		
Noise Figure	NF	_	4.0	dB	V_{CE} = -5.0V, I_{C} = -100 μ A, R_{S} = 1.0k Ω , f = 1.0kHz		
SWITCHING CHARACTERISTICS	•						
Delay Time	t _d		35	ns	V _{CC} = -3.0V, I _C = -10mA,		
Rise Time	t _r		35	ns	$V_{BE(off)} = 0.5V, I_{B1} = -1.0mA$		
Storage Time	ts	_	225	ns	V _{CC} = -3.0V, I _C = -10mA,		
Fall Time	t _f	_	75	ns	I _{B1} = I _{B2} = -1.0mA		


Notes: 6. Short duration pulse test used to minimize self-heating effect.












vs. Collector Current




Ordering Information (Note 7)

Device	Packaging	Shipping
MMDT3906V-7	SOT-563	3000/Tape & Reel

7. For packaging details, go to our website at http://www.diodes.com/datasheets/ap02007.pdf.

Marking Information



Date Code Key

Year	2005		2006	2007		2008	2009		2010	201	ı	2012
Code	S		Т	U		V	W		Х	Y		Z
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Au	g Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D



IMPORTANT NOTICE

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Diodes Incorporated does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

Diodes Incorporated products are not authorized for use as critical components in life support devices or systems without the expressed written approval of the President of Diodes Incorporated.