

NOT RECOMMENDED FOR NEW DESIGN USE 1N4448WSF-7



SURFACE MOUNT FAST SWITCHING DIODE PowerDl[®] 323

PD3SD2580

Features

- Fast Switching Speed
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability

Mechanical Data

- Case: PowerDI323
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020D
- Leads: Matte Tin Finish annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208
- Polarity: Cathode Band
- Marking Information: See Below
- Ordering Information: See Below
- Weight: 0.005 grams (approximate)



Ordering Information (Note 4)

Part Number	Case		Packaging
PD3SD2580-7	PowerDI323		3000/Tape & Reel
	800 800	1000	

1. EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. All applicable RoHS exemptions applied.

2. See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

4. For packaging details, go to our website at http"//www.diodes.com/products/packages.html.

Marking Information



D1 = Product Type Marking Code YM = Date Code Marking Y = Year (ex: T = 2006) M = Month (ex: 9 = September)

Date Code Key

Notes:

Year	2006	20	07	2008	2009	2010	2011	2012	2013	2014	2015	2016	2017
Code	Т	ι	J	V	W	Х	Y	Z	А	В	С	D	E
Month		Jan	Feb	Mai	· Apr	Мау	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code		1	2	3	4	5	6	7	8	9	0	Ν	D

^{3.} Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit		
Non-Repetitive Peak Reverse Voltage		V _{RM}	100	V		
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage		V _{RRM} V _{RWM} V _R	80	V		
RMS Reverse Voltage		V _{R(RMS)}	57	V		
Forward Continuous Current		I _{FM}	250	mA		
Repetitive Peak Forward Current		IFRM	500	mA		
· · · · · · · · · · · · · · · · · · ·	@ t = 1.0ms @ t = 1.0s	I _{FSM}	3.3 0.5	A		

Thermal Characteristics

	·	
Symbol	Value	Unit
PD	500	mW
R _{0JA}	250	ſW
TJ, TSTG	-65 to +150	°C
	PD Reja	P _D 500 R _{8JA} 250

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.),

Characteristic	Symbol	Min	Max	Unit	Test Condition
Reverse Breakdown Voltage (Note 5)	V _{BR(R)}	80	_	V	I _R = 1μΑ
		—	0.715		I _F = 1.0mA
	VF		0.72	v	I _F = 5.0mA
Forward Voltage		_	0.855		I _F = 10mA
roiwaid voltage		—	0.90		I _F = 50mA
		—	1.0		I _F = 100mA
		_	1.25		I _F = 150mA
			25	nA	V _R = 20V
			30	nA	V _R = 25V
Leakage Current (Note 5)	IR	—	100	nA	V _R = 80V
			30	μA	$V_R = 25V, T_J = +150^{\circ}C$
			50	μA	V _R = 75V, T _J = +150°C
Total Capacitance	CT	_	2.3	pF	V _R = 0, f = 1.0MHz
			10		$I_F = I_R = 10 \text{mA},$
Reverse Recovery Time	t _{rr}	—	4.0	ns	$I_{rr} = 0.1 \text{ x } I_R, R_L = 100\Omega$


Notes:

Short duration pulse test used to minimize self-heating effect.
Part mounted on FR-4 PC board with recommended pad layout, which can be found on our website at http://www.diodes.com/datasheets/ap02001.pdf.

NOT RECOMMENDED FOR NEW DESIGN USE 1N4448WSF-7



PD3SD2580




PowerDI is a registered trademark of Diodes Incorporated. PD3SD2580




Package Outline Dimensions

Please see AP02002 at http://www.diodes.com/datasheets/ap02002.pdf for latest version.



Suggested Pad Layout

Please see AP02001 at http://www.diodes.com/datasheets/ap02001.pdf for the latest version.



Dimensions	Value (in mm)
G	0.5
X1	2.0
X2	0.8
Y1	0.8
Y2	1.1



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or

- 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2013, Diodes Incorporated

www.diodes.com