

## Product Summary

$V_{RRM}$ (V)	$I_o$ (A)	$V_F$ Typ (V) @ +25°C	$t_{RR}$ Typ (ns) @ +25°C	$I_{RM}$ Typ (A) @ +25°C
600	10	2.5	15	1.7

## Description and Application

The 10A, 600V DIODES™ DSR10F600P rectifier is designed specifically for use as a boost diode in power factor correction (PFC) applications. Its soft, very fast switching characteristics make it ideal for use in hard switching and continuous conduction mode (CCM) PFC circuits. It can be used in:

- High Power SMPS
- Servers and Telecom Equipment
- Flat-Panel TVs



## Features and Benefits

- Very Fast  $t_{RR}$  Reduces MOSFET PFC Switching Losses
- Soft Switching Ensures Ringing and EMI are Reduced
- Low  $Q_{RR}$  and  $I_{RM}$  Minimize Boost Diode Recovery Losses
- **Lead-Free Finish; RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**
- **For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please [contact us](#) or your local Diodes representative.**

<https://www.diodes.com/quality/product-definitions/>

## Mechanical Data

- Case: TO220AC
- Case Material: Molded Plastic, Green Molding Compound. UL Flammability Classification Rating 94V-0
- Terminals: Matte Tin Finish Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 <sup>Ⓔ</sup>
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections: See Diagram Below
- Weight: 1.75 grams (Approximate)




## Ordering Information (Note 4)

Part Number	Case	Packaging
DSR10F600P	TO220AC (Type E) TO220AC (Type HE) (Future Release)	50 Pieces/Tube

- Notes:
1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
  2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
  3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
  4. For packaging details, go to our website at <https://www.diodes.com/design/support/packaging/diodes-packaging/>.

## Marking Information



ⓁⓂ = Manufacturer's Marking  
 DSR10F600 = Product Type Marking Code  
 AB = Foundry and Assembly Code  
 YYWW = Date Code Marking  
 YY = Last Two Digits of Year (ex: 21 = 2021)  
 WW = Week (01 to 53)

**Maximum Ratings** (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Peak Repetitive Reverse Voltage	V <sub>RRM</sub>	600	V
Working Peak Reverse Voltage	V <sub>RWM</sub>		
DC Blocking Voltage	V <sub>RM</sub>		
Average Rectified Output Current (Note 6)	I <sub>O</sub>	10	A
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half Sine-Wave Superimposed on Rated Load	I <sub>FSM</sub>	90	A

**Thermal Characteristics**

Characteristic	Symbol	Value	Unit
Typical Thermal Resistance, Junction to Case (Note 5)	R <sub>θJC</sub>	29	°C/W
Typical Thermal Resistance, Junction to Ambient (Note 5)	R <sub>θJA</sub>	56	°C/W
Typical Thermal Resistance, Junction to Case (Note 6)	R <sub>θJC</sub>	6	°C/W
Typical Thermal Resistance, Junction to Ambient (Note 6)	R <sub>θJA</sub>	11	°C/W
Storage Temperature Range	T <sub>STG</sub>	-55 to +175	°C
Maximum Operating Junction Temperature	T <sub>J</sub>	+175	°C

Notes: 5. Device free standing no heat sink.  
6. Device is mounted on a 20mm × 70mm × 19.8mm Al heat sink.

NOT RECOMMENDED FOR NEW DESIGN

**Electrical Characteristics** (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Voltage	V <sub>BR</sub>	600	—	—	V	I <sub>R</sub> = 50μA
Forward Voltage Drop	V <sub>F</sub>	—	2.5	3.2	V	I <sub>F</sub> = 10A, T <sub>J</sub> = +25°C
		—	1.7	—		I <sub>F</sub> = 10A, T <sub>J</sub> = +125°C
		—	1.5	—		I <sub>F</sub> = 10A, T <sub>J</sub> = +150°C
Leakage Current (Note 7)	I <sub>R</sub>	—	0.5	20	μA	V <sub>R</sub> = 600V, T <sub>J</sub> = +25°C
		—	12	—		V <sub>R</sub> = 600V, T <sub>J</sub> = +125°C
		—	40	—		V <sub>R</sub> = 600V, T <sub>J</sub> = +150°C
Junction Capacitance	C <sub>T</sub>	—	26	—	pF	V <sub>R</sub> = 10V, f = 1MHz
Reverse Recovery Time	t <sub>RR</sub>	—	15	30	ns	I <sub>F</sub> = 0.5A, I <sub>R</sub> = 1.0A, I <sub>RR</sub> = 0.25A
		—	26	—		I <sub>F</sub> = 1A, di/dt = 50A/μs, V <sub>R</sub> = 30V, T <sub>J</sub> = +25°C
		—	18	—		I <sub>F</sub> = 1A, di/dt = 100A/μs, V <sub>R</sub> = 30V, T <sub>J</sub> = +25°C
		—	52	—		I <sub>F</sub> = 10A, di/dt = 200A/μs, V <sub>R</sub> = 400V, T <sub>J</sub> = +25°C
		—	75	—		I <sub>F</sub> = 10A, di/dt = 200A/μs, V <sub>R</sub> = 400V, T <sub>J</sub> = +125°C
Reverse Recovery Current (Note 7)	I <sub>RM</sub>	—	1.7	—	A	I <sub>F</sub> = 10A, di/dt = 200A/μs, V <sub>R</sub> = 400V, T <sub>J</sub> = +25°C
		—	3.8	—		I <sub>F</sub> = 10A, di/dt = 200A/μs, V <sub>R</sub> = 400V, T <sub>J</sub> = +125°C
Reverse Recovery Charge	Q <sub>RR</sub>	—	43	—	nC	I <sub>F</sub> = 10A, di/dt = 200A/μs, V <sub>R</sub> = 400V, T <sub>J</sub> = +25°C
		—	140	—		I <sub>F</sub> = 10A, di/dt = 200A/μs, V <sub>R</sub> = 400V, T <sub>J</sub> = +125°C

Note: 7. Short duration pulse test used to minimize self-heating effect.

NOT RECOMMENDED FOR NEW DESIGN




Figure 1. Typical Forward Characteristics




Figure 2. Typical Reverse Characteristics




Figure 3. Total Capacitance vs. Reverse Voltage




Figure 4. Forward Current Derating Curve




Figure 5. Forward Power Dissipation






Figure 6. Operating Temperature Derating Curve

**Test Circuit and Waveform Definitions**



$t_{RR}$  Test Circuit




$t_{RR}$  Waveform and Definitions

NOT RECOMMENDED FOR NEW DESIGN

**Package Outline Dimensions**

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

**TO220AC (Type E)**




TO220AC (Type E)			
Dim	Min	Max	Typ
A	4.40	4.82	--
A1	1.10	1.40	--
A2	2.05	2.92	--
b	0.72	1.00	--
b2	1.16	1.45	--
c	0.36	0.68	--
D	14.70	15.87	--
e1	--	--	5.08
E	9.80	10.26	--
H1	5.80	6.40	--
L	12.70	13.96	--
L1	3.56	4.50	--
L2	-	1.30	--
P	3.70	3.90	--
Q	2.54	3.30	--
All Dimensions in mm			

NOT RECOMMENDED FOR NEW DESIGN

**Package Outline Dimensions**

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

**TO220AC (Type HE) (Future Release)**



TO220AC (Type HE)			
Dim	Min	Max	Typ
A	4.37	4.77	4.57
A1	1.22	1.42	1.27
A2	2.49	2.89	2.69
b	0.76	0.91	0.81
b2	1.17	1.47	1.27
c	0.30	0.48	0.38
D1	8.50	8.90	8.70
e	5.08 BSC		
E	9.86	10.36	10.16
H1	6.10	6.50	6.30
L	13.10	13.70	13.40
L1	--	4.10	3.75
PØ	3.70	3.99	3.84
Q	2.54	2.94	2.74
All Dimensions in mm			

NOT RECOMMENDED FOR NEW DESIGNS

**IMPORTANT NOTICE**

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

DIODES is a trademark of Diodes Incorporated in the United States and other countries.  
The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.  
© 2022 Diodes Incorporated. All Rights Reserved.

[www.diodes.com](http://www.diodes.com)