

# PNP SILICON PLANAR MEDIUM POWER TRANSISTOR

## FXT751


**ISSUE 1 – FEB 94**
**FEATURES**

- \* 60 Volt  $V_{CEO}$
- \* 2 Amp continuous current
- \*  $P_{tot} = 1$  Watt

**APPLICATIONS**

- \* Lamp, relay or solenoid drivers
- \* Audio circuits
- \* Replacement of TO126 and TO220 parts

REFER TO ZTX751 FOR GRAPHS


**E-Line  
TO92 Compatible**
**ABSOLUTE MAXIMUM RATINGS.**

PARAMETER	SYMBOL	VALUE	UNIT
Collector-Base Voltage	$V_{CBO}$	-80	V
Collector-Emitter Voltage	$V_{CEO}$	-60	V
Emitter-Base Voltage	$V_{EBO}$	-5	V
Peak Pulse Current	$I_{CM}$	-6	A
Continuous Collector Current	$I_C$	-2	A
Power Dissipation at $T_{amb}=25^{\circ}C$	$P_{tot}$	1	W
Operating and Storage Temperature Range	$T_j; T_{stg}$	-55 to +200	$^{\circ}C$

**ELECTRICAL CHARACTERISTICS (at  $T_{amb} = 25^{\circ}C$  unless otherwise stated).**

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	CONDITIONS.
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	-80			V	$I_C = -100\mu A, I_E = 0$
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	-60			V	$I_C = -10mA, I_B = 0^*$
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	-5			V	$I_E = -100\mu A, I_C = 0$
Collector Cut-Off Current	$I_{CBO}$			-0.1 -10	$\mu A$ $\mu A$	$V_{CB} = -60V, I_E = 0$ $V_{CB} = -60V, T_{amb} = 100^{\circ}C$
Emitter Cut-Off Current	$I_{EBO}$			-0.1	$\mu A$	$V_{EB} = -4V, I_C = 0$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$		-0.15 -0.28	-0.3 -0.5	V V	$I_C = -1A, I_B = -100mA^*$ $I_C = -2A, I_B = -200mA^*$
Base-Emitter Saturation Voltage	$V_{BE(sat)}$		-0.90	-1.25	V	$I_C = -1A, I_B = -100mA^*$
Base-Emitter Turn-On Voltage	$V_{BE(on)}$		-0.8	-1.0	V	$I_C = -1A, V_{CE} = -2V^*$
Static Forward Current Transfer Ratio	$h_{FE}$	70 100 80 40	200 200 170 150	300		$I_C = -50mA, V_{CE} = -2V^*$ $I_C = -500mA, V_{CE} = -2V^*$ $I_C = -1A, V_{CE} = -2V^*$ $I_C = -2A, V_{CE} = -2V^*$
Transition Frequency	$f_T$	100	140		MHz	$I_C = -100mA, V_{CE} = -5V$ $f = 100MHz$
Output Capacitance	$C_{obo}$			30	pF	$V_{CB} = -10V, f = 1MHz$

 \*Measured under pulsed conditions. Pulse width=300 $\mu s$ . Duty cycle  $\leq 2\%$