AH2985



#### TWO PHASE HALL-EFFECT SMART FAN MOTOR CONTROLLER

### **Description**

The AH2985 is a single-chip solution for driving two-coil brushless direct current (BLDC) fans and motors. The device includes a Halleffect sensor, dynamic offset correction and two complementary opendrain output drivers with internal Zener diode protection. It is optimized for low start-up voltage.

To help protect the motor coils, the AH2985 provides Rotor Lock Protection which shuts down output drives if rotor lock is detected. The device automatically re-starts when the rotor lock is removed. Over temperature shutdown provides thermal protection for the device.


The AH2985 is available in TO94 package.

#### **Features**

- Single-Chip Solution
- Operating Voltage: 2.5V to 15V
- Built-in Hall Sensor and Input Amplifier
- Rotor Lock Protection (Lock Detection, Output Shutdown and Automatic re-Start)
- Built-in Reverse Voltage Protection Diode
- Built-in Zener Protection for Output Drivers
- Average Output Current up to 500mA
- Package: TO94
- "Green" Molding Compound
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)

### **Pin Assignments**

(Top View)




# Applications

- Two-Coil BLDC Cooling Fans
- Low Voltage/ Low Power BLDC Motors

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
  2. See http://www.diodes.com/quality/lead\_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green"
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

### Typical Applications Circuit (Note 4)



12V Brushless DC Fan


4. D1 (Zener Diode) and Capacitor C are for power stabilization. Recommended value of C is 1μF/50V (E-Cap). Diode D2 is optional and helps to protect the device and fan coils from reverse power conditions. The AH2985 also includes an internal reverse blocking diode at V<sub>DD</sub> pin.



## **Pin Descriptions**

Pin Number Pin Name		Function
1 V <sub>DD</sub> II		Input Power
2	DO	Output Pin
3	DOB	Output Pin
4	GND	Ground

## **Functional Block Diagram**





### Absolute Maximum Ratings (@TA = +25°C, unless otherwise specified.) (Note 5)

Symbol	Parameter	Rating	Unit	
V <sub>DD</sub>	Supply Voltage	18	V	
V <sub>RDD</sub>	Reverse V <sub>DD</sub> Polarity Voltage	-15	V	
I <sub>O(AVE)</sub>		500		
IO(peak as hold)	Output Current (Note 6)	800	mA	
PD	Power Dissipation	550	mW	
T <sub>STG</sub>	Storage Temperature	-55 to +150	°C	
TJ	Maximum Junction Temperature	+150	°C	
θЈА	Thermal Resistance	227	°C/W	
θυς	Thermal Resistance	49	°C/W	

Notes:

### Recommended Operating Conditions (@TA = +25°C, unless otherwise specified.)

Symbol	Parameter	Condition	Min	Max	Unit
V <sub>DD</sub>	Supply Voltage	Operating	2.5	15	V
TA	Operating Ambient Temperature (Note 6)	Operating	-40	+105	°C

### Electrical Characteristics (@T<sub>A</sub> = +25°C, V<sub>DD</sub> = 12V, unless otherwise specified.)

Symbol	Parameter	Condition	Min	Тур	Max	Unit	
IDD	Supply Current	Operating, V <sub>DD</sub> = 12V	ı	1	5	mA	
ton	Locked Protection On Time	-	-	0.45	-	S	
toff	Locked Protection Off Time	-	_	2.7	_	s	
R <sub>DUTY</sub>	Locked Protection Duty Ratio	toff/ton	1	6	1	ı	
D	Output On Registeres	I <sub>O</sub> = 300mA	1	1	1.6		
RDS(ON)	Output On Resistance	I <sub>O</sub> = 500mA	-	1	1.8	Ω	
Vz	Output Zener-Breakdown Voltage	(Note 7)	20	28	36	V	

Note: 7. The  $V_Z$  value is in D.C voltage measurement. The  $V_Z$  may vary with coils in A.C. voltage measurements.

<sup>5.</sup> Stresses greater than those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "Recommended Operating Conditions" is not implied. Exposure to "Absolute Maximum Ratings" for extended periods may affect device reliability.

<sup>6.</sup> Shall not exceed P<sub>D</sub> and Safety Operation Area.




### Magnetic Characteristics (TA = +25°C, VDD = 2.5V to 15V, Note 8)

(1mT=10 Gauss)

Symbol	Parameter	Min	Тур	Max	Unit
Вор	Operate Point	5	30	60	Gauss
B <sub>RP</sub>	Release Point	-60	-30	-5	Gauss
Вну	Hysteresis	20	60	120	Gauss

Note: 8. The magnetic characteristics may vary with supply voltage, operating temperature and after soldering.

## **Operating Characteristics**






## **Performance Characteristics**

#### (1) TO94

T <sub>A</sub> (°C)	25	50	60	70	80	85	90	95	100
P <sub>D</sub> (mW)	550	440	396	352	308	286	264	242	220
T <sub>A</sub> (°C)	105	110	115	120	125	130	135	140	150
P <sub>D</sub> (mW)	198	176	154	132	110	88	66	44	0

## $P_D$ (mW)


### Power Dissipation Curve



T<sub>A</sub> (°C)



## **Ordering Information** (Note 9)




Part Number	Backago Codo	Packaging	Bulk		
Part Number	Package Code	(Note 9)	Quantity	Part Number Suffix	
AH2985-P-B	Р	TO94	1000	-B	

Note: 9. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

## **Marking Information**

(1) TO94



Y: Year: 0~9

WW: Week: 01~52, "52" represents

52 and 53 week


 $\underline{X}$ : Internal Code: A~Z: Green




### Package Outline Dimensions (All dimensions in mm.)

Please see AP02002 at http://www.diodes.com/datasheets/ap02002.pdf for the latest version.

#### (1) Package Type: TO94



TO94							
Dim	m Min Max						
Α	1.46	1.66	<b>Typ</b> 1.56				
A3	1	1	0.76				
q	0.35	0.56	0.39				
b2	-	-	0.46				
C	0.36	0.51	0.38				
D	5.12	5.32	5.22				
Е	3.55	3.75	3.65				
е		-	1.27				
e1	-	-	3.81				
Г	13.50	15.50	14.50				
L1	-	-	1.42				
S	0.63	0.83	0.73				
θ	-	-	6°				
θ1	-	-	4°				
θ2	-	-	11°				
θ3	-	-	6°				
All Dimensions in mm							





#### IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<a href="https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/">https://www.diodes.com/about/company/terms-and-conditions-of-sales/</a>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at <a href="https://www.diodes.com/about/company/terms-and-conditions/important-notice">https://www.diodes.com/about/company/terms-and-conditions/important-notice</a>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners.

© 2024 Diodes Incorporated, All Rights Reserved.

www.diodes.com

AH2985 8 of 8 February 2024

Document number: DS38175 Rev. 2 - 3 www.diodes.com © 2024 Copyright Diodes Incorporated. All Rights Reserved.