

**ESD PROTECTION DEVICE**

STAND-OFF VOLTAGE - **5.0** Volts  
POWER DISSIPATION - **130** WATTS

**GENERAL DESCRIPTION**

The L13L5V0C6-4C is ultra low capacitance TVS arrays designed to protect high speed data interfaces. This series has been specifically designed to protect sensitive components which are connected to high-speed data and transmission lines from overvoltage caused by ESD (electrostatic discharge), CDE (Cable Discharge Events), and EFT (electrical fast transients).

**FEATURES**

- Protects up to four high-speed I/O lines & one power line
- Low capacitance: 1.5pF typical (I/O to Gnd)
- Low clamping voltage
- IEC 61000-4-2 ( ESD ), > ±28KV ( air ) ; > ±21KV ( contact )


**APPLICATION**

- USB2.0 Power and Data lines protection
- Digital Visual Interface (DVI)
- Notebook and PC Computers
- Video Graphics Cards
- SIM ports

**MECHANICAL DATA**


- Case Material: "Green" molding compound UL flammability classification 94V-0 (No Br, Sb, Cl)
- Terminals: Lead Free Plating (Matte Tin Finish)
- Component in accordance to RoHs 2011/65/EU

**SOT23-6L**



SOT23-6L		
DIM.	MIN.	MAX.
A	0.90	1.45
A1	0.00	0.15
A2	0.90	1.30
b	0.30	0.50
c	0.08	0.22
D	2.45	3.00
E	1.50	1.75
E1	2.80 typ.	
e	0.95 typ.	
e1	1.90 typ.	
L	0.30	0.60

All Dimensions in millimeter



4 lines Protection

PIN ASSIGNMENT	
1, 3, 4, 6	I/O Lines
5	V <sub>CC</sub>
2	Ground

**OBSOLETE – PART DISCONTINUED**

**MAXIMUM RATINGS (T<sub>j</sub>= 25°C unless otherwise noticed)**

Rating	Symbol	Value	Unit
Peak Pulse Power (t <sub>p</sub> = 8/20us)	P <sub>pk</sub>	130	W
Peak Pulse Current (t <sub>p</sub> = 8/20us)	I <sub>pp</sub>	5.5	A
Operating Junction Temperature Range	T <sub>J</sub>	-55 to + 125	°C
Storage Temperature Range	T <sub>stg</sub>	-55 to + 150	°C
Soldering Temperature, t <sub>max</sub> = 10s	T <sub>L</sub>	260	°C

**ELECTRICAL CHARACTERISTICS (T<sub>j</sub>= 25°C unless otherwise noticed)**

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
Reverse standoff voltage	V <sub>RWM</sub>	Any pin to ground	---	---	5.0	V
Breakdown voltage	V <sub>BR</sub>	I <sub>R</sub> = 1 mA	6.0	---	9.0	V
Reverse leakage current	I <sub>RM</sub>	V <sub>DRM</sub> = 5V	---	---	1	uA
Clamping Voltage	V <sub>C</sub>	I <sub>PP</sub> = 1A, t <sub>p</sub> = 8/20μs, Any I/O pin to ground	---	---	10	V
		I <sub>PP</sub> = 5A, t <sub>p</sub> = 8/20μs, Any I/O pin to ground	---	---	26	
Junction capacitance	C <sub>J</sub>	V <sub>R</sub> = 2.5V, f = 1MHz, Any I/O pin to ground	---	0.9	1.7	pF




Figure 1. 8/20 us pulse waveform according to IEC 61000-4-5




Figure 2. ESD pulse waveform according to IEC 61000-4-2




Figure 3. Power Dissipation versus Pulse Time




Figure 4. Peak pulse power versus TJ




Figure 5. Typical Junction Capacitance




Figure 6. Reverse Leakage Current versus TJ




Figure 7. ESD Test Configuration




Figure 8. Clamped +8 kV ESD voltage waveform





Figure 9. Clamped -8 kV ESD voltage waveform

OBSOLETE


**Marking & Orientation**



**Packaging Information**

DEVICE	Q'TY/REEL (PCS)	REEL DIA. (INCH)	Q'TY/BOX (PCS)	Q'TY/CARTON (PCS)
L13L5V0C6-4C	3000	7	45000	90K/180K

**SOT23-6L Soldering Pad Layout**



Dim.	Millimeters	Inches
Z	3.60	0.141
X	0.80	0.031
W	2.60	0.102
Y	1.00	0.039
V	0.95	0.037

## Important Notice and Disclaimer

LSC reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

LSC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does LSC assume any liability for application assistance or customer product design. LSC does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of LSC.

LSC products are not authorized for use as critical components in life support devices or systems without express written approval of LSC.

OBSELETE