



DIMMABLE LED DRIVER

## Description

The DIODES<sup>™</sup> AL1692-10E is a high performance, high power factor, high efficiency, and high current precision buck-boost and flyback dimmable LED driver for triac dimmable LED lamp applications. The AL1692-10E topology provides an accurate output current over wide line and load regulation. The wide switching frequency operates at boundary conduction mode (BCM) to ease EMI/EMC design and testing to meet the latest regulatory standards.

The AL1692-10E LED driver integrates a 700V/1A high voltage MOSFET. It can cover both 120Vac and 230Vac triac dimmable applications with eliminating the external high voltage MOSFET and varistor, which will reduce the system BOM cost. The AL1692-10E has the built-in thermal fold-back protection trigger point to automatically reduce output current. Other protection features enhance LED lighting system's safety and reliability.

The AL1692-10E dimming curve is compliant with the NEMA SSL6 standard. The AL1692-10E applies to a wide range of dimmers, including leading edge and trailing edge dimmer, to achieve deep dimming down to 1%.

The AL1692-10E is available in SO-7 package.


### Features

- Tight Current Sense Tolerance : ±3%
- Low Startup Current: 100µA Typical
- Low Operation Current: 210µA (Switching Frequency at 4kHz
- Single Winding Inductor
- Wide Range of Dimmer Compatibility
- Integration of 700V/1A MOSFET
- NEMA SSL6 Dimming Curve Compliant
- Internal Protections
  - Under Voltage Lockout (UVLO)
  - Leading-Edge Blanking (LEB)
  - Cycle-by-Cycle Over Current Protection (OCP)
  - Output Open/Short Protection (OVP/OSP)
  - Thermal Foldback Protection (TFP)
  - Over-Temperature Protection (OTP)
- SO-7 Package
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. <u>https://www.diodes.com/quality/product-definitions/</u>
- Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
  - 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

# Pin Assignments




# Applications

- Mains dimmable LED lamps
- Offline LED power supply drivers



# **Typical Application Circuits**




# **Pin Descriptions**

Pin Number	Pin Name	Function
1	VCC	Power supply voltage
2	RT	Resistor set the system's maximum ton
3	COMP	Compensation for current control
4	GND	Ground
5	FB	Feedback for LED open protection voltage
6	CS	Current sensing
7	D	Drain of the internal high voltage MOSFET





# **Functional Block Diagram**





Symbol	Parameter	Rating	Unit
Vcc	Power Supply Voltage	18	V
VD	Voltage on Drain Pin	700	V
IDS	Continuous Drain Current T <sub>C</sub> = +25°C	1	А
Vcs	Voltage on CS Pin	-0.3 to 7	V
V <sub>RT</sub>	Voltage on RT Pin	-0.3 to 7	V
VFB	Voltage on FB Pin	-0.3 to 7	V
TJ	Operating Junction Temperature	-40 to +150	°C
T <sub>STG</sub>	Storage Temperature	-65 to +150	°C
TLEAD	Lead Temperature (Soldering, 10 seconds)	+260	°C
PD	Power Dissipation ( $T_A = +50^{\circ}C$ ) (Note 5)	0.8	W
ΑLθ	Thermal Resistance (Junction to Ambient) (Note 5)	123	°C/W
θ」C	Thermal Resistance (Junction to Case) (Note 5)	19	°C/W
_	ESD (Human Body Model)	2,000	V

# Absolute Maximum Ratings (@TA = +25°C, unless otherwise specified.) (Note 4)

Notes: 4. Stresses greater than those listed under Absolute Maximum Ratings can cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to Absolute Maximum Ratings for extended periods can affect device reliability. All voltages unless otherwise stated are measured with respect to GND.

5. Device mounted on 1" x 1" FR-4 substrate PCB, 2oz copper, with minimum recommended pad layout.

# Recommended Operating Conditions (@TA = +25°C, unless otherwise specified.)

Symbol	Parameter	Min	Мах	Unit
T <sub>A</sub>	Ambient Temperature (Note 6)	-40	+105	°C
Vcc	Operating Vcc Voltage	10	VCC_CLAMP (Min)	V

Note: 6. The device may operate normally at +125°C ambient temperature under the condition not trigger temperature protection.





# Electrical Characteristics (@TA = +25°C, unless otherwise specified.)


Symbol	Parameter	Condition	Min	Тур	Max	Unit
UVLO	<b>i</b>				•	
VTH (ST)	Startup Voltage	_	—	14.5	—	V
VOPR (MIN)	Minimal Operating Voltage	After Turn On	_	8.5	—	V
Vcc_clamp	Vcc Clamp Voltage	Icc = 1mA	14	15.5	—	V
Standby Current	<b>I</b>					
Ist	Startup Current	Vcc = VTH (ST)-0.5V Before Startup	—	100	_	μA
ICC (OPR)	Operating Current	Switching Frequency at		210	-	μA
Source Driver						
Rds(on)_LV	R <sub>DS(ON)_LV</sub> Internal Low Voltage MOSFET On- State Resistance (Note 7)			1	_	Ω
High Voltage and Super	-Junction MOSFET	•				
RDS(ON)_HV	Drain-Source On-State Resistance	-		8.8	10.5	Ω
VDS	Drain-Source Breakdown Voltage	-	700	_		V
I <sub>DSS</sub>	Drain-Source Leakage Current	-	_		1	μA
RT					Ť	
Vrt_ref	Reference Voltage of RT pin	-	_	0.5	—	V
Current Sense			Co			
V <sub>CS_CLAMP</sub>	CS Clamp Voltage	- /		1.6	_	V
Vref	Internal Current Loop Control Reference	+	0.388	0.4	0.412	V
ton_min	Minimum toN		—	550	—	ns
ton_max	Maximum toN	$R_{T} = 51k\Omega$ $V_{COMP} = 4V$	_	5.4	_	μs
toff_min	Minimum toff (Note 7)	-		4	—	μs
toff_max	Maximum toff	-	—	290		μs
FB						
V <sub>FB</sub>	Feedback Voltage	_	3.7	3.95	4.18	V
lfв	Feedback Pin Input Leakage Current	VFB = 2V	—	4	—	μA
Error Amplifier						
G <sub>M</sub>	G <sub>M</sub> Trans-Conductance	—	_	25	_	μA/V
ISOURCE	Amplifier Source Current	Vcs = 0V	—	10		μA
Isink	Amplifier Sink Current	Vcs = 1.5V	_	28		μA
Thermal Foldback and (	Over Temperature Protection (OTP)		•	•		
TFOLD	Thermal Foldback (Note 7)	_	_	+145	_	°C
	Thermal Shutdown (Notes 7 & 8)	<b>_</b>	_	+160	_	°C

Notes:

7. These parameters, although guaranteed by design, are not tested in production.8. The device will latch off when OTP happens, recovered after power cycle and the device won't operate normally at this temperature.



# Performance Characteristics (Note 9)



Minimum Operating Voltage Vs. Ambient Temperature

9. These electrical characteristics are tested under DC condition. The ambient temperature is equal to the junction temperature of the device. Note:



# **Functional Description and Application Information**

### Operation

The AL1692-10E is a single stage, single winding, high efficiency, and high power factor dimmable LED driver for triac dimmable LED lamp applications. The AL1692-10E integrates a 700V/1A high voltage MOSFET, and it can cover both 120Vac and 230Vac triac dimmable applications with eliminating external high voltage MOSFET and Varistor.

The AL1692-10E adopts source-driver technique to decrease the system operating current. It uses a novel method to detect the toFF time which results in the removal for the need of an auxiliary winding. The AL1692-10E operates at boundary conduction mode (BCM) which can ease EMI design and achieve high efficiency. High power factor (HPF) is achieved by using constant on-time mode. Coupled with a closed loop of constant current control, the AL1692-10E achieves good line and load regulation.

### Start-up and Supply Voltage

Before start-up, the Vcc capacitor C4 is charged by the startup resistors (R2, R3) from the high voltage mains. When the start-up voltage is reached, the AL1692-10E starts switching. During normal operation, the Vcc supply is provided by start-up resisters (R2, R3) and the output voltage (Vout) rectified by one diode (D2). In this way the system can provide Vcc supply at low dimming angle.

The AL1692-10E has an internal VCC clamp voltage (typical 15.5V), which is limited by one internal active Zener diode.

When VCC voltage drops to below the VOPR(MIN), switching is stopped. So the device can operate normally when the voltage on VCC pin is between VOPR(MIN) and VCC clamp voltage.

### Protections

#### Under Voltage Lockout (UVLO)

When the voltage on the VCC pin drops to below V<sub>OPR(Min)</sub>, the IC stops switching. The IC can restart when the voltage on VCC exceeds the startup voltage (V<sub>TH(ST)</sub>).

### Leading-Edge Blanking (LEB)

To prevent false detection of the peak current of the inductor, a blanking time following switch-on is designed. When the internal switch turns on, a short current spike can occur because of the capacitive discharge of the voltage over the drain and source. It is disregarded during the LEB time (ton\_MIN).

### Cycle-by-Cycle Over Current Protection (OCP)

The AL1692-10E has a built-in peak current detector. It is triggered when the voltage on CS pin reaches the peak level V<sub>CS\_CLAMP</sub>. The R5 is connected to the CS pin to sense the current of the inductor. The maximum peak current (IPEAK(MAX)) of the inductor can be calculated as below:

$$I_{PEAK(MAX)} = \frac{V_{CS\_CLAMP}}{R5}$$

The detection circuit is activated after the LEB time. When the detection circuit senses the CS voltage is higher than 1V, the IC will turn off the switching to limit the output current. It automatically provides protection for the maximum LED current during operation. A propagation delay exists between over current detection and actual source-switch off, so the actual peak current is a little higher than the OCP level set by the R5.

.....(1)

### Over-Voltage Protection and Output-Open Protection (OVP)

The output voltage is sensed by the FB pin, which provides an over-voltage protection (OVP) function. When the output is open or large transient happens, the output voltage will exceed the rated value (R8, R9). When the voltage exceeds VFB, the over-voltage is triggered and the IC will discharge Vcc. When the Vcc is below the UVLO threshold voltage, IC will restart and the Vcc capacitor is charged again by start-up resistance. If the over voltage condition still exists, the system will work in hiccup mode.

### **Output-Short Protection (OSP)**

When LED is shorted, the device cannot detect the toFF time, and the device controls the system operation at 4kHz low frequency.




## Functional Description and Application Information (continued)

#### Thermal Foldback Protection (TFP)

The AL1692-10E has a thermal foldback protection (TFP) function and adopts self-adaptive control method, which can prevent the system from breaking down caused by high temperature. The overheating temperature is set at +145°C typical. When the junction temperature of the IC is higher than +145°C typical, the device will linearly decrease the internal reference voltage to decrease the output current. As a result of this feature, the device can control the system's output power at high ambient temperature, to control the quantity of heat of the system. This enhances the safety of the system at high temperature.

Thermal foldback waveform is shown below:



#### **Over-Temperature Protection (OTP)**

The AL1692-10E has over temperature protection (OTP) function. When the junction temperature reach to +160°C typical, the IC will trigger an over-temperature protection, which causes the device to shut down and latched condition. Once OTP is triggered, the system needs to be resumed after the system's AC source supply has been reset and powered up.

### **Design Parameters**

#### Setting the Current Sense Resistor R5

The AL1692-10E adopts boundary conduction mode, the output current is calculated as below,

$$I_{O\_MEAN} = \frac{1}{\pi} \cdot \int_{0}^{\pi} \frac{1}{2} \cdot I_{PEAK} \cdot \frac{t_{OFF}}{t_{ON} + t_{OFF} + t_{DELAY}} dt$$

Where,

IPEAK is the peak current of the inductance ton is the internal MOSFET on time toff is the freewheel diode D1 conduction time t\_DELAY is typical  $0.4\mu s$ 

The AL1692-10E is a closed loop constant current control with the relationship between output current and current sense voltage follows this equation

$$V_{REF} = \frac{1}{\pi} \cdot \int_{0}^{\pi} I_{PEAK} \cdot \mathbf{R5} \cdot \frac{t_{OFF}}{t_{ON} + t_{OFF} + t_{DELAY}} dt$$

Where,

VREF is the internal reference, typical 0.4V.

R5 is the current sense resistor

So we can get the output current equation as below,

$$I_{O_{MEAN}} = \frac{1}{2} \cdot \frac{V_{REF}}{R5}$$

AL1692-10E Document number: DS39670 Rev. 3 - 3 8 of 14 www.diodes.com



## Functional Description and Application Information (continued)

#### Inductance Selection (L2)

In buck-boost structure, the peak current of the inductance can be calculated as below

$$I_{PEAK} = \frac{\pi \cdot V_{REF}}{R5 \cdot \int_{0}^{\pi} \sin(\theta) \cdot \frac{\sqrt{2} \cdot V_{IN\_RMS} \cdot \sin(\theta)}{\sqrt{2} \cdot V_{IN\_RMS} \cdot \sin(\theta) + Vo} d\theta}$$

Where,

VIN\_RMS is the input voltage's RMS value

Vo is the system output voltage

The AL1692-10E controls the system operating at boundary conduction mode which results in its operating frequency not being constant. To set the minimum switching frequency f<sub>MIN</sub> at the crest of the minimum AC input.

$$L2 = \frac{\sqrt{2}V_{IN\_RMS} \cdot V_O}{I_{PEAK} \cdot (\sqrt{2}V_{IN\_RMS} + V_O) \cdot f_{MIN}}$$

According to the Faraday's Law, the winding number of the inductance can be calculated by

$$N_{L2} = \frac{L2 \cdot I_{PEAK}}{A_c \cdot B_m}$$

Where,

Ae is the core effective area.

B<sub>m</sub> is the maximum magnetic flux density.

### ton\_max Setting

In order to get a good dimmer compatibility and a good dimming depth, the device sets a  $t_{ON\_MAX}$  by one external resistor  $R_T$  (R6). And the  $t_{ON\_MAX}$  time has the below equation:

$$t_{ON\_MAX} = \frac{3.3 \cdot C_{REF}}{\frac{V_{RT\_REF}}{10 \cdot R6} + 0.33uA}$$

Where,

 $V_{RT\_REF}$  is the internal RT pin 0.5V's reference. CREF is the internal 1.5pF capacitor.

## **Dimming Control**

The AL1692-10E is a closed loop control device; the dimming function is realized by ton\_MAX limited when dimmer is connected in. When the dimmer is at the largest conduction angle, the device still has the adjustability to control the output current constant before COMP voltage is adjusted to the maximum 4V, so for most of the dimmer, the output current is almost the same with the no dimmer condition at the largest conduction angle. If the conduction angle is decreased, the COMP pin voltage will continue to increase quickly till to the maximum level (typical 4V), the device will output ton\_MAX to limit system's output current. The ton\_MAX is set by RT pin connected with one resistor, so the dimming depth can be adjusted by RT resistor (R6).

Before the AL1692-10E enters ton\_MAX mode, it keeps the output current constant the same as no dimmer condition. When it enters ton\_MAX mode, we can get the following equation:


$$I_{PEAK\_DIM} = \frac{V_{IN\_RMS} \cdot Sin(\theta) \cdot t_{ON\_MAX}}{L2}$$



# Functional Description and Application Information (continued)

From the buck-boost output current equation, we can get the output current when dimming:

 $\alpha$  is the dimmer conduction angle.



### **Dimmer Compatibility**

### **Passive Bleeder Design**

The passive bleeder is designed to supply latching and holding current to eliminate dimmer misfire and flicker.




Figure 3. LED Driver Schematic with Passive Bleeder


The passive bleeder includes a capacitor (C2, in hundreds of nF) to provide latching current. A resistor (R1) is necessary to dampen the current spike. Because a large C2 will affect the PF, THD and efficiency, the value of the capacitor (C2) should be selected accordingly. Generally, 100nF/400V to 330nF/400V is recommended. R1 is used to limit the latching current. If R1 is too large, the latching current is not enough and the TRIAC dimmer will misfire causing LED flicker. If R1 is too small, it will result in greater power dissipation. Generally speaking, a 200Ω to 2kΩ resistor is selected for R1.

### **Passive Damping Design**

FR1 is the damper for reducing the spike current caused by quick charging of C2 at firing. In general, FR1 is selected from 20Ω to 100Ω for low line like 120V<sub>AC</sub> application, and 51 $\Omega$  to 200 $\Omega$  for high line like 230V<sub>AC</sub> application.



# Ordering Information






# Package Outline Dimensions (All dimensions in mm.)

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### Package Type: SO-7






# Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

### Package Type: SO-7



Dimensions	Z	G	X	Y	E	E1
	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)
Value	6.900/0.272	3.900/0.154	0.650/0.026	1.500/0.059	1.270/0.050	2.540/0.100





#### IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<u>https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/</u>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at <a href="https://www.diodes.com/about/company/terms-and-conditions/important-notice">https://www.diodes.com/about/company/terms-and-conditions/important-notice</a>

DIODES is a trademark of Diodes Incorporated in the United States and other countries. The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. © 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com