

SOT223 NPN SILICON PLANAR HIGH VOLTAGE TRANSISTOR

BFN36

ISSUE 4 - JANUARY 1996 

FEATURES:


- * High V_{CE0} and Low saturation voltage

APPLICATIONS:

- * Suitable for video output stages in TV sets
- * Switching power supplies

COMPLEMENTARY TYPE - BFN37

PARTMARKING DETAILS - BFN36



ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	VALUE	UNIT
Collector-Base Voltage	V_{CBO}	250	V
Collector-Emitter Voltage	V_{CEO}	250	V
Emitter-Base Voltage	V_{EBO}	5	V
Continuous Collector Current	I_C	500	mA
Power Dissipation at $T_{amb}=25^{\circ}C$	P_{tot}	2	W
Operating and Storage Temperature Range	$T_j; T_{stg}$	-55 to +150	$^{\circ}C$

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}C$).

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	CONDITIONS.
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	250			V	$I_C=100\mu A$
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	250			V	$I_C=1mA$
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	5			V	$I_E=100\mu A$
Collector Cut-Off Current	I_{CBO}			100 20	nA μA	$V_{CB}=200V$ $V_{CB}=200V, T_{amb}=150^{\circ}C$
Emitter Cut-Off Current	I_{EBO}			100	nA	$V_{EB}=4V$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$			0.4	V	$I_C=20mA, I_B=2mA$
Base-Emitter Saturation Voltage	$V_{BE(sat)}$			0.9	V	$I_C=20mA, I_B=2mA$
Static Forward Current Transfer Ratio	h_{FE}	25 40 40				$I_C=1mA, V_{CE}=10V^*$ $I_C=10mA, V_{CE}=10V^*$ $I_C=30mA, V_{CE}=10V^*$
Transition Frequency	f_T		70		MHz	$I_C=20mA, V_{CE}=10V$ $f=100MHz$
Output Capacitance	Cobo		1.5		pF	$V_{CB}=30V, f=1MHz$

*Measured under pulsed conditions. Pulse width=300 μs . Duty cycle $\leq 2\%$

For typical characteristics graphs see FMMTA42 datasheet.