

## LEDO001 USER GUIDE

### Performance

- Typical color temperature – 6500K
- Viewing angle - 120°
- Maximum drive current – 500mA
- Maximum junction Temperature – 125°C
- Optical Efficiency – 40 lm/W

### Ordering Information

Order Number
LEDO001

### Description

This demonstration circuit consists of a simple connectable printed circuit board carrying an LED, a thermistor and switching links. It allows the evaluation and testing of attachable Zetex LED driver circuits with varying numbers of series connected LEDs.

The PCB construction is a single layer of printed copper. There is a solid aluminium backing for heat dissipation. The material used is Aismalibar Cobritherm™<sup>[1]</sup> or similar, 1.5mm Al, 110µm dielectric and 35µm copper. It features 4 holes for M2.5 fixings if required.

The board is fitted with a male 6-pin input connector. This mates with any of the Diodes Zetex Evaluation boards which are fitted with a suitable socket. At the opposite end, a female connector is fitted, to allow multiple LED extensions as shown in the schematic below.


A jumper link is used to allow connection of the LED as the NEXT or LAST in the chain. A further jumper link is provided to select whether the thermistor on the board is connected (position TH), or whether the connection is passed to a board further down the chain (PASSTH).

The LEDO001 is fitted with the Osram LWW5SM LED:


<http://catalog.osram-os.com>



## Schematic



## PCB Layout



## USAGE

There are two circuits on the board:  
The LED circuit and the thermistor circuit.

The input (PL1) and output (SK1) connector pins 1+2 and 5+6 are used for the LED, and 4 and 5 are used for the thermistor.

### LED circuit

If only one LED board is being used, or is the last in a chain of several boards, the jumper JP1 should be inserted in the 'LAST' position. This connects the LED directly across pins 1+2 and 5+6 of input connector PL1.

If several boards are being used in a chain, and the board concerned is not in the last position, the jumper JP1 should be inserted in the 'NEXT' position. This connects the LED in series between pins 5+6 on the input connector PL1 and pins 5+6 on the output connector SK1.

It is not possible to configure the board for multiple LEDs in parallel.

### Thermistor circuit

In cases where the thermistor is not required, the position of JP2 is irrelevant but it should be removed if any other connections are made to pins 4 and 5 of PL1 or SK1.

If the thermistor is required, and only one LED board is being used, the jumper JP2 should be inserted in the 'TH' position. This connects the thermistor directly across pins 3 and 4 of the input connector PL1, thus making the thermistor 'active'.

If several boards are being used in a chain, the board on which the thermistor is required to be active should be set with JP2 in the 'TH' position. All the other boards should be set with JP2 in the 'THPASS' position. This disconnects the other thermistors and creates a direct link between pin 4 on the input connector PL1 and pin 4 on the output connector SK1. It is not possible to configure the board for multiple thermistors in parallel.

### Parts List

Count	Designator	Description	Package	Manufacturer	Part Number
1	D1	Osram LWW5SG LED	SMD	Osram	LWW5SM
1	R1	10k $\Omega$ Thermistor	0805	Vishay	2381 615
2	JP1, JP2	3- way headers for links		Samtec	TSM-103-02-L-SV

### Input/ Output

Count	Designator	Description	Function	Manufacturer	Part Number
1	PL1	6 pin Input power connector (male) Horizontal header	Connection to LED driver or to previous LED demonstration board in series	Samtec	TSM-106-03-L-SH
1	SK1	Output connector (female)	Allows connection for new demonstration board to be added in series	Samtec	SSM-106-L-SH

### Recommended Operating Conditions

Symbol	Parameter	Min	Max	Units
$V_F$	Forward Voltage at $I_F = 350\text{mA}$	2.7	3.8	V
$I_F$	Forward current at $T_A = 25^\circ\text{C}$	100	500	mA

<sup>[1]</sup> Cobritherm is a trademark of the Aismalibar Corporation

### IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channels.

Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably be expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2009, Diodes Incorporated

[www.diodes.com](http://www.diodes.com)

### Sales offices

#### The Americas

3050 E. Hillcrest Drive  
Westlake Village,  
CA 91362-3154  
Tel: (+1) 805 446 4800  
Fax: (+1) 805 446 4850

#### Europe

Kustermannpark  
Balanstraße 59,  
D-81541 München  
Germany  
Tel: (+49) 894 549 490  
Fax: (+49) 894 549 4949

#### Taiwan

7F, No. 50,  
Min Chuan Road  
Hsin-Tien  
Taipei, Taiwan  
Tel: (+886) 289 146 000  
Fax: (+886) 289 146 639

#### Shanghai

Rm. 606, No.1158  
Changning Road  
Shanghai, China  
Tel: (+86) 215 241 4882  
Fax (+86) 215 241 4891

#### Shenzhen

Room A1103-04,  
ANLIAN Plaza, #4018  
Jintian Road  
Futian CBD,  
Shenzhen, China  
Tel: (+86) 755 882 849 88  
Fax: (+86) 755 882 849 99

#### Korea

6 Floor, Changhwa B/D,  
1005-5 Yeongtong-dong,  
Yeongtong-gu, Suwon-si,  
Gyeonggi-do, Korea 443-813  
Tel: (+82) 312 731 884  
Fax: (+82) 312 731 885