ZXCT1011EV1 USER GUIDE

DESCRIPTION

The ZXCT1011EV1 is a current monitor evaluation board which measures 0.5A, 2.0A or a 2.5A load current. This current is then translated to a proportional output current which is scaled by an external resistor to give a 2.5V full scale output voltage.

A current reference resistor, external to the IC, results in a low temperature coefficient.

FEATURES

- Supply Range 2.5 to 20V
- Selectable current measurement range
- 2.5V Output Voltage
- SOT23-5 package
- Low Temperature Coefficient

ORDERING INFORMATION

ORDER NUMBER	
ZXCT1011EV1	

Please note evaluation boards are subject to availability and qualified leads

PAD NAMES AND DEFINITIONS

NAME	DESCRIPTION
VIN	Supply Voltage
VLOAD	Connection to load/Battery
VOUT	Output Voltage
GND	0V – Ground
SL6,SL7	Solder Links

The board also incorporates additional solder pads for a user defined sense resistor to cater for additional load currents which may require measuring.

APPLICATIONS

- Battery Charging
- Power Supplies
- DC motor and solenoid control

TYPICAL APPLICATION CIRCUIT



REFERENCE DESIGN

The ZXCT1011EV1 is configured to the schematic diagram in figure 1.0. The target applications are battery chargers, power supply units and automotive current monitoring.

The input voltage range for the ZXCT1011EV1 is 20V down to a minimum of 2.5V, making in suitable for a wide range of applications.

The ZXCT1011 IC ultilises an external reference resistor which gives the ZXCT1011 a low temperature coefficient.

<u>Rsense</u>

The board has been designed with three set selectable values of Rsense, to measure either a 0.5A, 2.0A or 2.5A range. The value of sense resistor can be chosen by using the solder links SL6 and SL7.

To measure a 0.5A load current, the $200m\Omega$ resistor (R3) should be selected by shorting SL7. To measure a 2.0A current, the $50m\Omega$ resistor (R2) should be selected by shorting SL6. To measure a 2.5A current, short both SL6 and SL7. The $50m\Omega$ in parallel with the $200m\Omega$ will give a $40m\Omega$ resistance. RST is also available if a user defined current load level is required to be measured. This allows the user to scale in a more appropriate value of sense resistor. If the value of sense resistor is changed, the maximum power dissipation of the resistor must be appropriate to the load current level.

NB The board is set by default to measure 0.5A i.e. SL7 is shorted, utilizing the 200m Ω resistor.

For further information on choosing a value of sense resistor please refer to the ZXCT1011 datasheet.

Vout

If the preset selectable values of sense resistor are chosen, the device will output 2.5V at both the 0.5A and 2.0A current levels. The board has been designed for each of the sense resistors to develop 100mV across them at the three levels of current.

Configuration table for ZXCT1011EV1

LOAD CURRENT (A)	R _{sense} (mΩ)	VOUT (V)	SOLDER LINK CONFIGURATION
0.5	200	2.5	Short SL7
2.0	50	2.5	Short SL6
2.5	40	2.5	Short SL7 and SL6

Configuration for different LOAD currents.

The board can be configured to accommodate different load currents if necessary. If surface mount sense resistors are to be used, remove R2 an R3 and replace with a required value. RST can be used if a through hole sense resistor is used. It is important to ensure an appropriate value of R_{sense} is selected to obtain the desired accuracy for a given output current.

NB Changing the sense resistor value will change the output current. It may therefore be necessary to change R5 to obtain the required output voltage.

The following lines describe how to scale a load current to an output voltage.

	$V_{sense} = (V_{sense+}) - (V_{sense-}) = I_{load} \times R_{sense}$
Defining then	$I_{out} = Iq + V_{sense} \times g_m$
since	g _m = 1.2 / R _{shunt}
	$I_{out} = Iq + [(V_{sense} \times 1.2) / R_{shunt}]$
	= Iq + [(1.2 x I _{load} x R _{sense} / R _{shunt})]

Note: Iq is embedded into the specification of the ZXCT1011 and therefore appears an offset error.

:. Vout = (Rout x Ioffset) + [(1.2 x Rout x Iload x Rsense) / Rshunt]

The output current of the ZXCT1011 is directly related to the size of the trimming resistor used. It is important to ensure the tolerance of R_{shunt} is considered. A 1% change in R_{shunt} will cause a 1% change in output.

Example: Scaling for 1.5A load current and a 500mV output.

Choose a value of R_{shunt} to give a required transconductance; using a 120 Ω resistor will give 10mA/V.

Choose a value of sense resistor to accommodate the required accuracy on the output.

A 150mV drop across the sense resistor will require a $100m\Omega$ sense resistor.

$V_{out} = g_m \times V_{sense} \times R_{out}$

Where $g_m = 1.2/R_{shunt}$ $g_m = transconductance (S)$

Therefore, the required output resistor for a 500mV output for $R_{shunt} = 120\Omega$ will be:

 $R_{out} = 500 \times 10^{-3} / (150 \times 10^{-3} \times 0.01) = 333.33 \Omega$

Nearest preferred value: 332Ω

Accuracy

The ZXCT1011 current monitor IC is a 2.5%¹ accurate device. The accuracy of the output voltage will be influenced by the tolerance of the external resistors used. The ZXCT1011EV1 uses a 1% accurate sense resistor and a 0.1% accurate output resistors.

¹ Maximum error at 200mV



Figure 1.0 Schematic Diagram (default configuration with SL7 shorted and SL6 open)

Materials List

Ref	Value	Package	Part Number	Manufacturer	Notes
R1	120Ω	0805		Panasonic	SMD ±25ppm 1%
R2	50mΩ	1206	LR1206	Welwyn	SMD Sense Resistor 1%
R3	200mΩ	1206	LR1206	Welwyn	SMD Sense Resistor 1%
R4	0Ω	0805			Zero ohm link
R5	2.49k	0805			SMD ±25ppm 0.1%
ZXCT		SOT23	ZXCT1011E5	ZETEX	

ZXCT1011EV1

Set-up and Test

The board is preset to measure 0.5A. SL7 is shorted to connect in the $200m\Omega$ sense resistor. To change the board to measure 2.0A, de-solder SL7 and short SL6.

0.5 Ampere load test

- 1. Ensure SL7 is shorted.
- 2. Connect a linear power supply of +10V between the VIN and GND terminals.
- 3. Set a load current of 0.5A.
- 4. Turn on the power supply
- 5. Check with a DVM the supply voltage is +10V between the VIN and GND terminals.
- 6. Measure VOUT with a DVM. The nominal output voltage should read 2.5V.

ZXCT1011EV1 ISSUE 2 – September 2005 The output current can be set by using either an external power resistor or an electronic load. The accuracy of the current set will have an influence on the output voltage.

Connection Diagram



The ZXCT1009EV1 board can also be used to evaluate the following Zetex current monitors IC's:

- ZXCT1008
- ZXCT1009

Layout

•

EVALUATION BOARD		
	RST	
VIN GND	R3	
	GND	
Bare ncb: 7DB237B2	Convright/Zelex PI C2005	

Top Silk



Bottom Copper



Top Copper



Drill File

ZXCT1011EV1 ISSUE 2 – September 2005

ZXCT1011EV1



Zetex plc. Fields New Road, Chadderton, Oldham, OL9 8NP, United Kingdom Telephone: (44) 161 622 4422 (Sales), (44) 161 622 4444 (General Enquiries) Fax: (44) 161 622 442

Zetex GmbH Streitfieldstraβe 19 D-81673 Munchen Germany Telefon: (49) 89 45 49 49 0 Fax: (49) 89 45 49 49 49 Zetex Inc. 47 Mall Drive, Unit 4 Commack NY 11725 USA Telephone: (631) 543-7100 Fax: (631) 864-7630 Zetex (Asia) Ltd. 3701-04 Metroplaza, Tower 1 Hing Fong Road, Kwai Fong, Hong Kong Telephone: (852) 26100 611 Fax: (852) 24250 494 These are supported by agents and distributoRS in major countries world-wide © Zetex plc 2000

http://www.zetex.com

This publication is issued to provide outline information only which (unless agreed by the company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contact or be regarded as a representation relating to the products or services concerned. The company reserves the right to alter without notice the specification, design, price or conditions of supply of any product or service.

ZXCT1011EV1 ISSUE 2 – September 2005