

## 7A SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER POWERMITE®3


### Features

- Guard Ring Die Construction for Transient Protection
- Low Power Loss, High Efficiency
- High Surge Capability
- Low Reverse Current
- For Use in Low Voltage, High Frequency Inverters, Free Wheeling, and Polarity Protection Applications

NOT RECOMMENDED FOR NEW DESIGNS

### Mechanical Data

- Case: POWERMITE®3
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture sensitivity: Level 1 per J-STD-020C
- Terminals: Solderable per MIL-STD-202, Method 208
- Polarity: See Diagram
- Marking: Type Number
- Weight: 0.072 grams (approximate)



POWERMITE®3		
Dim	Min	Max
A	4.03	4.09
B	6.40	6.61
C	.889 NOM	
D	1.83 NOM	
E	1.10	1.14
G	.178 NOM	
H	5.01	5.17
J	4.37	4.43
K	.178 NOM	
L	.71	.77
M	.36	.46
P	1.73	1.83
All Dimensions in mm		

Note: Pins 1 & 2 must be electrically connected at the printed circuit board.

### Maximum Ratings @ T<sub>A</sub> = 25°C unless otherwise specified

Single phase, half wave, 60Hz, resistive or inductive load.  
For capacitive load, derate current by 20%.

Characteristic	Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V <sub>RRM</sub> V <sub>RWM</sub> V <sub>R</sub>	60	V
RMS Reverse Voltage	V <sub>R(RMS)</sub>	42	V
Average Rectified Output Current (See also figure 4)	I <sub>O</sub>	7	A
Non-Repetitive Peak Forward Surge Current 8.3ms Single half sine-wave Superimposed on Rated Load @ T <sub>C</sub> = 55°C	I <sub>FSM</sub>	100	A
Typical Thermal Resistance Junction to Soldering Point	R <sub>θJS</sub>	2.5	°C/W
Operating Temperature Range	T <sub>J</sub>	-65 to +125	°C
Storage Temperature Range	T <sub>STG</sub>	-65 to +150	°C

### Electrical Characteristics @ T<sub>A</sub> = 25°C unless otherwise specified

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Breakdown Voltage (Note 1)	V <sub>(BR)R</sub>	60	—	—	V	I <sub>R</sub> = 0.5mA
Forward Voltage	V <sub>F</sub>	—	0.49 0.38 0.57 0.46	0.52 — 0.60 —	V	I <sub>F</sub> = 3.5A, T <sub>j</sub> = 25°C I <sub>F</sub> = 3.5A, T <sub>j</sub> = 125°C I <sub>F</sub> = 7A, T <sub>j</sub> = 25°C I <sub>F</sub> = 7A, T <sub>j</sub> = 125°C
Reverse Current (Note 1)	I <sub>R</sub>	—	5 10	200 20	μA mA	T <sub>j</sub> = 25°C, V <sub>R</sub> = 60V T <sub>j</sub> = 125°C, V <sub>R</sub> = 60V
Total Capacitance	C <sub>T</sub>	—	375	—	pF	f = 1.0MHz, V <sub>R</sub> = 4.0V DC

Notes: 1. Short duration test pulse used to minimize self-heating effect.




Fig. 1 Typical Forward Characteristics




Fig. 2 Typical Reverse Characteristics






Fig. 3 Typical Total Capacitance vs. Reverse Voltage




**Ordering Information** (Note 7)

Device	Packaging	Shipping
MBRM760-13	POWERMITE®3	5000/Tape & Reel

- Notes:
- $T_A = T_{SOLDERING\ POINT}$ ,  $R_{\theta JS} = 2.5^\circ C/W$ ,  $R_{\theta SA} = 0^\circ C/W$ .
  - Device mounted on GETEK substrate, 2"x2", 2 oz. copper, double-sided, cathode pad dimensions 0.75" x 1.0", anode pad dimensions 0.25" x 1.0".  $R_{\theta JA}$  in range of 25-30°C/W.
  - Device mounted on FR-4 substrate, 2"x2", 2 oz. copper, single-sided, pad layout as per Diodes Inc. suggested pad layout document AP02001 which can be found on our website at <http://www.diodes.com/datasheets/ap02001.pdf>.  $R_{\theta JA}$  in range of 85-90°C/W.
  - Maximum power dissipation when the device is mounted in accordance to the conditions described in Note 4.
  - Maximum power dissipation when the device is mounted in accordance to the conditions described in Note 3.
  - For Packaging Details, go to our website at <http://www.diodes.com/datasheets/ap02007.pdf>.

**Marking Information**



MBRM760 = Product type marking code  
 DII = Manufacturers' code marking  
 YYWW = Date code marking  
 YY = Last digit of year ex: 02 for 2002  
 WW = Week code 01 to 52  
 (K) = Factory Designator

**NOT RECOMMENDED FOR NEW DESIGNS**