

General Description

The DIODES AL8862Q is a step-down DC-DC converter designed to drive LEDs with a constant current. The AL8862Q operates with an input supply voltage from 5V to 55V and provides an externally adjustable output current up to 1A. Series connection of the LEDs provides identical LED currents resulting in uniform brightness and eliminating the need for ballast resistors. The AL8862Q switches at frequencies up to 1MHz. This allows for the use of smaller size external components, hence minimizing the PCB size.

The AL8862Q integrates the power switch and a high-side output current sensing circuit. The maximum output current of AL8862Q is set via an external resistor connected between the VIN and SET input pins. Dimming is achieved by applying either a DC voltage or a PWM signal at the CTRL input pin. The softstart time can be adjusted using an external capacitor from the CTRL pin to the ground. An input voltage of 0.3V or lower at CTRL pin will shut down the power switch.

The AL8862Q is qualified to AEC-Q100 Grade 1 and is automotive grade to support PPAPs.

Applications

- Automotive interior LED lamps
- Automotive exterior LED lamps

Key Features

- 2.0V to 60V Wide Input Voltage Range
- Wide Input Voltage Range: 5V to 55V
- Output Current up to 1A
- Internal 55V NDMOS Switch
- Typical 4% Output Current Accuracy
- Single Pin for On/Off and Brightness Control by DC Voltage or
- PWM Signal
- High Efficiency (Up to 97%)
- Fault Status Indication for Abnormal Operation
- LED Short-Circuit Protection
- Inherent Open-Circuit LED Protection
- Current-Sense Resistor Short-Circuit
 Protection
- Overtemperature Shutdown
- Up to 1MHz Switching Frequency
- SO-8EP Package Available in Green Molding Compound (No Br, Sb)

AL8862QEV2 Specifications


Parameter	Value
Input Voltage	9VDC to 16VDC
LED Current	1A
Number of LEDs	1~3 pcs
XY Dimension	68mm x 46mm



EVB Physical Picture



Figure 1. Top View





Connection Instructions and Quick Start Guide

- 1. Connect LED string anode end to "LEDA" and connect LED string cathode end to "LEDK".
- 2. Power Supply Input: 4.5~16VDC, connect two DC line wires to the BAR+ and BAR-terminals on the evaluation board. It's better to set at least 3V voltage gap between input and output.
- 3. For PWM dimming operation: supply a 0-3.3V 200Hz~2 kHz signal between DIM & GND.
- 4. The LED current of demonstration board is preset at 1A.
- 5. Ensure that the DC source is switched OFF or disconnected before soldering or connecting.
- 6. Ensure that the area around the board is clear and safe, and preferably that the board and LEDs are enclosed in a transparent safety cover.
- 7. Turn on the main switch. LED string should light up.



Evaluation Board Schematic




Figure 3. Evaluation Board Schematic

Evaluation Board Layout




Figure 4. PCB Top Layer




Figure 5. PCB Bottom Layer




Bill of Material


Location	Description	Package			
R2	Resistor, SMT, 0 ohm, 0603, 5%				
R3	Resistor, SMT, 51K ohm, 0805, 5%				
R4,R5	Resistor, SMT, 0.2 ohm, 1206, 1%				
R1,R6	Resistor, SMT, 20 ohm, 0805, 5%				
C2,C3,C5,C6	Cap, Cer, GCJ32DC72A475KE01L, 4.7uF, 100V, X7S, 1210, -55°C~125°C, AEC-Q200, Murata				
C1,C4,C7,C9	Cap, Cer, CGA4J2X7R2A104K125AA, 100nF,100V,X7R, 0805,-55°C~125°C, AEC-Q200,TDK				
C15,C16	Cap, Cer, CGA3E2X7R2A103K080AA, 10nF, 100V, X7R, 0603, -55°C~125°C, AEC-Q200, TDK				
C17,C18	Cap, Cer, CGA3E2X7R2A102K080AA, 1nF, 100V, X7R, 0603, -55°C~125°C, AEC-Q200, TDK	0603			
C10,C11	Cap, Cer, CL21C681JCC1PNC, 680pF, 100V, NP0, 0805, -55°C~125°C, AEC-Q200, Samsung	0805			
C12,C13	Cap, Cer, CGA4J3X7R1H105K125AB, 1uF, 50V, X7R, 0805, -55°C~125°C, AEC-Q200, TDK	0805			
C14,C20	Cap, Cer, CGA4J2X8R1H104K125AA, 100nF, 50V, X8R, 0805, -55°C~150°C, AEC-Q200, TDK	0805			
C19	Cap, Cer, GCD188R71H102KA01D, 1nF, 50V, X7R, 0603, -55°C~125°C, AEC-Q200, Murata	0603			
U1	IC, AL8862QSP-13, AEC-Q100 Qualified, DIODES,	SO-8EP			
B1,B2,B3,B4	78279221601, 600ohm@100MHz, AEC-Q200, Würth Elektronik	1206			
L1	744778004, 4.7uH, Isat=4.2A, 7.3x7.3x2.8mm, AEC-Q200, Würth Elektronik	SMT			
L2	744373965150,15uH, Isat=10.2A, 13.65x12.5x6.2mm, AEC-Q200, Würth Elektronik	SMT			
D2,D3	Diode, SBR8M100P5Q-13,8A,100V, AEC-Q101 Qualified, DIODES	POWER DI5			
DIM, FAULT,GND	Connector, Orange color	DIP			
LEDK	Connector, Black color	DIP			
BAR-	Connector, White color	DIP			
LEDA, BAR+	Connector, Red color	DIP			



System Performance




PWM Dimming Curve Test @VIN=12V, LED voltage=5.3V





Waveforms:






Figure 6. Startup @ Output =1 LED

Turn OFF:




Figure 8. Turn off @Output =1 LED







Figure 9. Turn off @Output =3 LEDs





PWM Dimming Waveforms, PWM duty =50%





Figure 12. Output =1 LED



Thermal Test:




IC Tc = 48.8C degree @ ambient = 23C degree, temperature rise is 25.8C degree. Tested in VIN=13.5V, VLED=9.5V.



Conductive Emission Test:

Tested in VIN=13.5V, loading with 3pcs LED (Vo =9.5V)



Frequency	MaxPeak	Average	Limit	Margin	MeasTime	Bandwidth	Line	Corr.
MHz	dBµV	dBµV	dBµV	dB	ms	kHz		dB
5.95		35.38	45.00	9.62			Single Line	0.1
5.955	37.50		65.00	27.50			Single Line	0.1
31.800		23.56	36.00	12.44			Single Line	0.2
53.000	26.50		46.00	19.50			Single Line	0.2
75.800		23.68	29.98	6.30			Single Line	0.4
75.800	29.09		46.00	16.91			Single Line	0.4



IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<u>https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/</u>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatso ever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com