

PACKAGE INFORMATION

SOT363

Mechanical Data

- Surface Mount Package
- Case Material: Molded Plastic, UL Flammability Classification Rating 94V-0
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 3
- Weight: 0.006 grams (Approximate)
- Max Soldering Temperature +260°C for 30 secs as per JEDEC J-STD-020


Package Outline Dimensions


Package View

SOT363




Top View





SOT363						
Dim	Min	Max	Тур			
A1	0.00	0.10	0.05			
A2	0.90	1.00	0.95			
b	0.10	0.30	0.25			
С	0.10	0.22	0.11			
D	1.80	2.20	2.15			
Е	2.00	2.20	2.10			
E1	1.15	1.35	1.30			
е	0.650 BSC					
F	0.40	0.45	0.425			
L	0.25	0.40	0.30			
а	a 0°					
All Dimensions in mm						

Suggested Pad Layout



Dimensions	Value (in mm)		
С	0.650		
G	1.300		
Х	0.420		
Y	0.600		
Y1	2.500		

Note: The suggested land pattern dimensions have been provided for reference only, as actual pad layouts may vary depending on application. These dimensions may be modified based on user equipment capability or fabrication criteria. A more robust pattern may be desired for wave soldering and is calculated by adding 0.2 mm to the 'Z' dimension. For further information, please reference document IPC-7351A, Naming Convention for Standard SMT Land Patterns, and for International grid details, please see document IEC, Publication 97.

Note: For high voltage applications, the appropriate industry sector guidelines should be considered with regards to creepage and clearance distances between device Terminals and PCB tracking.



Minimum Packing Quantity


	Quantity	Tape Width	Part Number Suffix			
7" Reel	3,000	8mm	-7, -7R			
13" Reel	10,000	8mm	-13, -13R			
Inte: Package quantities given are for minimum packaging quantity only, not minimum order quanti						

Note: Package quantities given are for minimum packaging quantity only, not minimum order quantity. For minimum order quantity, please contact Sales Department.

Note: No mixed date codes or partial quantity (less than minimum packaging quantity) per packaging is allowed.

Note: In no case shall there be two or more consecutive components missing from any reel for any reason.


Device Tape Orientation




Note: Tape and package drawings are not to scale and are shown for device tape orientation only.




Embossed Carrier Tape Specifications



Tape Width (W)	Dimension	Value (mm)	Dimension	Value (mm)	Dimension	Value (mm)	
8mm	B1	4.5 max.	F	3.5±0.05	P2	2.0±0.05	
	D	1.5+0.10 -0.0	к	2.4 max.	t	0.40 max.	
	D1	0.35 min.	Р	4.0±0.10	w	8±0.30	
	E	1.75±0.10	P0	4.0±0.10			
	A0 B0 K0	Determined by component size. The clearance between the component and the cavity must comply to the rotational and lateral movement requirement provided in figures in the "Maximum Component Movement in Tape Pocket" section.					








Allowable camber to be 1mm/100mm tape, non-cumulative

R min. - 25mm

Bending radius of tape




Maximum Component Movement in Tape Pocket






Surface Mount Reel Specifications



* Drive spokes optional. If used, dimensions with asterisks apply.

Tape Width	Reel Size	A (mm)	B Max (mm)	C (mm)	D Max (mm)	N Min (mm)	G (mm)	T Max (mm)
8mm	7"	178 ±2	2.0 +0.5 -0	13 +0.5 -0.2	20.5 ±0.2	55 ±5	8.4 +1.5 -0.0	14.4
	13"	330 ±2	2.0 +0.5 -0	13 +0.5 -0.2	20.5 ±0.2	100 ±2	8.4 +1.5 -0.0	14.4

Tape Leader and Trailer Specifications



Note: There shall be a leader of at least 230mm which may consist of carrier tape and/or cover tape or a start tape followed by at least 160mm of empty carrier tape sealed with cover tape.

Note: There shall be a trailer of at least 160mm of empty carrier tape sealed with cover tape. The entire carrier tape must release from the reel hub as the last portion of the tape unwinds from the reel without damage to the carrier tape and the remaining components in the cavities.