

PACKAGE INFORMATION

Mechanical Data

- Surface Mount Package
- Case Material: Molded Plastic, UL Flammability Rating 94V-0
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208
- Weight: 0.059 grams (Approximate)
- Max Soldering Temperature +260°C for 30 secs as per JEDEC L-STD-020


Package View



Top View

Package Outline Dimensions


SOT89-5



SOT89-5						
Dim	Min	Max	Тур			
Α	1.40	1.60	1.50			
В	0.50	0.62	0.56			
B1	0.44	0.54	0.48			
С	0.35	0.43	0.38			
D	4.40	4.60	4.50			
D1	1.62	1.83	1.733			
Е	2.40	2.60	2.50			
е	-	-	1.50			
Н	3.95	4.25	4.10			
L	0.65	0.95	0.80			
All Dimensions in mm						

Suggested Pad Layout

SOT89-5



Dimensions	Value (in mm)
С	1.500
C1	1.050
Χ	0.680
X1	0.760
X2	1.930
Х3	3.680
Υ	1.200
Y1	1.200
Y2	4.250
Y3	4.500

Note:

The suggested land pattern dimensions have been provided for reference only, as actual pad layouts may vary depending on application. These dimensions may be modified based on user equipment capability or fabrication criteria. A more robust pattern may be desired for wave soldering and is calculated by adding 0.2 mm to the 'Z' dimension. For further information, please reference document IPC-7351A, Naming Convention for Standard SMT Land Patterns, and for International grid details, please see document IEC, Publication 97.

Note:

For high voltage applications, the appropriate industry sector guidelines should be considered with regards to creepage and clearance distances between device Terminals and PCB tracking.



Minimum Packing Quantity

	Quantity	Tape Width	Part Number Suffix	
13" Reel	2,500	12mm	-13	


Note: Package quantities given are for minimum packaging quantity only, not minimum order quantity. For minimum order quantity, please contact Sales

Department.

Note: No mixed date codes or partial quantity (less than minimum packaging quantity) per packaging is allowed.

Note: In no case shall there be two or more consecutive components missing from any reel for any reason.


Device Tape Orientation



Note: For part marking, refer to product datasheet.

Note: Tape and package drawings are not to scale and are shown for device tape orientation only.


Embossed Carrier Tape Specifications




Tape Width (W)	Dimension	Value (mm)	Dimension	Value (mm)	Dimension	Value (mm)	
	B1	8.2 max.	F	5.5±0.05	P2	2.0±0.05	
	D	1.5+0.10 -0.0	К	4.5 max.	t	0.40 max.	
12mm	D1	1.5 min.	Р	8.0±0.10	w	12±0.30	
1211111	E	1.75±0.10	P0	4.0±0.10			
	A0 B0 K0	Determined by component size. The clearance between the component and the cavity must comply to the rotational and lateral movement requirement provided in figures in the "Maximum Component Movement in Tape Pocket" section.					



Embossed Carrier Tape Specifications (Continued)






Allowable camber to be 1mm/100mm tape, non-cumulative




Maximum Component Movement in Tape Pocket

Component Lateral Movement 12mm Tape



Maximum Component Rotation Top View




Maximum Component Rotation Side View






Surface Mount Reel Specifications



 Drive spokes optional. If used, dimensions with asterisks apply

Tape Width	Reel Size	A (mm)	B Max (mm)	C (mm)	D Max (mm)	N Min (mm)	G (mm)	T Max (mm)
12mm 7"	7"	178 ±2	2.0 +0.5 -0	13 +0.5 -0.2	20.5 ±0.2	55 ±5	12.4 +2.0 -0.0	18.4
	13"	330 ±2	2.0 +0.5 -0	13 +0.5 -0.2	20.5 ±0.2	100 ±2	12.4 +2.0 -0.0	18.4

Tape Leader and Trailer Specifications



Note: There shall be a leader of at least 230mm which may consist of carrier tape and/or cover tape or a start tape followed by at least 160mm of empty carrier tape sealed with cover tape.

Note: There shall be a trailer of at least 160mm of empty carrier tape sealed with cover tape. The entire carrier tape must release from the reel hub as the last portion of the tape unwinds from the reel without damage to the carrier tape and the remaining components in the cavities.