

### DESCRIPTION

The AP64351 is 3.5A, synchronous buck converter with a wide input voltage range of 3.8V to 40V. The device fully integrates a 75mΩ high-side power MOSFET and a 45mΩ low-side power MOSFET to provide high-efficiency step-down DC/DC conversion.

The AP64351 device is easily used by minimizing the external component count due to its adoption of peak current mode control.

The AP64351 design is optimized for Electromagnetic Interference (EMI) reduction. The converter features

Frequency Spread Spectrum (FSS) with a switching frequency jitter of  $\pm 6\%$ , which reduces EMI by not allowing emitted energy to stay in any one frequency for a significant period of time. It also has a proprietary gate driver scheme to resist switching node ringing without sacrificing MOSFET turn-on and turn-off times, which reduces high-frequency radiated EMI noise caused by MOSFET switching.

The device is available in a SO-8EP package.

### FEATURES

- Wide Input Range: 3.8V to 40V
- 3.5A Continuous Output Current
- 0.8V  $\pm 1\%$  Reference Voltage
- 22 $\mu$ A Ultralow Quiescent Current (Pulse Frequency Modulation)
- 570kHz Switching Frequency
- Programmable Soft-Start Time
- Proprietary Gate Driver Design for Best EMI Reduction
- Frequency Spread Spectrum (FSS) to Reduce EMI
- Low-Dropout (LDO) Mode
- Precision Enable Threshold to Adjust UVLO
- Protection Circuitry
  - Undervoltage Lockout (UVLO)
  - Output Overvoltage Protection (OVP)
  - Cycle-by-Cycle Peak Current Limit
  - Thermal Shutdown
- Totally Lead-Free & Fully RoHS Compliant
- Halogen and Antimony Free. “Green” Device

### APPLICATIONS

- 5V, 12V, and 24V Distributed Power Bus Supplies
- White Goods and Small Home Appliances
- Home Audio
- Network Systems
- Consumer Electronics
- Cordless Power Tools
- Optical Communication and Networking Systems
- General Purpose Point of Load

### TYPICAL APPLICATIONS CIRCUIT




Figure 1. Typical Application Circuit

### ABSOLUTE MAXIMUM RATINGS

| Symbol            | Parameter                | Rating   | Unit |
|-------------------|--------------------------|--|------|
| VIN               | Supply Pin Voltage       | -0.3 to +42.0 (DC)                             | V    |
|                   |                          | -0.3 to +45.0 (400ms)                          |      |
| V <sub>BST</sub>  | Bootstrap Pin Voltage    | V <sub>SW</sub> - 0.3 to V <sub>SW</sub> + 6.0 | V    |
| V <sub>EN</sub>   | Enable/UVLO Pin Voltage  | -0.3 to +42.0                                  | V    |
| V <sub>SS</sub>   | Soft-Start Pin Voltage   | -0.3 to +6.0                                   | V    |
| V <sub>FB</sub>   | Feedback Voltage         | -0.3V to +6.0                                  | V    |
| V <sub>COMP</sub> | Compensation Pin Voltage | -0.3 to +6.0                                   | V    |
| V <sub>SW</sub>   | Switch Node Voltage      | -0.3 to VIN + 0.3 (DC)                         | V    |
|                   |                          | -2.5 to VIN + 2.0 (20ns)                       |      |
| T <sub>J</sub>    | Junction Temperature     | +160   | °C   |
| T <sub>L</sub>    | Lead Temperature         | +260   | °C   |

### RECOMMENDED OPERATING CONDITIONS

| Symbol           | Parameter                            | Min | Max  | Unit |
|------------------|--------------------------------------|-----|------|------|
| V <sub>IN</sub>  | Supply Voltage                       | 3.8 | 40   | V    |
| V <sub>OUT</sub> | Output Voltage                       | 0.8 | 39   | V    |
| T <sub>A</sub>   | Operating Ambient Temperature Range  | -40 | +85  | °C   |
| T <sub>J</sub>   | Operating Junction Temperature Range | -40 | +125 | °C   |

### EVALUATION BOARD




Figure 2. AP64351SP-EVM

### QUICK START GUIDE

The AP64351SP-EVM has a simple layout and allows access to the appropriate signals through test points. To evaluate the performance of the AP64351SP, follow the procedure below:

1. Connect a power supply to the input terminals  $V_{IN}$  and GND. Set  $V_{IN}$  to 12V.
2. Connect the positive terminal of the electronic load to  $V_{OUT}$  and negative terminal to GND.
3. For Enable, place a jumper at JH6 to “ON” position to connect EN pin to  $V_{IN}$  through 100K $\Omega$  resistor to enable IC. Jump to “OFF” position to disable IC.
4. The evaluation board should now power up with a 5.0V output voltage.
5. Check for the proper output voltage of 5.0V ( $\pm 1\%$ ) at the output terminals  $V_{OUT}$  and GND. Measurement can also be done with a multimeter with the positive and negative leads between  $V_{OUT}$  and GND.
6. Set the load to 3.5A through the electronic load. Check for the stable operation of the SW signal on the oscilloscope. Measure the switching frequency.

### MEASUREMENT/PERFORMANCE GUIDELINES:

- 1) When measuring the output voltage ripple, maintain the shortest possible ground lengths on the oscilloscope probe. Long ground leads can erroneously inject high frequency noise into the measured ripple.
- 2) For efficiency measurements, connect an ammeter in series with the input supply to measure the input current. Connect an electronic load to the output for output current.

### SETTING OUTPUT VOLTAGE:

Table 1 shows a list of recommended component selections for common output voltages.

| VOUT | R1             | R2           | L1          | R7             | C7    | C1, C2       | C5, C6       |
|------|----------------|--------------|-------------|----------------|-------|--------------|--------------|
| 1.2V | 4.99K $\Omega$ | 10K $\Omega$ | 3.3 $\mu$ H | 3.32K $\Omega$ | 3.3nF | 2x10 $\mu$ F | 2x22 $\mu$ F |
| 1.5V | 8.66K $\Omega$ | 10K $\Omega$ | 3.3 $\mu$ H | 4.22K $\Omega$ | 3.3nF | 2x10 $\mu$ F | 2x22 $\mu$ F |
| 1.8V | 12.4K $\Omega$ | 10K $\Omega$ | 3.3 $\mu$ H | 4.99K $\Omega$ | 3.3nF | 2x10 $\mu$ F | 2x22 $\mu$ F |
| 2.5V | 21.5K $\Omega$ | 10K $\Omega$ | 4.7 $\mu$ H | 6.98K $\Omega$ | 3.3nF | 2x10 $\mu$ F | 2x22 $\mu$ F |
| 3.3V | 31.6K $\Omega$ | 10K $\Omega$ | 4.7 $\mu$ H | 9.31K $\Omega$ | 3.3nF | 2x10 $\mu$ F | 2x22 $\mu$ F |
| 5.0V | 52.3K $\Omega$ | 10K $\Omega$ | 5.5 $\mu$ H | 14K $\Omega$   | 3.3nF | 2x10 $\mu$ F | 2x22 $\mu$ F |
| 12V  | 140K $\Omega$  | 10K $\Omega$ | 10 $\mu$ H  | 33.2K $\Omega$ | 3.3nF | 2x10 $\mu$ F | 2x22 $\mu$ F |

**Table 1. Common Output Voltages**

### EVALUATION BOARD SCHEMATIC




Figure 3. AP64351SP-EVM Schematic

### PCB TOP LAYOUT








Figure 4. AP64351SP-EVM – Top Layer



### BILL OF MATERIALS for AP64351SP-EVM for V<sub>OUT</sub>=5V

| Ref              | Value          | Description                                   | Qty | Size            | Vendor Name          | Manufacturer PN    | PCB Layer |
|------------------|----------------|---|-----|-----------------|----------------------|--------------------|-----------|
| C1, C2           | 10 $\mu$ F     | Ceramic Capacitor, 50V, X7R, 10%              | 2   | 1206            | Samsung              | CL31B106KBHNNNE    | Top       |
| C3, C4, C9       | 0.1 $\mu$ F    | Ceramic Capacitor, 50V, X7R, 10%              | 3   | 0603            | Würth Electronics    | 885012206095       | Top       |
| C5, C6           | 22 $\mu$ F     | Ceramic Capacitor, 16V, X7R                   | 2   | 1210            | Samsung              | CL32B226KOJNNNE    | Top       |
| C7               | 3.3nF          | Ceramic Capacitor, 25V, X7R                   | 1   | 0603            | Würth Electronics    | 885012206062       | Top       |
| C8               | 10nF           | Ceramic Capacitor, 25V, X7R                   | 1   | 0603            | Würth Electronics    | 885012206065       | Top       |
| R1               | 52.3K $\Omega$ | SMD Resistor, 1%                              | 1   | 0603            | Panasonic            | ERJ-3EKF5232V      | Top       |
| R2               | 10K $\Omega$   | SMD Resistor, 1%                              | 1   | 0603            | Panasonic            | ERJ-3EKF1002V      | Top       |
| R3               | 0 $\Omega$     | RES SMD 1% 1/10W                              | 1   | 0603            | Vishay               | CRCW06030000Z0EAC  | Top       |
| R4               | 100K $\Omega$  | RES SMD 1% 1/10W                              | 1   | 0603            | Yageo                | RC0603FR-07100KL   | Top       |
| R7               | 14K $\Omega$   | RES SMD 1% 1/10W                              | 1   | 0603            | Bourns Inc           | CR0603-FX-1402ELF  | Top       |
| R8               | 0 $\Omega$     | RES SMD 1% 1/10W                              | 1   | 0603            | Vishay               | MCT06030Z0000ZP500 | Top       |
| L1               | 5.5 $\mu$ H    | DCR=10.3m $\Omega$ , I <sub>r</sub> =10A      | 1   | 10.2x 10.2x 5mm | Würth Electronics    | 744325550          | Top       |
| JH6              |                | PCB Header, 40 POS                            | 1   | 1X3             | 3M                   | 2340-6111TG        | Top       |
| VIN, VOUT, GNDx2 | 1598           | Terminal Turret Triple 0.094" L (Test Points) | 4   | Through-Hole    | Keystone Electronics | 1598-2             | Top       |
| U1               | AP64351        | Sync Buck DC/DC Converter                     | 1   | SO-8EP          | Diodes Inc           | AP64351SP          | Top       |

**TYPICAL PERFORMANCE CHARACTERISTICS**





### IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

[www.diodes.com](http://www.diodes.com)