

### PAM8407 EV Board User Guide

AE Department

#### 1. Revision Information

Date	Revision	Description	Comment
2013/10	V1.0	Initial release	



## PAM8407 EVB User Guide

#### 2. Key Features

- 3W Output at 10% THD with a  $4\Omega$  load and 5V Power Supply
- 2.4W Output at 1% THD with a 4Ω Load and 5V Power Supply
- Filterless, Low Quiescent Current and Low EMI
- Low THD+N
- ♦ 32-step Digital Volume Control from -80dB(mute) to 24dB
- Superior Low Noise: 60uV
- Minimize Pop/Clip Noise
- High Efficiency up to 90%
- Auto Recovery Short Circuit Protection
- Thermal Shutdown
- Pb-Free Package







## 4. EV-Board PAM8407 EB37AA Description

PAM8407 EB37AA is designed for evaluated PAM8407. The PAM8407 is a 3W, class-D audio amplifier. Advanced 32-step Digital volume control minimizes external components and allows speaker volume control. The board is targeted to be used in providing a simple and convenient evaluation environment for the PAM8407.

### 5. EV Board View and Jack Description





#### 6. EV board operational sequence:

- a. Connect SD to a high for normal operation.
- b. To use the PAM8407 with a differential source, connect the positive lead of the audio source to the INP input and the negative lead of the audio source to the INN input. To use the PAM8407 with a single-ended source, the INN input should be ac- grounded.
- c. Connect the loading(speaker or power resistor) to the output jack.
- d. Power on: 2.7V to 5.5V DC power supply.

ltem	Value	Туре	Rating	Description	Vender and port
C1,C2,	0.1.15	X5R/X7R,	25V	Input coupling	TAIYO YUDEN
C3,C4	0. TUF	Ceramic/0603		CAP	UMK212B7104KG-T
C5, C7	1uF	X5R/X7R,	25\/	VDD coupling	TAIYO YUDEN
		Ceramic/0603	237	CAP,	TMK107B7105KA-T
C6, C8	10uF	X5R/X7R,	16\/	VDD main	TAIYO YUDEN
		Ceramic/0805	100	coupling CAP,	EMK212ABJ106KD-T
R1,R2,	Oohm	0603	1%	Input Resistor	
R3,R4	UUIIII	0603			
IC1	PM8407	SOP-16L			

#### 7. EV Board BOM List



# PAM8407 EVB User Guide

### 8. PCB Layout Example





## PAM8407 EVB User Guide

#### **Bottom layer**

