


Package Outline Dimensions


U-DFN2510-10 (Type CJ)



U-DFN2510-10 (Type CJ)			
Dim	Min	Max	Typ
A	0.545	0.605	--
A1	0.00	0.05	--
A3	0.152REF		
b	0.150	0.250	--
b1	0.350	0.450	--
D	2.450	2.575	--
E	0.950	1.075	--
e	--	--	0.500
E	0.950	1.075	1.000
L	0.350	0.450	--
k	0.200REF		
All Dimensions in mm			

Suggested Pad Layout

U-DFN2510-10 (Type CJ)



Dimensions	Value (in mm)
C	0.500
X	0.250
X1	0.450
X2	2.250
Y	0.625
Y1	0.575
Y2	0.700
Y3	1.400

ALL DIMENSIONS ARE NOMINAL VALUES SHOWN IN MILLIMETERS

Note: The suggested land pattern dimensions have been provided for reference only, as actual pad layouts may vary depending on application. These numbers may be modified based on user equipment capability or fabrication criteria. A more robust pattern may be desired for wave soldering and is calculated by adding 0.2 mm to the 'Z' dimension. For further information, please reference document IPC-7351A, Naming Convention for Standard SMT Land Patterns, and for International grid details, please see document IEC, Publication 97.