

Evaluation Board User Guide

Doc: ZXCT1080EV1-UG

Issue: 1.2

Date: 24 April 2008

Page: 1 of 8



Figure 1 Evaluation board components' layout

#### DESCRIPTION

The ZXCT1080EV1 evaluation board is intended for the evaluation of the ZXCT1080 device. The ZXCT1080 is a wide input common mode range current monitor. Because this wide input common mode range includes ground, the device is able to measure short circuit currents. It has a fixed gain of ten and requires no additional components thus making it a versatile device with a minimal components count.

The evaluation board is delivered with the values shown in Figure 2 below. As can be seen,  $R_S$  consists of two resistors (R1 and R2) which are configured in parallel such that either one or both resistors could be connected by completing the solder-bridge link next to each one. R2 (0.1R) is connected by default.

R3 consists of two pads with a hole in each pad and provides means for connecting an external  $R_{\rm S}$ .

With the values shown, the board produces an output of 1V/A

The printed circuit board is common to other devices in the ZXCT family and contains redundant component positions which will not be discussed here as they are not relevant.



# Evaluation Board User Guide

Doc: ZXCT1080EV1-UG

Issue: 1.2

Date: 24 April 2008

Page: 2 of 8




Figure 2 Equivalent circuit diagram for evaluation board ZXCT1080EV1

V<sub>CC</sub> range 4.5V to 12V Supply Range 3V to 60V



Evaluation Board User Guide

Doc: ZXCT1080EV1-UG

Issue: 1.2

Date: 24 April 2008

Page: 3 of 8

#### ORDERING INFORMATION

ORDER NUMBER
ZXCT1080EV1

Please note that evaluation boards are subject to availability and qualified leads.

#### PAD NAMES AND DEFINITIONS

NAME	DESCRIPTION		
V1	Supply Voltage		
V2	Connection to Load		
VOUT	Output Voltage		
FLAG	Not used		
GND	0V / Ground		
SL1,SL2	Solder Links		
V <sub>CC</sub>	Device supply		

The target applications are battery chargers, power supply units and other applications where high side current measurement is a requirement along with ability to measure down to 0V.

The input voltage (voltage on V1) range for the ZXCT1080EV1 is from 3V to 60V whilst  $V_{CC}$  ranges from 4.5V to 12V.



## Evaluation Board User Guide

Doc: ZXCT1080EV1-UG

Issue: 1.2

Date: 24 April 2008

Page: 4 of 8

### **ZXCT1080EV1 Summary**




Figure 3 Actual circuit diagram for ZXCT1080EV1

### **Sense resistor**

The board has been designed with two selectable values of sense resistor. The value of the sense resistor can be chosen by using the solder links SL1 and SL2.

The board is also tracked for a user defined through hole resistor (R3).

The  $50m\Omega$  resistor (R1) is selected by shorting SL1 and opening SL2. This results in an output of 0.5 V/A.

The  $100m\Omega$  resistor (R2) is selected by shorting SL2 and opening SL1, resulting in an output of 1V/A.

If both links are shorted the effective resistance is  $33.33m\Omega$  giving an output of 333.3mV/A.

If both links are open, the optional leaded resistor R3 can be exclusively used as the sense resistor. The maximum power dissipation rating of the resistor must be appropriate to the load current level.

For further information on choosing a value of sense resistor please refer to the ZXCT1080 datasheet.



### ZXCT1080EV1 Evaluation Board

Evaluation Board User Guide

Doc: ZXCT1080EV1-UG

Issue: 1.

Date: 24 April 2008

Page: 5 of 8

#### Configuration table for ZXCT1080EV1

LOAD CURRENT (A)	$R_{SENSE}$ (m $\Omega$ )	VOUT (V)	SOLDER LINK CONFIGURATION
1.0	100	1.0	Short SL2
1.0	50	0.5	Short SL1
1.0	33.33	0.33	Short SL1 & SL2

#### **Configuration for different LOAD currents.**

The board can be configured for different load currents by changing the SMD resistors or fitting a suitable wire ended resistor and opening both solder links. It is important to ensure an appropriate value of  $R_{\rm S}$  is selected to obtain the desired accuracy for a given output current.

The value of V<sub>OUT</sub> is the voltage dropped across the sensing resistor multiplied by ten.

Choosing a larger value for R<sub>S</sub> gives a higher output voltage for a given current resulting in better resolution but at the expense of increased voltage drop and higher dissipation in R<sub>S</sub>.

The ZXCT1080 is optimized for values of V<sub>SENSE</sub> between 10mV and 150mV.

#### Accuracy

The ZXCT1080 has a typical 3% accuracy for a  $V_{SENSE}$  of 100 mV. The accuracy of the output voltage will be influenced by the tolerance of the external sense used. The ZXCT1080EV1 utilizes 1% sense resistors.



## Evaluation Board User Guide

Doc: ZXCT1080EV1-UG

Issue: 1.

Date: 24 April 2008

Page: 6 of 8

#### COMPONENTS LIST

Ref	Value	Package	Part Number	Manuf- acturer	Notes
R1	50mΩ	2512	LR2512-R050FW	Welwyn	SMD Sense Resistor 1%
R2	100m $Ω$	2512	LR2512-R100FW	Welwyn	SMD Sense Resistor 1%
R5,R6	0R	Link/0805	0805 1% generic		
I/O's		Test loops	100-108	Hughes	Rapid 17-1835 (6-off)
PCB			ZDB341R2	Zetex	
ZXCT		SOT23-5	ZXCT1080E5	Zetex	

#### **SET-UP AND TEST**

The board is preset to give an output Voltage of 1V for a load current of 1A (SL2 is shorted to connect in the  $100m\Omega$  (R2) sense resistor). To change the board to give an output Voltage of 1V for a current of 2.0A, de-solder SL2 and short SL1. This connects the  $50m\Omega$  (R1) sense resistor.

#### **Required Equipment**

- 1. 1 x 10R 5W resistor (load).
- 2. 2 x adjustable bench PSUs.
- 3. 2 x DVMs (one for voltage measurement and one for current measurement)

Note: BUT = Board Under Test

#### 500mA load test

- 1. Ensure SL2 is shorted.
- 2. Limit PSU1's current to between 10mA and 40mA.
- 3. Limit PSU2's current to 0.6A.
- 4. Set PSU1 to 5V  $\pm 0.1V$  and connect it to  $V_{CC}$  on BUT.
- 5. Set PSU2 to 0V and connect between the V1 and GND terminals .
- 6. Connect the resistor in series with the ammeter between the V2 and GND terminals (10R 5W resistor is suggested, if using a different value, make sure it's power rating is P ≥ 2\*I<sup>2\*</sup>R).
- 7. Switch on PSU1, followed by PSU2.
- 8. Adjust PSU2 until the ammeter reads 500 mA ±1 mA,
- 9. Measure  $V_{OUT}$  with a DVM. The output voltage should read 0.5V  $\pm$  25mV.



Evaluation Board User Guide

Doc: ZXCT1080EV1-UG

Issue: 1.2

Date: 24 April 2008

Page: 7 of 8






Figure 4 Test diagram for ZXCT1080EV1

#### **EVALUATION BOARD**





**Top Silk** 

**Top Copper** 



### ZXCT1080EV1 **Evaluation Board**

User Guide

ZXCT1080EV1-UG Doc:

Issue:

24 April 2008 Date:

8 of 8 Page:

#### Definitions

#### Product change

Zetex Semiconductors reserves the right to alter, without notice, specifications, design, price or conditions of supply of any product or service. Customers are solely responsible for obtaining the latest relevant information before placing orders

#### Applications disclaimer

The circuits in this design/application note are offered as design ideas. It is the responsibility of the user to ensure that the circuit is fit for the user's application and meets with the user's requirements. No representation or warranty is given and no liability whatsoever is assumed by Zetex with respect to the accuracy or use of such information, or infringement of patents or other intellectual property rights arising from such use or otherwise. Zetex does not assume any legal responsibility or will not be held legally liable (whether in contract, tort (including negligence), breach of statutory duty, restriction or otherwise) for any damages, loss of profit, business, contract, opportunity or consequential loss in the use of these circuit applications, under any circumstances.

#### Life support

Zetex products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Zetex Semiconductors plc. As used herein:

Life support devices or systems are devices or systems which:

1. are intended to implant into the body

or

- 2. support or sustain life and whose failure to perform when properly used in accordance with instructions
- for use provided in the labelling can be reasonably expected to result in significant injury to the user.
- A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

#### Reproduction

The product specifications contained in this publication are issued to provide outline information only which (unless agreed by the company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contract or be regarded as a representation relating to the

#### Terms and Conditions

All products are sold subjects to Zetex' terms and conditions of sale, and this disclaimer (save in the event of a conflict between the two when the terms of the contract shall prevail) according to region, supplied at the time of order acknowledgement.

For the latest information on technology, delivery terms and conditions and prices, please contact your nearest Zetex sales office.

Zetex is an ISO 9001 and TS16949 certified semiconductor manufacturer.

To ensure quality of service and products we strongly advise the purchase of parts directly from Zetex Semiconductors or one of our regionally authorized distributors. For a complete listing of authorized distributors please visit: www.zetex.com/salesnetwork

Zetex Semiconductors does not warrant or accept any liability whatsoever in respect of any parts purchased through unauthorized sales channels.

#### ESD (Electrostatic discharge)

Semiconductor devices are susceptible to damage by ESD. Suitable precautions should be taken when handling and transporting devices. The possible damage to devices depends on the circumstances of the handling and transporting, and the nature of the device. The extent of damage can vary from immediate functional or parametric malfunction to degradation of function or performance in use over time. Devices suspected of being affected should be replaced.

#### Green compliance

Zetex Semiconductors is committed to environmental excellence in all aspects of its operations which includes meeting or exceeding regulatory requirements with respect to the use of hazardous substances. Numerous successful programs have been implemented to reduce the use of hazardous substances and/or emissions

All Zetex components are compliant with the RoHS directive, and through this it is supporting its customers in their compliance with WEEE and ELV directives

Product status key:

"Preview Future device intended for production at some point. Samples may be available "Active"

Product status recommended for new designs

"Last time buy (LTB)" Device will be discontinued and last time buy period and delivery is in effect "Not recommended for new designs" Device is still in production to support existing designs and production

Production has been discontinued

Datasheet status key:

This term denotes a very early datasheet version and contains highly provisional "Draft version

information, which may change in any manner without notice.

"Provisional version" This term denotes a pre-release datasheet. It provides a clear indication of anticipated performance. However,

changes to the test conditions and specifications may occur, at any time and without notice.

"Issue" This term denotes an issued datasheet containing finalized specifications. However, changes to specifications

may occur, at any time and without notice.

Europe Americas Asia Pacific **Corporate Headquarters** Zetex GmbH Zetex Inc Zetex (Asia Ltd) Zetex Semiconductors plc Kustermann-park 700 Veterans Memorial Highway 3701-04 Metroplaza Tower 1 Zetex Technology Park, Chadderton Balanstraße 59 Hauppauge, NY 11788 Hing Fong Road, Kwai Fong Oldham, OL9 9LL D-81541 München Hong Kong United Kingdom Germany Telefon: (49) 89 45 49 49 0 Telephone (44) 161 622 4444 Telephone: (1) 631 360 2222 Telephone: (852) 26100 611 Fax: (49) 89 45 49 49 49 Fax: (852) 24250 494 Fax: (44) 161 622 4446 Fax: (1) 631 360 8222 europe.sales@zetex.com usa.sales@zetex.com asia.sales@zetex.com ha@zetex.com

© 2006 Published by Zetex Semiconductors plc