


Package Outline Dimensions

W-QFN1520-10




W-QFN1520-10			
Dim	Min	Max	Typ
A	0.70	0.80	0.75
A1	0.00	0.05	0.03
A3	—	—	0.152
b	0.220	0.280	0.250
D	1.45	1.55	1.50
E	1.95	2.05	2.00
e	—	—	0.500
L	0.325	0.425	0.375
L1	0.575	0.675	0.625
z	0.100	0.150	0.125

All Dimensions in mm

Suggested Pad Layout

W-QFN1520-10



Dimensions	Value (in mm)
C	0.500
X	0.350
X1	1.850
X2	2.100
Y	0.475
Y1	0.725
Y2	1.600

ALL DIMENSIONS ARE NOMINAL VALUES SHOWN IN MILLIMETERS

Note: The suggested land pattern dimensions have been provided for reference only, as actual pad layouts may vary depending on application. These numbers may be modified based on user equipment capability or fabrication criteria. A more robust pattern may be desired for wave soldering and is calculated by adding 0.2 mm to the 'Z' dimension. For further information, please reference document IPC-7351A, Naming Convention for Standard SMT Land Patterns, and for International grid details, please see document IEC, Publication 97.