



R1, R2, SMBUS Address set

\* C1=C2=8pF for CL=8pF crystal, other CL value crystal use C1=C2=2xCL-8

25M CMOS for LAN Ref. CLK

Put close to pin <300mil

**6 Low Power HCSL Output**

SSC\_SEL "H" = -0.5% SSC  
 SSC\_SEL "L" or "M" = SSC off  
 Use SMBUS to set -0.25%

**App Note:**

1. All VDD pin needs 0.1u +1uF decoupling cloase to pin
2. VDDA, VDDOSC use small R+C filtering for better DC/DC ripple noise rejection
3. This is LP-HCSL type output: serial 0 ohm is optional, but it can be replace in 5 to 15 ohm for fine tune board RX end each clock skew due to different trace length
4. Since OSC pin cap.=5pF so select CL=8pF crystal can C1=C2=8pF, other CL value crystal C1=C2=2xCL-5-3, 3 is PCB C\_stray pF
5. Note SSC\_EN and SMBUS address pins are power on latch once set;
6. Make LVDS clock, it needs AC coupling and then RX side use pull-up/down Rs to bias LVDS level, refer to datasheet;
7. OEx# pins have internal pull-down
8. Connect epad to GND plane in 8 vias

Title		
Pi6CG33602C Application schematic		
Size B	Document Number Diodes Inc. Clock IC Application engineering	Rev 2
Date:	Monday, May 04, 2020	Sheet 1 of 1