



Mechanical Data

- Surface Mount Package
- Weight: 0.003 grams (Approximate)
- Max Soldering Temperature +260°C for 30 secs as per JEDEC J-STD-020
- Case Material – Molded Plastic, UL Flammability Rating 94V-0
- Terminals: Finish – Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 (e3)

Package View




Package Outline Dimensions



SOT563			
Dim	Min	Max	Typ
A	0.55	0.60	--
b	0.15	0.30	0.20
c	0.10	0.18	0.11
D	1.50	1.70	1.60
E	1.55	1.70	1.60
E1	1.10	1.25	1.20
e	--	--	0.50
e1	0.90	1.10	1.00
L	0.10	0.30	0.20
a	8°	9°	7°

All Dimensions in mm

Suggested Pad Layout



Dimensions	Value (in mm)
C	0.500
C1	1.270
G	0.600
X	0.300
X1	1.300
Y	0.670
Y1	1.940

Note: The suggested land pattern dimensions have been provided for reference only, as actual pad layouts may vary depending on application. These dimensions may be modified based on user equipment capability or fabrication criteria. A more robust pattern may be desired for wave soldering and is calculated by adding 0.2 mm to the 'Z' dimension. For further information, please reference document IPC-7351A, Naming Convention for Standard SMT Land Patterns, and for International grid details, please see document IEC, Publication 97.

Note: For high voltage applications, the appropriate industry sector guidelines should be considered with regards to creepage and clearance distances between device Terminals and PCB tracking.

Minimum Packing Quantity

Reel Size	Quantity	Tape Width	Part Number Suffix	Notes
7" Reel	3,000	8mm	-7, 7A	
7" Reel	4,000	8mm	-7	Applies to Logic Products
7" Reel	8,000	8mm	-7B	
13" Reel	10,000	8mm	-13, -13A	

Note: Package quantities given are for minimum packaging quantity only, not minimum order quantity. For minimum order quantity, please contact Sales Department.

Note: No mixed date codes or partial quantity (less than minimum packaging quantity) per packaging is allowed.

Note: In no case shall there be two or more consecutive components missing from any reel for any reason.

Device Tape Orientation

Tape Width	Part Number Suffix	Tape Orientation
8mm	-7 -13	<p>Symmetrical</p>
		<p>Asymmetrical</p>
8mm	-7A -13A	<p>Symmetrical</p>
8mm	-7B	<p>Symmetrical</p>


Note: For part marking, refer to product datasheet.

Note: Tape and package drawings are not to scale and are shown for device tape orientation only.

Direction of feed


Embossed Carrier Tape Specifications

a) P = 4.0mm (Part Number Suffix -7, -7A, -13, -13A)





Tape Width (W)	Dimension	Value (mm)	Dimension	Value (mm)	Dimension	Value (mm)
8mm	D	1.55 ±0.05	F	3.5 ±0.05	P2	2.0 ±0.05
	D1	0.5 ±0.05	P	4.0 ±0.10	t	0.20 ±0.02
	E	1.75 ±0.10	P0	4.0 ±0.10	W	8.0 +0.2/-0.1
	A0 B0 K0	Determined by component size. The clearance between the component and the cavity must comply to the rotational and lateral movement requirement provided in figures in the "Maximum Component Movement in Tape Pocket" section.				

b) P = 2.0mm (Part Number Suffix -7B)



Tape Width (W)	Dimension	Value (mm)	Dimension	Value (mm)	Dimension	Value (mm)
8mm	D	1.50 ±0.10	F	3.5 ±0.05	P2	2.0 ±0.05
	D1	0.5 ±0.05	P	2.0 ±0.05	t	0.18 ±0.05
	E	1.75 ±0.10	P0	4.0 ±0.10	W	8.0 ±0.10
	A0 B0 K0	Determined by component size. The clearance between the component and the cavity must comply to the rotational and lateral movement requirement provided in figures in the "Maximum Component Movement in Tape Pocket" section.				


Embossed Carrier Tape Specifications (Continued)




Camber (Top View)
Allowable camber to be 1mm/100mm tape, non-cumulative

Maximum Component Movement in Tape Pocket


Component Lateral Movement
8mm Tape




Maximum Component Rotation
Top View



Maximum Component Rotation
Side View




Surface Mount Reel Specifications



* Drive spokes optional. If used, dimensions with asterisks apply.

Tape Width	Reel Size	A (mm)	B Max (mm)	C (mm)	D Max (mm)	N Min (mm)	G (mm)	T Max (mm)
8mm	7"	178 ±2	2.0 +0.5 -0	13 +0.5 -0	20.5 ±0.2	55 ±5	8.4 +1.5 -0.0	14.4
	13"	330 ±2	2.0 +0.5 -0	13 +0.5 -0	20.5 ±0.2	100 ±2	8.4 +1.5 -0.0	14.4

Tape Leader and Trailer Specifications



Note: There shall be a leader of at least 230mm which may consist of carrier tape and/or cover tape or a start tape followed by at least 160mm of empty carrier tape sealed with cover tape.

Note: There shall be a trailer of at least 160mm of empty carrier tape sealed with cover tape. The entire carrier tape must release from the reel hub as the last portion of the tape unwinds from the reel without damage to the carrier tape and the remaining components in the cavities.