



New Product Announcement

PI6CB332001A

Twenty-Output PCIe 4.0 and 5.0 Buffer for Server and Data-Center Applications

The DIODES™ PI6CB332001A is a 20-output, low-power, PCIe 4.0 and 5.0 clock buffer capable of distributing reference clocks for PCIe®, UPI, SAS, SATA, and other interfaces.

The device takes a reference input and provides fanout for twenty 100MHz-differential HCSL outputs with on-chip terminations. This in turn saves up to 80 external resistors.

With a very low additive jitter and a small size, the device is an ideal solution for server, high-performance computing (HPC), and data-center applications.

The PI6CB332001A is packaged in the small-footprint 80-aQFN (6mm x 6mm) package.



The DIODES™ Advantage

- **Intel DB2000QL-Compliant Clock Buffer**
 Follows Intel® DB2000QL pinout/function definition;
 Intel P/N: K20599-009;
 Supports ultra-low jitter to meet PCIe 4.0 & 5.0 requirements with a small 6x6mm package
- **On-Chip Termination Saves Up to 80 External Resistors**
 Reduces bill-of-materials (BOM) cost, saves board space, and simplifies PCB layout
- **Very Low Additive Jitter: DB2000Q <30fs RMS**
 Provides jitter margin for system designs
- **Power-Down-Tolerant OE Pins**
 Allows the OE pins to be driven by external signals when the device is in a power-down or reset condition

Applications

- Servers
- Data centers
- High-performance computing (HPC) devices


The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.

DIODES is a trademark of Diodes Incorporated in the United States and other countries.

© 2022 Copyright Diodes Incorporated. All Rights Reserved.

All other trademarks are the property of their respective owners.

Typical Application



Product Portfolio

Part Number	Number of Outputs	Output Impedance	Voltage Support	Package
PI6CB332001A	20	85Ω	3.3V	80-aQFN (6mm x 6mm)
PI6CB33201	2	85Ω	3.3V	24-TQFN (4mm x 4mm)
PI6CB33202	2	100Ω	3.3V	24-TQFN (4mm x 4mm)
PI6CB33401	4	85Ω	3.3V	32-TQFN (5mm x 5mm)
PI6CB33402	4	100Ω	3.3V	32-TQFN (5mm x 5mm)
PI6CB33601	6	85Ω	3.3V	40-TQFN (5mm x 5mm)
PI6CB33602	6	100Ω	3.3V	40-TQFN (5mm x 5mm)
PI6CB33801	8	85Ω	3.3V	48-TQFN (6mm x 6mm)
PI6CB33802	8	100Ω	3.3V	48-TQFN (mm6 x 6mm)

Ordering Information

Orderable Part Number	Family	Package Code	MOQ
PI6CB332001AZXBIE	Clock Buffer	ZXB	3,000