


Package Outline Dimensions


TO252 (Type WX)



TO252 (Type WX)			
Dim	Min	Max	Typ
A	2.20	2.38	2.30
A1	0.00	0.10	--
A2	0.97	1.17	1.07
b	0.72	0.85	0.78
b3	5.23	5.46	5.33
c	0.43	0.58	0.53
D	6.00	6.20	6.10
D1	5.30 REF		
e	2.286 REF		
E	6.50	6.70	6.60
E1	4.70	4.92	4.83
H	9.90	10.30	10.10
L	1.40	1.70	1.50
L1	2.90 REF		
L2	0.51 BSC		
L3	0.90	1.25	--
L4	0.60	1.00	0.80
L5	1.70	1.90	1.80
a	0°	8°	-
a1	5°	9°	7°
a2	5°	9°	7°
All Dimensions in mm			

Suggested Pad Layout

TO252 (Type WX)



Dimensions	Value (in mm)
C	4.572
X	1.060
X1	5.632
Y	2.600
Y1	5.700
Y2	10.700

ALL DIMENSIONS ARE NOMINAL VALUES SHOWN IN MILLIMETERS

Note: The suggested land pattern dimensions have been provided for reference only, as actual pad layouts may vary depending on application. These numbers may be modified based on user equipment capability or fabrication criteria. A more robust pattern may be desired for wave soldering and is calculated by adding 0.2 mm to the 'Z' dimension. For further information, please reference document IPC-7351A, Naming Convention for Standard SMT Land Patterns, and for International grid details, please see document IEC, Publication 97.