

2×33W STEREO/1×66W MONO, DIGITAL INPUT CLASS-D AUDIO AMPLIFIER WITH AUDIO EFFECT TURNING

Description

The PAMS5804 is a fully integrated, high-efficiency, stereo Class-D audio amplifier with digital inputs. The application circuit requires few passive components to operate with 4.5V to 26.4V PVDD supply, 3.3V or 1.8V DVDD supply. It can drive 2×33W output power into BTL 6Ω and 1×66W into PBTL 3Ω @1% THD+N.

The PAMS5804 features one novel PWM modulation architecture, which adjusts PWM common duty cycle during start-up phase to avoid startup pop click.

Spread spectrum technology provides lower EMI noise. It allows inductor free application with specified output power situation with the PAMS5804.

The advanced audio effect tuning capability inside the PAMS5804 provides one highly integrated solution. It allows turning on/off each block with highly free operations. Both BQs and volume help a lot to maintain audio headroom.

The PAMS5804 is packaged in TSSOP-28EP (Type TH-1).

Applications


- Portable speakers: bluetooth, smart speakers with voice assistant
- Home audios: TV, sound-bar, STB (set top box), HTiB (home theatre in a box)
- PCs and laptops

Features

- Flexible Power Supply Configurations
 - PVDD: 4.5V to 26.4V
 - DVDD and I/O: 3.3V or 1.8V
- Various Output Configurations
 - 2×33W, Stereo Mode (6Ω, 22V, THD+N = 1%)
 - 1×66W, Stereo Mode (3Ω, 22V, THD+N = 1%)
- Excellent Audio Performance
 - THD+N ≤ 0.02% at 1W, 1kHz, PVDD = 12V
 - 107dB A-Weighted Signal-to-Noise Ratio (SNR)
 - Idle Switching A-Weighted Noise ≤ 35μVRMS
 - 24mA Low Quiescent Current
 - 90% Efficiency into 6Ω Load at 12V
- Configurable Digital Audio Interface
 - I2C Control with Up to 4 Selectable Addresses
 - I2S Left-Justified, Right-Justified, TDM Audio Format
 - 3-Wire Digital Audio Interface without MCLK Required
 - 32kHz, 44.1kHz/48kHz Input Sample Rate
 - SDOUT for Acoustic Echo Cancellation – AEC or 1.1/2.1 System Sub-Channel Signal Routing
- Advanced Audio Effect Tuning
 - Flexible Digital and Analog Gain Adjustment
 - High Pass Filter for DC Blocking
 - Input Signal Router for Left and Right Channel
 - 2×10 BQs to Support Enhanced Audio Frequency Tuning
 - Dynamic Range Boost (DRB)
 - Full-Band AGL to Limit Output Power
- Analog Protections
 - FAULT Status Report through GPIO and I2C Registers
 - Overcurrent and Direct Current Protection
 - Overtemperature Protection
 - Undervoltage and Overvoltage Protection
 - Clock Error Protection
- TSSOP-28EP (Type TH-1) Package
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please [contact us](mailto:contact_us@diodes.com) or your local Diodes representative.
<https://www.diodes.com/quality/product-definitions/>

Notes: 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.


Pin Descriptions



TSSOP-28EP (Type TH-1) Top View

Pin No.	Name	Type	Description
1	DGND	PWR	Digital ground.
2	DVDD	PWR	Digital power supply input: 3.3V or 1.8V.
3	ADR/GPIO2	DIO	I2C address selection/ GPIO2: FAULT/WARNING/SDOUT...
4	VREG_DVDD	AOUT	Digital regulator output.
5	GPIO3	DIO	GPIO3: FAULT/WARNING/SDOUT... Default setting is allowed to directly short to GND.
6	FSYNC	DIN	Word select clock for the digital signal.
7	BCLK	DIN	Bit clock for the digital signal.
8	SDIN	DIN	Serial data input.
9	GPIO1	DIO	GPIO1: FAULT/WARNING/SDOUT...
10	SDA	DIO	I2C serial data.
11	SCL	DIN	I2C clock.
12	PDN	DIN	Shut down, low active.
13	VREG_AVDD	AOUT	Analog regulator output.
14	AGND	PWR	Analog ground.
15	PVDD	PWR	Power stage supply input.
16	PVDD	PWR	Power stage supply input.
17	OUT_R+	AOUT	Right channel positive output of H-bridge.
18	BST_R+	AIN	Bootstrap capacitor for OUT_R+.
19	PGND	PWR	Power stage ground.
20	OUT_R-	AOUT	Right channel negative output of H-bridge.
21	BST_R-	AIN	Bootstrap capacitor for OUT_R-.
22	BST_L-	AIN	Bootstrap capacitor for OUT_L-.
23	OUT_L-	AOUT	Left channel negative output of H-bridge.
24	PGND	PWR	Power stage ground.
25	BST_L+	AIN	Bootstrap capacitor for OUT_L+.
26	OUT_L+	AOUT	Left channel positive output of H-bridge.
27	PVDD	PWR	Power stage supply input.
28	PVDD	PWR	Power stage supply input.

Functional Block Diagram




Device Family Comparison


Device Name	R _{DS(on)}	PVDD	Output Power
PAMS5803	110m Ω	4.5V to 17V	Stereo 2x24W (4 Ω , 16V, THD+N = 1%)
PAMS5804	135m Ω	4.5V to 26.4V	Stereo 2x33W (6 Ω , 22V, THD+N = 1%)
PAMS5825	75m Ω	4.5V to 21V	Stereo 2x33W (6 Ω , 21V, THD+N = 1%)
PAMS5826	95m Ω	4.5V to 26.4V	Stereo 2x40W (6 Ω , 24V, THD+N = 1%)
PAMS5827	75m Ω	4.5V to 26.4V	Stereo 2x41W (6 Ω , 24V, THD+N = 1%)

Typical Applications Circuits (Notes 4 & 5)

Application Circuit Example of Stereo




Application Circuit Example of Mono



- Notes:
- Both 0.47 μ F or 0.22 μ F are suitable for BST caps.
 - GPIO3 default setting is allowed to directly short to GND.

Ordering Information (Note 9)




Orderable Part Number	Identification Code	Package Code	Package	Packing	
				Qty.	Carrier
PAMS5804T28ZE-13	PAMS5804	T28ZE	TSSOP-28EP (Type TH-1)	3000	13" Tape and Reel

9. For packaging details, go to our website at <https://www.diodes.com/design/support/packaging/diodes-packaging/>.

Marking Information

(Top View)



Logo :

Marking : PAMS5804

YY: Year: 25, 26, 27~

WW: Week: 01 to 52; 52

Represents 52 and 53 Week


XX: Internal Code

E: Exposed Pad

Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

TSSOP-28EP (Type TH-1)




TSSOP-28EP (Type TH-1)			
Dim	Min	Max	Typ
A	--	1.20	--
A1	0.05	0.15	--
A2	0.80	1.00	--
A3	0.39	0.49	0.44
b	0.20	0.29	--
c	0.13	0.18	--
D	9.60	9.80	9.70
D2	5.40	5.60	5.50
E	6.20	6.60	6.40
E1	4.30	4.50	4.40
E2	2.60	2.80	2.70
e	0.65BSC		
L	0.45	0.75	0.60
L1	1.00BSC		
θ	0°	8°	--
All Dimensions in mm			

Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

TSSOP-28EP (Type TH-1)



Dimensions	Value (in mm)
C	0.650
X	0.345
X1	5.600
X2	4.398
X3	8.795
Y	1.450
Y1	2.800
Y2	2.000
Y3	6.900

Mechanical Data

- Moisture Sensitivity: Level 3 per J-STD-020
- Terminals: Finish – Sn, Solderable per J-STD-002, Test B1 (e1)
- Weight: 0.15 grams (Approximate)

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.

All other trademarks are the property of their respective owners.
© 2025 Diodes Incorporated. All Rights Reserved.

www.diodes.com