



# PI2EQX6812ZHE 2-lane SAS/SATA ReDriver Application Information

#### Contents

- General Introduction
- How to use pin strap and I2C control
- > External Components Requirement
- Layout Design Guide
- Power Supply Bypassing
- Power Supply Sequencing
- Equalization Setting
- Output Swing Setting
- De-emphasis Setting
- > I2C Configuration Sequence
- > Typical application circuit
- PCB Layout Sample
- > Pericom SATA/SAS ReDriver Selection Table

#### **General Introduction**


PI2EQX6812 is TWO-Lane SAS/SATA redrivers to support up to 6Gbps signal, and they provide flexible output strength and de-emphasis controls separately on each lane to provide the optimum signal to pre-compensate for losses across long trace or noisy environments so that the receiver gets a clean with good eye opening. PI2EQX6812 only provides I2C function set output swing/de-emphasis and input equalization.

#### Packaging: 42-contact TQFN (5x11mm) for PI2EQX6812

Main Application:

- ✓ Server
- ✓ Desktop
- ✓ Storage/Workstation

Figure1 is typical application sample.





Application\_Note

# How to use I2C control for output swing/de-emphasis and input equalization of PI2EQX6812

For PI2EQX6812, it provides one way as below to set output swing/de-emphasis and input equalization. And the way depends on the state of the MODE pin with 100k internal pull-up resistor.

# Note: Control of input/output configuration is separated for the A and B channels, so that each channel within group may have the different setting.

When MODE pin is set HIGH, the configuration only has some selection, not for all table value. So it is not recommended to use.

When MODE pin is LOW, all the internal configuration registers can be programmed by I2C function. Note that during initial power-on, the value at the configuration input pins will be latched to the configuration registers as initial startup states.

Note: Each channel is independtently controlled for input equalizer, output swing and output de-emphasis.

 The integrated I2C interfaces operate as a slave device, supporting standard rate operation of 100Kbps, with 7bit addressing mode and LSB indication either a read or write operation as shown below. The address for a specific device is determined by A0, A1 and A4 pins with internal pull-up resistors. So up to eight PI2EQX6812 devices can be connected to a single I2C bus.

Address Assignment							
A6	A5	A4	A3	A2	A1	A0	R/W
1	1	Program	0	0	Programmable		1=R, 0=W

 Data bytes must be 8-bits long and transferred with MSB first. Please see I2C data transfer diagram in Page12 of datasheet. For data byte definition as below, please see Page8 -10 of datasheet in detail.

#### **Configuration Register Summary**

Byte	Mnemonic	Function		
0	SIG	Signal Detect, indicates valid input signal level		
1	RSVD	Reserved for future use		
2	LBDEC	Loopback and De-emphasis Control, provides for control of the loopback function and De-emphasis mode (Half-bit or Full-bit)		
3	INDIS	Channel Input Disable, controls whether s channels input buffer is enabled or disabled		
4	OUTDIS	Channel Output Disable, controls whether a channel output buffer is enabled or disabled.		
5	A0	Channel A0 configuration		
6	B0	Channel B0 configuration		
11	A1	Channel A1 configuration		
12	B1	Channel B1 configuration		
13	VTH	Input level threshold configuration		
14	RSVD	Reserved for future use		

- For I2C inputs, SCL and SDA pin are tolerant with +3.3V power.
- For I2C configuration sequence in detail, please see Page6-7 in this file.

#### **External Components Requirement**

PI2EQX6812 require AC coupling capacitors for all redriver inputs and outputs. High-quality, low-ESR, X7R, 10nF, 0402-sized capacitors are recommended.

#### Layout Design Guide



# Application\_Note

#### ■ Layout Considerations for Differential Pairs

- ✓ The trace length miss-matching shall be less than 5 mils for the "+" and "-" traces in the same pairs
- ✓ Use wider trace width, with 100ohm differential impedance, to minimize the loss for long routes
- ✓ Target differential Zo of 100ohm ±20%
- More pair-to-pair spacing for minimal crosstalk coupling, it is recommended to have >3X gap spacing between differential pairs.
- ✓ It is preferable to route differential lines exclusively on one layer of the board, particularly for the input traces
- ✓ The use of vias should be avoided if possible, if vias must be used, they should be used sparingly and must be placed symmetrically for each side of a given differential pair.
- ✓ Route the differential signals away from other signals and noise sources on the printed circuit board

#### PCB Layout Trace Routings




Figure2 Layout Sample for Trace Routings

#### **Power-Supply bypass**

More careful attention must be paid to the details associated with high-speed design as well as providing a clean power supply; there are some approaches as recommendation.

- The supply (VDD) and ground (GND) pins should be connected to power planes routed on adjacent layers of the printed circuit board. The distance to plane should be <50mil.</p>
- ✓ The layer thickness of the dielectric should be minimized so that the VDD and GND planes create a low inductance supply with distributed capacitance.
- ✓ Careful attention to supply bypassing through the proper use of bypass capacitors is required. A low-ESR 0.01uF bypass capacitor should be connected to each VDD pin such that the capacitor is placed as close as possible to PI2EQX6812. Smaller body size capacitors can help facilitate proper component placement. The distance of capacitors to IC body should be <100mil.</p>
- ✓ One capacitor with capacitance in the range of 1uF to 10uF should be incorporated in the power supply bypassing design as well. It is can be either tantalum or an ultra-low ESR ceramic.





Proper power supply sequencing is recommened for all devices. Always apply GND and VDD before applying signals., especially if the signal is not current limited.

Application\_Na

Caution: Do NOT exceed the absolute maximum ratings because stresses beyond the listed ratings can cause permanent damage to the device.

## **Equalization Setting**

#### Various Input Trace and Eye Test with different EQ setting

Figure3 is PI2EQX6812 test setup for different EQ setting, R is PI2EQX6812. Signal Source: PRBS2^7-1 pattern, Differential Voltage is 600mV, Pre-emphasis is 0dB




Figure3 PI2EQX6812 test setup for different equalization setting

#### Table1 Eye Diagram at TP4 vs. Input FR4 trace and EQ setting at 6Gb/s for PI2EQX6812

	Input Trace Length	SEL[20] Setting	Input Eye at TP3	Output Eye at TP4
	6 inch FR4 Lab trace (-2dB loss at 6GHz)	3.2dB (SEL[2,1,0] =010)		
Eye Diagram vs.	18 inch FR4 Lab trace (-6dB loss at 3GHz)	6.9dB (SEL[2,1,0] =100)		
EQ setting at 6Gb/s	30 inch FR4 Lab trace (-10dB at 3GHz)	10.4dB (SEL[2,1,0] =110)		
	48 inch FR4 Lab trace (-16dB at 3GHz)	13.8dB (SEL[2,1,0] =111)		



# **Output Swing Setting**

Figure4 is PI2EQX6812 test setup for different output swing setting, R is PI2EQX6812. Signal Source: PRBS2^7-1 pattern, Differential Voltage is 500mV, Pre-emphasis is 0dB





Figure4 PI2EQX6812 test setup for different output swing setting

Table2 Output Swing at TP4 vs. OS setting at 3Gb/s and 6Gb/s for PI2EQX6812



# **De-emphasis Setting**

Figure5 is PI2EQX6812 test setup for different De-emphasis setting, R is PI2EQX6812. Signal Source: PRBS2^7-1 pattern, Differential Voltage is 500mV, Pre-emphasis is 0dB





Figure5 PI2EQX6812 test setup for different De-emphasis setting




# Application\_Note

### Table3 De-emphasis at TP4 vs. D[2..0] setting at 3Gb/s and 6Gb/s for PI2EQX6812




# **I2C Configuration Sequence**



#### Figure6 I2C WRITE Sequence Diagram

**Note:** there is one DUMMY byte to be added into sequence.



#### Figure7 I2C WRITE Sequence Sample








Figure8 I2C READ Sequence Diagram Note: there is NO DUMMY byte to be added into sequence.

Figure9 is one sample for read sequence sample at Address=C1 (A4, A1, A0 are pulled down) and Data byte[0..11]= 00 00 FE 00 00 FF FF FF FF FF FF FF FF FF EF 00.




Figure9 I2C READ Sequence Sample

Note: Byte0 means Channel-A2 has signal input.





# **Typical Application Circuit**

Figure10 shows typical application circuit of PI2EQX6812.




Figure10 Typical Application Circuit of PI2EQX6812

# **PCB Layout Sample**

Figure11 shows typical layout routing of PI2EQX6812.




Figure11 Typical Layout Routing of PI2EQX6812





Page 9

## Pericom SATA/SAS ReDriver Selection Table

					\			
ReDriver P/N	Protocol	Port	Channel	Configuration Control	Power, VCC	Package	Application Area	Remark
PI3EQX6701C	GATA 8 (GA 60	0		Pin Strap	1.2V +/-5%	TQFN20	Server/Storage, Workstation	Parlies 60 sizes has hime
	SATA3/SAS2	One	TX and RX	(EQ, 1dB or 4dB)	2.5~3.3V +/-5%	TQFN20	Server/Storage, workstation	Earlier 6G signal redriver
PI3EQX6701D	0.00.00.00	_		Pin Strap	1.2V+/-5%	TOPNOO	Server/Storage, Workstation	Particular CO since has himse
	SATA3/SAS2	One	TX and RX	(EQ, 7dB or 11dB)	2.5~3.3V +/-5%	TQFN20		Earlier 6G signal redriver
				Pin Strap	1.2V +/-5%			
PI3EQX6701E	SATA3/SAS2	One	TX and RX	(EQ, 1dB or 4dB at TX, 7dB	2.5~3.3V +/-5%	TQFN20	Server/Storage, Workstation	Earlier 6G signal redriver
				or 11dB at RX)	2.5-3.37 +/-576			
PISEOV6901	CATAS/CACO	One	TX and RX	Pin Strap	1.5V +/-5%	TQFN20	Server/Storage, Workstation	Pin compatible with 6701x
PI3EQX6801	SATA3/SAS2	One	IN and RA	(EQ, 4/8/16dB)	3.3V +/-10%	1QPh20	Server/Storage, Workstation	Pin companyie with 0701x
PI2EQX6811	SATA3/SAS2	One	TX and RX	Pin Strap (EQ, 4/8/16dB)	1 EV + / E04	TOPNOO	Desktop, Notebook, Docking	16 steps EQ at I2C/SMBus
FIZEQA0011	AUGII SAIAJ/SAS2		IN and KA	I2C/SMBus 1.5V +/-5%		TQFN20	Server/Storage, Workstation	To steps EQ at 12C/ SMBus
PI3EQX6741ST	SATA3	One	TX and RX	Pin Strap	3.3V +/-10%	TQFN20	Desktop, Notebook, Docking	Lower Power consumption
13507014131	SATAS	One	TA and RA	(EQ, 3/6/9dB)	3.37 1/-1076	1.01.120	Desktop, Notebook, Docking	Lower Power consumption
PI3EQX6741SL	SATA3	One	TX and RX	Pin Strap	1.05 V +/-5%	TQFN20	Desktop, Notebook, Docking	Lower VCC
195654195	SAIAS	One	IA and KA	(EQ, 3/6/9dB)	1.00 ( +/-0%	1.61.120	Desktop, Hotebook, Docking	Lower Power consumption
PI2EQX6812	SATA3/SAS2	Two	TX and RX	I2C/SMBus	1.2V +/-5%	TQFN42	Server/Storage, Workstation	Same Performance as PI2EQX6814
PIOPOV6904 A	SATA3/SAS2	Four	TX and RX	Pin Strap,	1.2V +/-5%	LFBGA100	Server/Storage, Workstation	Same Performance
PI2EQX6804-A S	SATAS/SAS2	rour	IN and KA	I2C/SMBus	1.20 +/-576	LFBGA100	Server/Storage, Workstation	(same control at I2C/SMBus for TX
PI2EQX6864-A	SATA3/SAS2	Four	TX and RX	I2C/SMBus	1.2V +/-5%	TQFN56	Server/Storage, Workstation	or RX Channel)
PIOPOV6914	SATA3/SAS2	52 Four	TX and RX	Pin Strap,	1.2V +/-5%	LFBGA100	Samer (Starage Werkstation	Same Performance
PI2EQX6814	SATAS/ SASZ	Four	TA and RA	I2C/SMBus,	1.20 7/-370	LFBGA100	Server/Storage, Workstation	(Channel by Channel control at
PI2EQX6874	SATA3/SAS2	Four	TX and RX	I2C/SMBus	1.2V +/-5%	TQFN56	Server/Storage, Workstation	I2C/SMBus for TX or RX Channel)





#### History

Version 1.0

Original Version

Nov. 13, 2012