



#### SURFACE MOUNT SCHOTTKY BARRIER DIODE

### **Product Summary**

V <sub>R</sub> (V)	I <sub>FM</sub> (mA)	V <sub>F MAX</sub> (V) @ 20mA, +25°C	I <sub>R MAX</sub> (μΑ) @ V <sub>R</sub> , +25°C
20			
30	350	0.37	5.0
40			

## **Description and Applications**

This Schottky barrier device has been designed to meet the stringent requirements of Automotive Applications. The devices are ideally suited to use as:

- Polarity protection diodes
- Re-circulating diodes
- Switching diodes

### **Features and Benefits**

- Low Forward Voltage Drop
- Guard Ring Construction for Transient Protection
- Negligible Reverse Recovery Time
- Low Reverse Capacitance
- Ultra-Small Surface Mount Package
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- This part is qualified to JEDEC standards (as references in AEC-Q) for High Reliability.

https://www.diodes.com/quality/product-definitions/

 An Automotive-Compliant Part is Available Under Separate Datasheet (SD103AWSQ - SD103BWSQ)

### **Mechanical Data**

• Package: SOD323

Package Material: Molded Plastic.
 UL Flammability Classification Rating 94V-0

Moisture Sensitivity: Level 1 per J-STD-020

 Terminals: Finish – Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 (3)

· Polarity: Cathode Band

Weight: 0.004 grams (Approximate)



Top View


### **Ordering Information** (Note 4)

Part Number	Doolsons	Packing		
Fait Number	Package	Qty.	Carrier	
SD103AWS-7-F	SOD323	3,000	Tape & Reel	
SD103BWS-7-F	SOD323	3,000	Tape & Reel	
SD103CWS-7-F	SOD323	3,000	Tape & Reel	


Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

# **Marking Information**



XX = Product Type Marking Code S4 &  $\overline{S}4$  =  $\underline{SD}103\underline{A}WS$ S5 or S4 &  $\overline{S}5$  or  $\underline{S}4$  =  $\underline{SD}103\underline{B}WS$ S6 or S5 or S4 &  $\overline{S}6$  or  $\overline{S}5$  or  $\overline{S}4$  =  $\overline{SD}103CWS$ 





## Maximum Ratings (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	SD103AWS	SD103BWS	SD103CWS	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	VRRM VRWM VR	40	30	20	V
RMS Reverse Voltage	VR(RMS)	28	21	14	V
Forward Continuous Current	IFM		350		mA
Non-Repetitive Peak Forward Surge Current  @ 8.3ms Half-Sine Waveform	IFSM		1.5		А

# **Thermal Characteristics**


Characteristic	Symbol	Value	Unit
Power Dissipation (Note 6)	PD	200	mW
Thermal Resistance, Junction to Ambient Air (Note 5)	RθJA	625	°C/W
Operating and Storage Temperature Range	T <sub>J</sub> , T <sub>STG</sub>	-65 to +125	°C

### Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)


Characteristic			Min	Тур	Max	Unit	Test Conditions
Reverse Breakdown Voltage (Note 6) SD103AWS SD103BWS SD103CWS		V <sub>(BR)R</sub>	40 30 20	_	_	٧	IR = 100µA IR = 100µA I <sub>R</sub> = 100µA
Forward Voltage Drop		VF	_	_	0.37 0.60	V	IF = 20mA IF = 200mA
Peak Reverse Current (Note 6) SD103AWS SD103BWS SD103CWS		I <sub>R</sub>	_	_	5.0	μΑ	V <sub>R</sub> = 30V V <sub>R</sub> = 20V V <sub>R</sub> = 10V
Total Capacitance		Ст	_	35	_	pF	V <sub>R</sub> = 0V, f = 1.0MHz
Reverse Recovery Time		t <sub>RR</sub>	_	10	_	ns	$I_F = I_R = 200 \text{mA},$ $I_{RR} = 0.1 \text{ x } I_R, R_L = 100 \Omega$

Notes:


- $5. \ \, \text{Device mounted on Alumina ceramic PC board, single-sided, 2oz copper pad area } 25 \text{mm}^2.$
- 6. Short duration test pulse used to minimize self-heating effect.




V<sub>F</sub>, INSTANTANEOUS FORWARD VOLTAGE (mV) Fig. 1 Typical Forward Characteristics










# **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### **SOD323**




SOD323					
Dim	Min	Max	Тур		
A1		0.10	0.05		
A2	1.00	1.10	1.05		
b	0.25	0.35	0.30		
С	0.10	0.15	0.11		
D	1.20	1.40	1.30		
Е	1.60	1.80	1.70		
He	2.30	2.70	2.50		
L	0.20	0.40	0.30		
а	00	8º			
All Dimensions in mm					

# **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### SOD323



Dimensions	Value (in mm)		
Х	0.590		
X1	2.700		
Υ	0.450		



#### **IMPORTANT NOTICE**

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at <a href="https://www.diodes.com/about/company/terms-and-conditions/important-notice">https://www.diodes.com/about/company/terms-and-conditions/important-notice</a>

DIODES is a trademark of Diodes Incorporated in the United States and other countries. The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. © 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com