

IntelliFET®

New Product Announcement ZXMS82090S14PQ ZXMS82120S14PQ ZXMS82180S14PQ

Dual-Channel, High-Side Power Switches Provide Combined Protection for High Inrush Current Loads

The ZXMS82xxxS14PQ series of **IntelliFETs** consists of automotive-compliant, dual-channel, intelligent, high-side power switches designed to handle high inrush current loads while offering robust protection for both the device itself and the connected load.

This protection, from the integrated controller, extends to various potentially damaging events, such as overvoltage, overtemperature, short circuit, and electrostatic discharge.

These switches are particularly well-suited for driving automotive loads, encompassing inductive, capacitive, and resistive loads.

Each device features vertical DMOS MOSFETs with respective R_{DS(ON)} (Typ. @25°C):

- ZXMS82090S14PQ 75mΩ
- ZXMS82120S14PQ 100mΩ
- ZXMS82180S14PQ 150mΩ

The onboard diagnostics detect fault conditions and self-protection events, including open load, overload, and overtemperature shutdown.

Additional protection for reverse polarity and loss of ground is easily implemented with minimal additional components.

The ZXMS82xxxS14PQ series is available in the thermally efficient SO-14EP package with exposed underside heatsink.

Automotive-compliant - AEC qualified, manufactured in IATF 16949 certified sites supporting PPAP documents.

IntelliFET is a registered trademark of Diodes Incorporated in the United Kingdom and other countries.

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.

All other trademarks are the property of their respective owners.

© 2024 Copyright Diodes Incorporated. All Rights Reserved.



The DIODES Advantage

The ZXMS82xxxS14PQ series of IntelliFETs provides a compact dual-channel solution to safely drive automotive loads.

- Overvoltage Protection, Including Load Dump
 Protects the device if the battery voltage exceeds the clamp voltage
- Overtemperature Protection with Auto-Restart
 Thermal shutdown when TJ max is reached during overload condition
- Reverse Polarity Protection*
 Protects the device should battery supply be accidentally reversed
- Voltage Dependent Current Limiting
 Protects the device and the load from an overcurrent condition
- Loss of Ground Protection*
 Protects the device and leaves the load OFF should the ground connection be lost
- Diagnostics Using Current Sense
 Enables measurement of load current, monitoring of overall application state, and detection of open load conditions

Applications

*using minimal external components


- 12V Automotive loads
- LEDs
- Bulbs
- Actuators
- Lighting systems
- Resistive, inductive, and capacitive loads
- Motors in automotive body control
- Relay, fuse, and discrete circuit replacement

diodes.com



New Product Announcement ZXMS82090S14PQ ZXMS82120S14PQ ZXMS82180S14PQ

Typical Application



Product Portfolio

Part Number	Channels	R _{DS(ON)} @ TJ = 25°C (Typ)	R _{DS(ON)} @ TJ = +150°C (Max)	I _{L(NOM)} One Channel	I _{L(NOM)} Both Channels	Eas max	Package
		mΩ	mΩ	Α	Α	mJ	
ZXMS82090S14PQ	2	75	180	3.5	2.5	42	SO-14EP
ZXMS82120S14PQ	2	100	240	2.5	2	15	SO-14EP
ZXMS82180S14PQ	2	150	360	2	1.5	30	SO-14EP

Ordering Information

Orderable Part Number	Compliance (Only Automotive	Packing		
Orderable Part Number	Supports PPAP)	Quantity	Carrier	
ZXMS82090S14PQ-13	Automotive	2,500	Tape & Reel	
ZXMS82120S14PQ-13	Automotive	2,500	Tape & Reel	
ZXMS82180S14PQ-13	Automotive	2,500	Tape & Reel	