

AP61200/AP61201/AP61202/AP61203

2.3V TO 5.5V INPUT. 2A LOW IQ SYNCHRONOUS BUCK CONVERTER

Description

The DIODESTM AP61200 / DIODESTM AP61201 / DIODESTM AP61202 / DIODESTM AP61203 is a 2A, synchronous buck converter with a wide input voltage range of 2.3V to 5.5V. The device fully integrates a $110m\Omega$ high-side power MOSFET and an $80m\Omega$ low-side power MOSFET to provide high-efficiency step-down DC-DC conversion.


The AP61200/AP61201/AP61202/AP61203 device is easily used by minimizing the external component count due to its adoption of Constant On-Time (COT) control to achieve fast transient response, easy loop stabilization, and low output voltage ripple.

The device is available in a SOT563 package.

Features

- VIN: 2.3V to 5.5V
- Output Voltage (VOUT): 0.6V to 3.6V
- 2A Continuous Output Current
- 0.6V ± 2% Reference Voltage
- 19µA Low Quiescent Current (Pulse Frequency Modulation)
- 1.3MHz Switching Frequency (VIN = 5V, VOUT = 1.8V)
- Up to 89% Efficiency at 5mA Light Load
- Operation Mode Options
 - Pulse Frequency Modulation: AP61200 and AP61202
 - Force Pulse Width Modulation: AP61201 and AP61203
- Power-Good Indicator
 - AP61202 and AP61203
- Protection Circuitry
 - Undervoltage Lockout (UVLO)
 - VIN Overvoltage Protection (OVP)
 - Peak Current Limit
 - Valley Current Limit
 - Thermal Shutdown
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

Pin Assignments



Applications

- 5V distributed power bus supplies
- · White goods and small home appliances
- FPGA, DSP, and ASIC supplies
- Network video cameras
- · Wireless routers
- Consumer electronics
- General purpose point of loads

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



Typical Application Circuit




Figure 1. Typical AP61200/AP61201 Application Circuit

Figure 2. Typical AP61202/AP61203 Application Circuit (OUT as No Connection for AP61200/AP61201)




Figure 3. AP61200/AP61202 Efficiency vs. Output Current




Figure 4. PWM Efficiency vs. Output Current



Pin Descriptions

Pin Name	Pin Number	Function
FB 1		Feedback sensing terminal for the output voltage. Connect this pin to the resistive divider of the output.
1.5	'	See Setting the Output Voltage section for more details.
GND	2	Power Ground.
		Power Input. VIN supplies the power to the IC as well as the step-down converter power MOSFETs. Drive
VIN	3	VIN with a 2.3V to 5.5V power source. Bypass VIN to GND with a suitably large capacitor to eliminate noise
		due to the switching of the IC. See Input Capacitor section for more details.
SW	1	Power Switching Output. SW is the switching node that supplies power to the output. Connect the output LC
300	4	filter from SW to the output load.
EN	5	Enable Input. EN is a digital input that turns the regulator on or off. Drive EN high to turn on the regulator and
LIN	3	low to turn it off.
OUT		Output Voltage Power Rail. Connect OUT to the output load as shown in Figure 1. OUT cannot be tied to
(AP61200/AP61201)		GND but can be treated as a No Connect pin and left floating. If left floating, then a feed-forward capacitor,
(AF01200/AF01201)	6	C3, must be used as shown in Figure 2.
PG		Power-Good. Open drain power-good output that is pulled to GND when the output voltage is out of its
(AP61202/AP61203)		regulation limits or during soft-start.

Functional Block Diagram




Figure 5. Functional Block Diagram



Absolute Maximum Ratings (Note 4) (@ TA = +25°C, unless otherwise specified.)

Symbol	Parameter	Rating	Unit			
VIN	Supply Pin Voltage	-0.3 to +6.5 (DC)	V			
VIIV	Supply I III Voltage	-0.3 to +7.0 (400ms)	v			
V _{FB}	Feedback Pin Voltage	-0.3 to VIN + 0.3	V			
Vsw	Switch Pin Voltage	-1.0 to VIN + 0.3 (DC)	V			
VSW	Switch Fill Voltage	-2.5 to VIN + 2.0 (20ns)	V			
V _{EN}	Enable Pin Voltage	-0.3 to VIN + 0.3	V			
VOUT	Output Pin Voltage	-0.3 to +6.0 (DC)	V			
(AP61200/AP61201)	Output i iii voltage	-0.5 to +0.0 (DC)	V			
V _P G	Power-Good Pin Voltage	-0.3 to +6.0 (DC)	V			
(AP61202/AP61203)	Towar Cood Firm Vollago	0.0 to 10.0 (20)	·			
T _{ST}	Storage Temperature	-65 to +150	°C			
TJ	Junction Temperature	+160	°C			
TL	Lead Temperature	+260	°C			
ESD Susceptibility (No	ESD Susceptibility (Note 5)					
HBM	Human Body Model	±2000	V			
CDM	Charged Device Model	±1000	V			

Notes:

Thermal Resistance (Note 6)

Symbol	Parameter	Rat	ing	Unit
θја	Junction to Ambient	SOT563	141	°C/W
θЈС	Junction to Case	SOT563	33	°C/W

Note:

Recommended Operating Conditions (Note 7) (@ T_A = +25°C, unless otherwise specified.)

Symbol	Parameter	Min	Max	Unit
VIN	Supply Voltage	2.3	5.5	V
VOUT	Output Voltage	0.6	3.6	V
TA	Operating Ambient Temperature	-40	+85	°C
TJ	Operating Junction Temperature	-40	+125	°C

Note:

7. The device function is not guaranteed outside of the recommended operating conditions.

^{4.} Stresses greater than the Absolute Maximum Ratings specified above can cause permanent damage to the device. These are stress ratings only; functional operation of the device at these or any other conditions exceeding those indicated in this specification is not implied. Device reliability can be affected by exposure to absolute maximum rating conditions for extended periods of time.

^{5.} Semiconductor devices are ESD sensitive and can be damaged by exposure to ESD events. Suitable ESD precautions should be taken when handling and transporting these devices.

^{6.} Test condition for SOT563: Device mounted on FR-4 substrate, two-layer PCB, 2oz copper, with minimum recommended pad layout.




Electrical Characteristics (@ T_J = +25°C, VIN = 5V, unless otherwise specified. Min/Max limits apply across the recommended operating junction temperature range, -40°C to +125°C, and input voltage range, 2.3V to 5.5V, unless otherwise specified.)

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Ishdn	Shutdown Supply Current	VEN = 0V	_	0.1	_	μA
1-	Outgoont Supply Current	PFM, V _{FB} = 0.65V	_	19	_	μA
ΙQ	Quiescent Supply Current	PWM, V _{FB} = 0.65V	_	620	_	μA
POR	VIN Power-on Reset Rising Threshold	_	_	2.00	2.25	V
UVLO	VIN Undervoltage Lockout Falling Threshold	_	_	1.84	_	V
OVPvin	VIN Overvoltage Rising Threshold	_	_	6.3	_	V
OVP _{VIN_HYS}	VIN Overvoltage Hysteresis	_	_	300	_	mV
RDS(ON)1	High-Side Power MOSFET On-Resistance (Note 8)	_	_	110	_	mΩ
RDS(ON)2	Low-Side Power MOSFET On-Resistance (Note 8)	_	_	80	_	mΩ
I _{PEAK_LIMIT}	HS Peak Current Limit (Note 8)	From Source to Drain	2.4	3.2	_	Α
IVALLEY_LIMIT	LS Valley Current Limit (Note 8)	From Source to Drain	_	2.3	_	Α
fsw	Oscillator Frequency	VOUT = 1.8V, CCM	_	1.3	_	MHz
ton_min	Minimum On-Time	_	_	70	_	ns
toff_min	Minimum Off-Time	_	_	70	_	ns
V _{FB}	Feedback Voltage	ССМ	0.588	0.600	0.612	V
V _{EN_} H	EN Logic High Threshold	_	_	0.91	_	V
V _{EN_L}	EN Logic Low Threshold	_	_	0.83	_	V
tss	Soft-Start Time	_	_	0.5	_	ms
PGuv_fall	Undervoltage Falling Threshold	AP61202/AP61203, Percent of Output Regulation, Fault	_	90	_	%
PGuv_rise	Undervoltage Rising Threshold	AP61202/AP61203, Percent of Output Regulation, Good	_	95	_	%
PGov_rise	Overvoltage Rising Threshold	AP61202/AP61203, Percent of Output Regulation, Fault	_	110	_	%
PGov_fall	Overvoltage Falling Threshold	AP61202/AP61203, Percent of Output Regulation, Good	_	105	_	%
tpg_rd	Power-Good Rise Delay Time	AP61202/AP61203	_	55	_	μs
Vpg_ol	Power-Good Output Logic Low	AP61202/AP61203, I _{PG} = -1mA	_	_	0.4	٧
Rpg	Power-Good Pull-Up Resistor	AP61202/AP61203	_	5	_	mΩ
T _{SD}	Thermal Shutdown (Note 8)	_	_	+160	_	°C
T _{Hys}	Thermal Shutdown Hysteresis (Note 8)	_	_	+30	_	°C

Note: 8. Compliance to the datasheet limits is assured by one or more methods: production test, characterization, and/or design.



Typical Performance Characteristics (AP61200/AP61201/AP61202/AP61203 @ $T_A = +25$ °C, VIN = 5V, VOUT = 1.8V, BOM = Table 1, unless otherwise specified.)







Figure 6. Power MOSFET RDS(ON) vs. Temperature

Figure 7. V_{FB} vs. Temperature







Figure 8. I_{SHDN} vs. Temperature

Figure 9. VIN Power-On Reset and UVLO vs. Temperature




Typical Performance Characteristics (AP61200/AP61202 @ TA = +25°C, VIN = 5V, VOUT = 1.8V, BOM = Table 1, unless otherwise specified.)



VOUT = 3.3V, L = 1μH — $-VOUT = 1.8V, L = 1\mu H$ 100 95 90 Efficiency (%) 85 80 75 70 65 60 55 50 0.001 0.010 1.000 0.100 10.000 IOUT (A)

Figure 10. Efficiency vs. Output Current, VIN = 3.3V

Figure 11. Efficiency vs. Output Current, VIN = 5V







Figure 12. Line Regulation

Figure 13. Load Regulation







Figure 14. IQ vs. Temperature

Figure 15. fsw vs. Load



Typical Performance Characteristics (AP61200/AP61202 @ T_A = +25°C, VIN = 5V, VOUT = 1.8V, BOM = Table 1, unless otherwise specified.) (continued)



VOUT (10mV/div)


IL (1A/div)

Vsw (5V/div)

1µs/div

Figure 16. Output Voltage Ripple, IOUT = 50mA

Figure 17. Output Voltage Ripple, IOUT = 2A






Figure 18. Load Transient, IOUT = 50mA to 500mA to 50mA

Figure 19. Load Transient, IOUT = 1A to 2A to 1A




Figure 20. Load Transient, IOUT = 50mA to 2A to 50mA



Typical Performance Characteristics (AP61201/AP61203 @ TA = +25°C, VIN = 5V, VOUT = 1.8V, BOM = Table 1, PWM, unless otherwise specified.)




Figure 21. Efficiency vs. Output Current, VIN = 3.3V




Figure 23. Line Regulation




Figure 25. IQ vs. Temperature




Figure 22. Efficiency vs. Output Current, VIN = 5V




Figure 24. Load Regulation





Figure 26. f_{SW} vs. Temperature, IOUT = 0A




Typical Performance Characteristics (AP61201/AP61203 @ TA = +25°C, VIN = 5V, VOUT = 1.8V, BOM = Table 1, PWM, unless otherwise specified.) (continued)



VOUTAC (10mV/div) I∟ (1A/div) Vsw (5V/div)

Figure 27. fsw vs. Load

Figure 28. Output Voltage Ripple, IOUT = 50mA






Figure 29. Output Voltage Ripple, IOUT = 2A

Figure 30. Load Transient, IOUT = 50mA to 500mA to 50mA




Figure 31. Load Transient, IOUT = 1A to 2A to 1A

Figure 32. Load Transient, IOUT = 50mA to 2A to 50mA



Typical Performance Characteristics (AP61200/AP61201 @ T_A = +25°C, VIN = 5V, VOUT = 1.8V, BOM = Table 1, unless otherwise specified.)




Figure 33. Startup Using EN, IOUT = 2A

Figure 34. Shutdown Using EN, IOUT = 2A




Figure 35. Output Short Protection, IOUT = 2A

Figure 36. Output Short Recovery, IOUT = 2A



Typical Performance Characteristics (AP61202/AP61203 @ T_A = +25°C, VIN = 5V, VOUT = 1.8V, BOM = Table 1, unless otherwise specified.)




Figure 37. Startup Using EN, IOUT = 2A

Figure 38. Shutdown Using EN, IOUT = 2A




Figure 39. Output Short Protection, IOUT = 2A

Figure 40. Output Short Recovery, IOUT = 2A



Application Information

1 Pulse Width Modulation (PWM) Operation

The AP61200/AP61201/AP61202/AP61203 device is a 2.3V-to-5.5V input, 2A output, fully integrated synchronous buck converter. Refer to the block diagram in Figure 5. The device employs constant on-time control to provide fast transient response and easy loop stabilization. At the beginning of each cycle, the one-shot pulse turns on the high-side power MOSFET, Q1, for a fixed on-time, ton. This one-shot on-pulse timing is calculated by the converter's input voltage and output voltage to maintain a pseudo-fixed frequency over the input voltage range. When Q1 is on, the inductor current rises linearly and the device charges the output capacitor. Q1 turns off after the fixed on-time expires, and the low-side power MOSFET, Q2, turns on. Once the output voltage drops below the output regulation, Q2 turns off. The one-shot timer is then reset and Q1 turns on again. The on-time is inversely proportional to the input voltage and directly proportional to the output voltage. It is calculated by the following equation:

$$\mathbf{t_{ON}} = \frac{\mathbf{VOUT}}{\mathbf{VIN} \cdot \mathbf{f_{SW}}}$$
 Eq. 1

Where:

- VIN is the input voltage
- VOUT is the output voltage
- fsw is the switching frequency

The off-time duration is tope and starts after the on-time expires. The off-time expires when the feedback voltage decreases below the reference voltage, which then triggers the on-time duration to start again. The minimum off-time is 70ns typical.

2 Pulse Frequency Modulation (PFM) Operation

The AP61200/AP61202 enters PFM operation at light load conditions for high efficiency during light load conditions, the regulator automatically reduces the switching frequency. As the output current decreases, so too does the inductor current. The inductor current, I_L , eventually reaches 0A, marking the boundary between Continuous Conduction Mode (CCM) and Discontinuous Condition Mode (DCM). During this time, both Q1 and Q2 are off, and the load current is provided only by the output capacitor. When V_{FB} becomes lower than 0.6V, the next cycle begins, and Q1 turns on. Because the AP61200/AP61202 can work in PFM during light load conditions, it can achieve power efficiency of up to 89% at a 5mA load condition.

Likewise, as the output load increases from light load to heavy load, the switching frequency increases to maintain the regulation of the output voltage. The transition point between light and heavy load conditions can be calculated using the following equation:

$$I_{LOAD} = \left(\frac{VIN - VOUT}{2L}\right) \cdot t_{ON} \tag{Eq. 2}$$

Where:

• L is the inductor value

The quiescent current of AP61200/AP61202 is 19µA typical under a no-load, non-switching condition.

3 Enable

When disabled, the device shutdown supply current is only 0.1μ A. When applying a voltage greater than the EN logic high threshold (typical 0.91V, rising), the AP61200/AP61201/AP61202/AP61203 enables all functions and the device initiates the soft-start phase. The AP61200/AP61202/AP61203 has a built-in 0.5ms soft-start time to prevent output voltage overshoot and inrush current. When the EN voltage falls below its logic low threshold (typical 0.83V, falling), the internal SS voltage discharges to ground and device operation disables.



4 Power-Good (PG) Indicator (AP61202/AP61203)

The PG pin of AP61202/AP61203 is an open-drain output that is actively held low during the soft-start period until the output voltage reaches 95% of its target value. When the output voltage is outside of its regulation by $\pm 10\%$, PG pulls low until the output returns within 5% of its set value. The PG rising edge transition is delayed by 55 μ s. The PG pin is connected to VIN through an internal 5M Ω pull-up resistor.

5 Undervoltage Lockout (UVLO) and Input Overvoltage Protection (OVP)

Undervoltage lockout is implemented to protect the IC from insufficient input voltages. The AP61200/AP61201/AP61202/AP61203 disables if the input voltage falls below 1.84V. In this UVLO event, both the high-side and low-side power MOSFETs turn off and the $1k\Omega$ active discharge enables to discharge the output voltage to ground.

Similarly, input overvoltage protection is implemented to protect the IC from excess input voltages. The AP61200/AP61201/AP61202/AP61203 disables if the input voltage rises above 6.3V. In this OVP event, both the high-side and low-side power MOSFETs turn off and the $1k\Omega$ active discharge enables to discharge the output voltage to ground.

6 Overcurrent Protection (OCP)

The AP61200/AP61201/AP61202/AP61203 has cycle-by-cycle valley current limit protection by sensing the current through the internal low-side power MOSFET, Q2. While Q2 is on, the internal sensing circuitry monitors its conduction current. The overcurrent limit has a corresponding voltage limit, VLIMIT. When the voltage between GND and SW is lower than VLIMIT due to excessive current through Q2, the OCP triggers, and the controller turns off Q2. During this time, both Q1 and Q2 remain off. A new switching cycle begins only when the voltage between GND and SW rises above VLIMIT. If Q2 consistently hits the valley current limit for 0.6ms, the buck converter enters hiccup mode and shuts down. After 3.4ms of down time, the buck converter restarts powering up. Hiccup mode reduces the power dissipation in the overcurrent condition.

The AP61200/AP61201/AP61202/AP61203 also has cycle-by-cycle peak current limit protection by sensing the current through the internal high-side power MOSFET, Q1, through a similar mechanism as the cycle-by-cycle valley current limit protection.

Because the R_{DS(ON)} values of the power MOSFETs increase with temperature, V_{LIMIT} has a temperature coefficient of 0.4%/°C to compensate for the temperature dependency of R_{DS(ON)}.

7 Thermal Shutdown (TSD)

If the junction temperature of the device reaches the thermal shutdown limit of +160°C, the AP61200/AP61201/AP61202/AP61203 shuts down both its high-side and low-side power MOSFETs and triggers the output active discharge. When the junction temperature reduces to the required level (+130°C typical), the device initiates a normal power-up cycle with soft-start.



8 Power Derating Characteristics

To prevent the regulator from exceeding the maximum recommended operating junction temperature, some thermal analysis is required. The regulator's temperature rise is given by:

$$T_{RISE} = PD \cdot (\theta_{IA})$$
 Eq. 3

Where:

- · PD is the power dissipated by the regulator
- θ_{JA} is the thermal resistance from the junction of the die to the ambient temperature

The junction temperature, TJ, is given by:

$$T_{I} = T_{A} + T_{RISE}$$
 Eq. 4

Where:

• TA is the ambient temperature of the environment

For the SOT563 package, the θ_{JA} is 141°C/W. The actual junction temperature should not exceed the maximum recommended operating junction temperature of +125°C when considering the thermal design. Figure 41 shows a typical derating curve versus ambient temperature.




Figure 41. Output Current Derating Curve vs. Ambient Temperature, VIN = 5V



9 Setting the Output Voltage

The AP61200/AP61201/AP61202/AP61203 has adjustable output voltages starting from 0.6V using an external resistive divider. The resistor values of the feedback network are selected based on a design trade-off between efficiency and output voltage accuracy. There is less current consumption in the feedback network for high resistor values, which improves efficiency at light loads. However, values too high cause the device to be more susceptible to noise affecting its output voltage accuracy. R2 can be determined by the following equation:

$$R2 = \frac{0.6 \cdot R1}{VOUT - 0.6V}$$
 Eq. 5

Table 1 shows a list of recommended component selections for common AP61200/AP61201/AP61202/AP61203 output voltages referencing Figure 1 and Figure 2.

AP61200/AP61201/AP61202/AP61203							
C3 (pF)							
Output Voltage (V)	R1 (kΩ)	R2 (kΩ)	L (µH)	C1 (µF)	C2 (µF)	AP61200 AP61201	AP61202 AP61203
1.0	200.0	301.0	1.0	10	10	OPEN	33
1.2	200.0	200.0	1.0	10	10	OPEN	33
1.5	200.0	133.0	1.0	10	10	OPEN	33
1.8	200.0	100.0	1.0	10	10	OPEN	33
2.5	200.0	63.2	1.0	10	10	OPEN	33
3.3	200.0	44.2	1.0	10	10	OPEN	33

Table 1. Recommended Component Selections

10 Inductor

Calculating the inductor value is a critical factor in designing a buck converter. For most designs, the following equation can be used to calculate the inductor value:

$$L = \frac{VOUT \cdot (VIN - VOUT)}{VIN \cdot \Delta I_L \cdot f_{SW}} \label{eq:loss}$$
 Eq. 6

Where:

- ΔI_L is the inductor current ripple
- · fsw is the buck converter switching frequency

For AP61200/AP61201/AP61202/AP61203, choose ∆I_L to be 30% to 50% of the maximum load current of 2A.

The inductor peak current is calculated by:

$$I_{L_{PEAK}} = I_{LOAD} + \frac{\Delta I_{L}}{2}$$
 Eq. 7

Peak current determines the required saturation current rating, which influences the size of the inductor. Saturating the inductor decreases the converter efficiency while increasing the temperatures of the inductor and the internal power MOSFETs. Therefore, choosing an inductor with the appropriate saturation current rating is important. For most applications, it is recommended to select an inductor of approximately 1.0μ H to 1.5μ H with a DC current rating of at least 35% higher than the maximum load current. For highest efficiency, the inductor's DC resistance should be less than $50m\Omega$. Use a larger inductance for improved efficiency under light load conditions.



11 Input Capacitor

The input capacitor reduces both the surge current drawn from the input supply as well as the switching noise from the device. The input capacitor must sustain the ripple current produced during the on-time of Q1. It must have a low ESR to minimize power dissipation due to the RMS input current.

The RMS current rating of the input capacitor is a critical parameter and must be higher than the RMS input current. As a rule of thumb, select an input capacitor with a RMS current rating greater than half of the maximum load current.

Due to large dl/dt through the input capacitor, electrolytic or ceramic capacitors with low ESR should be used. If using a tantalum capacitor, it must be surge protected or else capacitor failure could occur. Using a ceramic capacitor of 10µF or greater is sufficient for most applications.

12 Output Capacitor

The output capacitor keeps the output voltage ripple small, ensures feedback loop stability, and reduces both the overshoots and undershoots of the output voltage during load transients. During the first few microseconds of an increasing load transient, the converter recognizes the change from steady-state and sets the off-time to minimum to supply more current to the load. However, the inductor limits the change to increasing current depending on its inductance. Therefore, the output capacitor supplies the difference in current to the load during this time. Likewise, during the first few microseconds of a decreasing load transient, the converter recognizes the change from steady-state and increases the off-time to reduce the current supplied to the load. However, the inductor limits the change in decreasing current as well. Therefore, the output capacitor absorbs the excess current from the inductor during this time.

The effective output capacitance, COUT, requirements can be calculated from the equations below.

The ESR of the output capacitor dominates the output voltage ripple. The amount of ripple can be calculated by:

$$VOUT_{Ripple} = \Delta I_L \cdot \left(ESR + \frac{1}{8 \cdot f_{SW} \cdot COUT}\right)$$
 Eq. 8

An output capacitor with large capacitance and low ESR is the best option. For most applications, a 10µF to 22µF ceramic capacitor is sufficient. To meet the load transient requirements, the calculated COUT should satisfy the following inequality:

$$COUT > max \left(\frac{L \cdot I_{Trans}^2}{\Delta V_{Overshoot} \cdot VOUT}, \frac{L \cdot I_{Trans}^2}{\Delta V_{Undershoot} \cdot (VIN - VOUT)} \right)$$
 Eq. 9

Where:

- I_{Trans} is the load transient
- ΔV_{Overshoot} is the maximum output overshoot voltage
- ΔV_{Undershoot} is the maximum output undershoot voltage



Layout

PCB Layout

- 1. The AP61200/AP61201/AP61202/AP61203 works at 2A load current so heat dissipation is a major concern in the layout of the PCB. 2oz copper for both the top and bottom layers is recommended.
- 2. Place the input capacitors as closely across VIN and GND as possible.
- 3. Place the inductor as close to SW as possible.
- 4. Place the output capacitors as close to GND as possible.
- 5. Place the feedback components as close to FB as possible.
- 6. If using four or more layers, use at least the 2nd and 3rd layers as GND to maximize thermal performance.
- 7. Add as many vias as possible around both the GND pin and under the GND plane for heat dissipation to all the GND layers.
- 8. Add as many vias as possible around both the VIN pin and under the VIN plane for heat dissipation to all the VIN layers.
- 9. See Figure 42 and Figure 43 for more details.




Figure 42. Recommended AP61200/AP61201 PCB Layout





Figure 43. Recommended AP61202/AP61203 PCB Layout




Ordering Information



Part Number	Part Number Mode Function Package Package Code		Mode	Function Package Package Cod		Pack	ing
Fait Number	Wiode	runction	Package	ackage Package Code	Qty.	Carrier	
AP61200Z6-7	PFM	_	SOT563	Z6	3,000	7" Tape and Reel	
AP61201Z6-7	PWM	_	SOT563	Z6	3,000	7" Tape and Reel	
AP61202Z6-7	PFM	PG	SOT563	Z6	3,000	7" Tape and Reel	
AP61203Z6-7	PWM	PG	SOT563	Z6	3,000	7" Tape and Reel	

Marking Information

SOT563



XX: Identification Code

<u>Y</u> : Year 0~9

W: Week: A~Z: 1~26 week; a~z: 27~52 week; z represents


52 and 53 week X: Internal Code

Part Number	Package	Identification Code
AP61200Z6-7	SOT563	НМ
AP61201Z6-7	SOT563	GP
AP61202Z6-7	SOT563	HN
AP61203Z6-7	SOT563	GR



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.




	SOT563						
Dim	Min	Max	Тур				
Α	0.55	0.60					
b	0.15	0.30	0.20				
С	0.10	0.18	0.11				
D	1.50	1.70	1.60				
E	1.55	1.70	1.60				
E1	1.10	1.25	1.20				
е			0.50				
e1	0.90	1.10	1.00				
L	0.10	0.30	0.20				
а	8°	9°	7°				
All	Dimens	sions in	mm				

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT563



Dimensions	Value (in mm)
С	0.500
C1	1.270
G	0.600
Х	0.300
X1	1.300
Υ	0.670
Y1	1.940

Mechanical Data

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.003 grams (Approximate)



IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

DIODES is a trademark of Diodes Incorporated in the United States and other countries.

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.

© 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com