

SINGLE 2 INPUT POSITIVE NOR GATE

Description

The 74LVC1G02 is a single 2-input positive NOR gate with a standard push-pull output. The device is designed for operation with a power supply range of 1.65V to 5.5V. The inputs are tolerant to 5.5V allowing this device to be used in a mixed-voltage environment. The device is fully specified for partial power down applications using $I_{\rm OFF}$. The $I_{\rm OFF}$ circuitry disables the output preventing damaging current backflow when the device is powered down.


The gate performs the positive Boolean function:

$$Y = \overline{A + B} \text{ or } Y = \overline{A} \bullet \overline{B}$$

Features

- Wide Supply Voltage Range from 1.65 to 5.5V
- ± 24mA Output Drive at 3.3V
- CMOS low power consumption
- I_{OFF} Supports Partial-Power-Down Mode Operation
- Inputs accept up to 5.5V
- ESD Protection Tested per JESD 22
 - Exceeds 200-V Machine Model (A115)
 - Exceeds 2000-V Human Body Model (A114)
 - Exceeds 1000-V Charged Device Model (C101)
- Latch-Up Exceeds 100mA per JESD 78, Class I
- Range of Package Options
- Direct Interface with TTL Levels
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

Pin Assignments



Applications

- Voltage level shifting
- General-purpose logic
- Power down signal isolation
- Wide array of products such as:
 - PCs, networking, notebooks, netbooks, PDAs
 - Tablet computers, E-readers
 - Computer peripherals, hard drives, CD/DVD ROM
 - TV, DVD, DVR, set top boxes
 - Cell phones, personal navigation / GPS
 - MP3 players ,cameras, video recorders


Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

74LVC1G02 1 of 16
Document number: DS32197 Rev. 11 - 2 www.diodes.com



Ordering Information (Note 4)



Orderable	Package	Package	Package		Packing	
Part Number	Code	(Notes 5 & 6)	Size	Quantity	Carrier	Part Number Suffix
74LVC1G02W5-7	W5	SOT25	3.0mm x 2.8mm x 1.2mm 0.95 mm lead pitch	3,000	7" Tape & Reel	-7
74LVC1G02SE-7	SE	SOT353	2.0mm x 2.0mm x 1.1mm 0.65 mm lead pitch	3,000	7" Tape & Reel	-7
74LVC1G02Z-7	Z	SOT553	1.6mm x 1.6 mm x 0.62mm 0.5 mm lead pitch	4,000	7" Tape & Reel	-7
74LVC1G02FS3-7	FS3	X2-DFN0808-4	0.8mm x 0.8 mm x 0.35mm 0.5 mm pad pitch (diamond)	5,000	7" Tape & Reel	-7
74LVC1G02FW5-7	FW5	X1-DFN1010-6 (Type B)	1.0mm x 1.0mm x 0.5mm 0.35 mm pad pitch	5,000	7" Tape & Reel	-7
74LVC1G02FW4-7	FW4	X2-DFN1010-6	1.0mm x 1.0mm x 0.4mm 0.35 mm pad pitch	5,000	7" Tape & Reel	-7
74LVC1G02FX4-7	FX4	X2-DFN1409-6 Chip scale alternative	1.4mm x 0.9mm x 0.4mm 0.5 mm pad pitch	5,000	7" Tape & Reel	-7
74LVC1G02FZ4-7	FZ4	X2-DFN1410-6	1.4mm x 1.0mm x 0.4mm 0.5 mm pad pitch	5,000	7" Tape & Reel	-7


Notes:

- For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.
 Pad layout as shown in our suggested pad layouts, which can be found on our website at see http://www.diodes.com/package-outlines.html.
 The taping orientation is located on our website at http://www.diodes.com/datasheets/ap02007.pdf.

Pin Descriptions

Pin Name	Description
А	Data Input
В	Data Input
GND	Ground
Υ	Data Output
Vcc	Supply Voltage
NC	No Connection

Logic Diagram



Function Table

Inp	Output	
Α	В	Υ
Н	Х	L
Х	Н	L
L	L	Н



Absolute Maximum Ratings (Notes 7 & 8)

Symbol	Description	Rating	Unit
ESD HBM	Human Body Model ESD Protection	2	kV
ESD CDM	Charged Device Model ESD Protection	1	kV
ESD MM	Machine Model ESD Protection	200	V
Vcc	Supply Voltage Range	-0.5 to 6.5	V
VI	Input Voltage Range	-0.5 to 6.5	V
Vo	Voltage applied to output in high impedance or I _{OFF} state	-0.5 to 6.5	V
Vo	Voltage applied to output in high or low state.	-0.5 to V _{CC} +0.5	V
lıĸ	Input Clamp Current V _I < 0	-50	mA
lok	Output Clamp Current	-50	mA
I _O	Continuous output current	±50	mA
I _{CC} , I _{GND}	Continuous current through V _{CC} or GND	±100	mA
TJ	Operating Junction Temperature	-40 to +150	°C
T _{STG}	Storage Temperature	-65 to +150	°C

Notes:

- 7. Stresses beyond the absolute maximum may result in immediate failure or reduced reliability. These are stress values and device operation should be within recommend values.
- 8. Forcing the maximum allowed voltage could cause a condition exceeding the maximum current or conversely forcing the maximum current could cause a condition exceeding the maximum voltage. The ratings of both current and voltage must be maintained within the controlled range.

Recommended Operating Conditions (Note 9)

Symbol		Parameter	Min	Max	Unit	
Vaa	Operating Voltage	Operating	1.65	5.5	V	
V _{CC}	Operating voltage	Data retention only	1.5	_	V	
		$V_{CC} = 1.65V$ to 1.95V	0.65 x V _{CC}	_		
VIH	High-Level Input Voltage	$V_{CC} = 2.3V$ to 2.7V	1.7	_	V	
VIH	Trigit-Level input voltage	$V_{CC} = 3V$ to 3.6V	2	_	ď	
		$V_{CC} = 4.5V \text{ to } 5.5V$	0.7 x V _{CC}	_		
		V _{CC} = 1.65V to 1.95V	_	0.35 x V _{CC}		
.,	Low Lovel Input Voltage	V _{CC} = 2.3V to 2.7V	_	0.7	.,	
V_{IL}	Low-Level Input Voltage	V _{CC} = 3V to 3.6 V	_	0.8	V	
		V _{CC} = 4.5V to 5.5V	_	0.3 x V _{CC}]	
VI	Input Voltage	·	0	5.5	V	
Vo	Output Voltage		0	Vcc	V	
		V _{CC} = 1.65V	_	-4		
		V _{CC} = 2.3V	_	-8]	
,	High-Level Output Current	V _{CC} = 2.7V	_	-12	mA	
I _{OH}	High-Level Output Current	., 2,,	_	-16	IIIA	
			V _{CC} = 3V	_	-24]
		$V_{CC} = 4.5V$	_	-32		
		V _{CC} = 1.65V	_	4		
		$V_{CC} = 2.3V$	_	8]	
la.	Low-Level Output Current	$V_{CC} = 2.7V$	_	12	m A	
l _{OL}	Low-Level Output Current	V 2V	_	16	mA	
		Vcc = 3V	_	24		
		$V_{CC} = 4.5V$	_	32		
		$V_{CC} = 1.8V \pm 0.15V, 2.5V \pm 0.2V$		20		
Δt/ΔV	Input Transition Rise or Fall Rate	$V_{CC} = 3.3V \pm 0.3V$	_	10	ns/V	
	, and	$V_{CC} = 5V \pm 0.5V$	_	5		
T _A	Operating Free-Air Temperatu	re —	-40	+125	°C	

Note: 9. Unused inputs should be held at V_{CC} or Ground.



Electrical Characteristics (All typical values are at $V_{CC} = 3.3V$, $T_A = +25$ °C)

Cumbel	Doromots:	Test Conditions	V	-40	0°C to +85°	C	-40°C to	+125°C	l lmi4
Symbol	Parameter	lest Conditions	V _{CC}	Min	Тур.	Max	Min	Max	Unit
		I _{OH} = -100μA	1.65V to 5.5V	V _{CC} - 0.1	_	_	V _{CC} - 0.1		
		I _{OH} = -4mA	1.65V	1.2	_	_	0.95		
	l	I _{OH} = -8mA	2.3V	1.9	_	_	1.7		
V_{OH}	High-Level Output Voltage	$I_{OH} = -12mA$	2.7V	2.2	_	_	1.9	_	V
	Carpar Voltago	I _{OH} = -16mA	3V	2.4	_	_	2.2		
		I _{OH} = -24mA	3 V	2.3	_	_	2.0		
		I _{OH} = -32mA	4.5V	3.8	_	_	3.4	-	
		I _{OL} = 100μA	1.65V to 5.5V	_	_	0.1	_	0.1	
		I _{OL} = 4mA	1.65V	_	_	0.45	_	0.7	
	l	I _{OL} = 8mA	2.3V	_	_	0.3	_	0.45	V
V_{OL}	Low -Level Output Voltage	$I_{OL} = 12mA$	2.7V	_	_	0.4	_	0.6	
	Carpar Voltago	I _{OL} = 16mA	3V	_	_	0.4	_	0.6	
		I _{OL} = 24mA	3 V	_	_	0.55	_	0.8	
		I _{OL} = 32mA	4.5V	_	_	0.55	_	.8	
II	Input Current	V _I = 5.5V or GND	0 to 5.5V	_	± 0.1	±5	_	±100	μA
l _{OFF}	Power Down Leakage Current	V_I or $V_O = 5.5V$	0V	_	_	±10	_	±200	μΑ
Icc	Supply Current	V _I = 5.5V or GND I _O =0	5.5V	_	0.1	10	_	200	μA
ΔI _{CC}	Additional Supply Current	One input at V _{CC} –0.6V Other inputs at V _{CC} or GND	3V to 5.5V	_	_	500	_	5,000	μΑ
Ci	Input Capacitance	$V_i = V_{CC} - \text{or GND}$	3.3V	_	5	_	_	_	pF



Package Characteristics (All typical values are at $V_{CC} = 3.3V$, $T_A = 25$ °C)

Symbol	Parameter	Test Conditions	Vcc	Min	Тур.	Max	Unit
		SOT25		_	204	_	
		SOT353		_	371	_	
		SOT553		_	231	_	
	Thermal Resistance	X2-DFN0808-4	(Note 10)	_	400	_	°C/W
θ_{JA}	Junction-to-Ambient	X1-DFN1010-6 (Type B)	(Note 10)	_	435	_	C/VV
		X2-DFN1010-6		_	445	_	
		X2-DFN1409-6		_	470	_	
		X2-DFN1410-6	X2-DFN1410-6		460	_	
		SOT25		_	52	_	
		SOT353		_	143	_	
		SOT553		_	105	_	
0	Thermal Resistance	X2-DFN0808-4	(Note 10)	_	225	_	°C/W
₽JC	θ _{JC} Junction-to-Case	X1-DFN1010-6 (Type B)	(Note 10)	_	250	_	C/VV
		X2-DFN1010-6	X2-DFN1010-6		250	_	
		X2-DFN1409-6		_	275	_	
		X2-DFN1410-6		_	265	_	

Note:

Switching Characteristics

Figure 1 Typical Values at $T_A = +25^{\circ}C$ and nominal voltages 1.8V, 2.5V, 2.7V, 3.3V, and 5.0V.

Doromotor	From	То	V	T _A	= -40°C to +8	5°C	T _A = -40°C	to +125°C	l lmi4
Parameter	Input	Output	V _{cc}	Min	Тур	Max	Min	Max	Unit
			1.8V ± 0.15V	1.0	3.2	8.0	1.0	10.5	
			2.5V ± 0.2V	0.5	2.2	5.5	0.5	7.0	
t _{pd}	A or B	Y	2.7V	0.5	2.5	5.5	0.5	7.0	ns
			$3.3V \pm 0.3V$	0.5	2.1	4.5	0.5	6.0	
			5.0V ± 0.5V	0.5	1.7	4.0	0.5	5.5	

Operating Characteristics


 $T_A = +25$ °C

Parameter		Test Conditions	V _{CC} = 1.8V	V _{CC} = 2.5V	V _{CC} = 3.3V	V _{CC} = 5V	Unit
		Тур.		Тур.	Тур.	Тур.	
$C_{\sf pd}$	Power Dissipation Capacitance	f = 10 MHz	14	14	14	14	pF


^{10.} Test condition for each of the 8 package types: Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.




Parameter Measurement Information



V _{CC}	In	puts	V M	C _L	R _L
• 60	Vı	t _r /t _f	1	٥	
1.8V ± 0.15V	Vcc	≤2ns	V _{CC} /2	30pF	1kΩ
2.5V ± 0.2V	Vcc	≤2ns	V _{CC} /2	30pF	500Ω
2.7V	Vcc	≤2.5ns	1.5V	50pF	500Ω
3.3V ± 0.3V	3.0V	≤2.5ns	1.5V	50pF	500Ω
$5.0V \pm 0.5V$	Vcc	≤2.5ns	V _{CC} /2	50pF	500Ω



Voltage Waveform Pulse Duration



Voltage Waveform Propagation Delay Times Inverting and Non Inverting Outputs

Figure 1. Load Circuit and Voltage Waveforms


Notes:

- A. Includes test lead and test apparatus capacitance.
- B. All pulses are supplied at pulse repetition rate ≤ 10 MHz.
 C. Inputs are measured separately one transition per measurement.
- D. t_{PLH} and t_{PHL} are the same as t_{PD} .



Marking Information

(1) SOT25, SOT353 and SOT553



Orderable Part Number	Package	Identification Code
74LVC1G02W5-7	SOT25	UT
74LVC1G02SE-7	SOT353	UT
74LVC1G02Z-7	SOT553	UT

(2) DFN packages

(Top View)

XX $\underline{Y} \underline{W} \underline{X}$


XX : Identification Code
Y: Year 0~9
W: Week: A~Z: 1~26 week;
a~z: 27~52 week; z represents 52 and 53 week \underline{X} : A~Z: Internal Code

Orderable Part Number	Package	Identification Code
74LVC1G02FS3-7	X2-DFN0808-4	WT
74LVC1G02FW5-7	X1-DFN1010-6 (Type B)	V3
74LVC1G02FW4-7	X2-DFN1010-6	UT
74LVC1G02FX4-7	X2-DFN1409-6	MB
74LVC1G02FZ4-7	X2-DFN1410-6	UT



Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT25




SOT25			
Dim	Min	Max	Тур
Α	0.35	0.50	0.38
В	1.50	1.70	1.60
С	2.70	3.00	2.80
D	-	-	0.95
Н	2.90	3.10	3.00
J	0.013	0.10	0.05
K	1.00	1.30	1.10
L	0.35	0.55	0.40
М	0.10	0.20	0.15
N	0.70	0.80	0.75
α	0°	8°	-
All Dimensions in mm			

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.


SOT25





Dimensions	Value
Z	3.20
G	1.60
Х	0.55
Υ	0.80
C1	2.40
C2	0.95



Please see http://www.diodes.com/package-outlines.html for the latest version.









SOT353

SOT353				
Dim	Min	Max	Тур	
A1	0.00	0.10	0.05	
A2	0.90	1.00	0.95	
b	0.10	0.30	0.25	
U	0.10	0.22	0.11	
D	1.80	2.20	2.15	
Е	2.00	2.20	2.10	
E1	1.15	1.35	1.30	
е	0.650 BSC			
F	0.40	0.45	0.425	
L	0.25	0.40	0.30	
а	0°	8°		
All Dimensions in mm				

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.






Dimensions	Value	
Dillielisions	(in mm)	
С	0.650	
C1	1.900	
G	1.300	
Х	0.420	
X1	1.720	
Y	0.600	
V1	2 500	



Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT553




SOT553			
Dim	Min	Max	Тур
Α	0.55	0.62	0.60
b	0.15	0.30	0.20
U	0.10	0.18	0.15
D	1.50	1.70	1.60
Е	1.55	1.70	1.60
E1	1.10	1.25	1.20
e	0.50 BSC		
e1	1.00 BSC		
F	0.00	0.10	_
Ĺ	0.10	0.30	0.20
а	6°	8°	7°
All Dimensions in mm			

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT553




Dimensions	Value
Z	2.2
G	1.2
Х	0.375
Υ	0.5
C1	1.7
C2	0.5



Please see http://www.diodes.com/package-outlines.html for the latest version.

X2-DFN0808-4




X2-DFN0808-4			
Dim	Min	Max	Тур
Α	0.25	0.35	0.30
A1	0	0.04	0.02
A3	-	-	0.13
b	0.17	0.27	0.22
D	0.75	0.85	0.80
D2	0.15	0.35	0.25
E	0.75	0.85	0.80
E2	0.15	0.35	0.25
е	-	-	0.48
k	0.20	-	-
L	0.17	0.27	0.22
L1	0.02	0.12	0.07
z	-	-	0.05
All Dimensions in mm			

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

X2-DFN0808-4




Dimensions	Value
С	0.480
Χ	0.320
X1	0.300
X2	0.106
Х3	0.800
Υ	0.320
Y1	0.300
Y2	0.106
Y3	0.900



Please see http://www.diodes.com/package-outlines.html for the latest version.

X1-DFN1010-6 (Type B)




	X1-DFN1010-6 (Type B)				
Dim					
Α	-	0.50	0.39		
A1	-	0.04	-		
b	0.12	0.20	0.15		
D	0.95	1.050	1.00		
Е	0.95	1.050	1.00		
е	0.35 BSC				
e1	0.55 BSC				
L3	0.27	0.30	0.30		
L3a	0.32	0.40	0.35		
All Dimensions in mm					

Suggested Pad Layout

 $\label{prop:lease} Please see \ http://www.diodes.com/package-outlines.html \ for \ the \ latest \ version.$

X1-DFN1010-6 (Type B)




Dimensions	Value (in mm)	
С	0.350	
G	0.150	
G1	0.150	
Χ	0.200	
X1	0.900	
Υ	0.500	
Y1	0.525	
Y2	0.475	
Y3	1.150	



Please see http://www.diodes.com/package-outlines.html for the latest version.

X2-DFN1010-6




X2-DFN1010-6			
Dim	Min	Max	Тур
Α		0.40	0.39
A 1	0.00	0.05	0.02
А3			0.13
b	0.14	0.20	0.17
b1	0.05	0.15	0.10
D	0.95	1.05	1.00
Е	0.95	1.05	1.00
е			0.35
L	0.35	0.45	0.40
K	0.15		
Z			0.065
All Dimensions in mm			

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

X2-DFN1010-6




Dimensions	Value (in mm)
С	0.350
G	0.150
X	0.200
X1	0.900
Υ	0.550
Y1	1.250



Please see http://www.diodes.com/package-outlines.html for the latest version.

X2-DFN1409-6 CHIP SCALE ALTERNATIVE




X2-DFN1409-6					
Dim	Min	Max	Тур		
Α	-	0.40	0.39		
A1	0	0.05	0.02		
A3	1	-	0.13		
Ø	0.20	0.30	0.25		
D	1.35	1.45	1.40		
E	0.85	0.95	0.90		
e1	-	-	0.50		
e2	-	-	0.50		
Z1	-	-	0.075		
Z2	-	-	0.075		
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.


X2-DFN1409-6 CHIP SCALE ALTERNATIVE



Dimensions	Value	
Dillielisions	(in mm)	
С	1.000	
C1	0.500	
D	0.300	
G	0.200	
G1	0.200	
Х	0.400	
Y	0.150	




Please see http://www.diodes.com/package-outlines.html for the latest version.



X2-DFN1410-6				
Dim	Min	Max	Тур	
Α		0.40	0.39	
A1	0.00	0.05	0.02	
A3		_	0.13	
b	0.15	0.25	0.20	
D	1.35	1.45	1.40	
Е	0.95	1.05	1.00	
е			0.50	
L	0.25	0.35	0.30	
Z		_	0.10	
Z1	0.045	0.105	0.075	
All Dimensions in mm				

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



X2-DFN1410-6

Dimensions	Value (in mm)	
С	0.500	
G	0.250	
X	0.250	
X1	1.250	
Υ	0.525	
Y1	1.250	



IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners.

© 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com

74LVC1G02 16 of 16 September 2023
Document number: DS32197 Rev. 11 - 2 www.diodes.com © 2023 Copyright Diodes Incorporated. All Rights Reserved.