

## AP61100/AP61102

2.3V TO 5.5V INPUT, 1A LOW IQ SYNCHRONOUS BUCK CONVERTER

### Description

The DIODES<sup>TM</sup> AP61100/AP61102 is a 1A, synchronous buck converter with a wide input voltage range of 2.3V to 5.5V. The device fully integrates a 110m $\Omega$  high-side power MOSFET and an 80m $\Omega$  low-side power MOSFET to provide high-efficiency step-down DC-DC conversion.

The AP61100/AP61102 device is easily used by minimizing the external component count due to its adoption of Constant On-Time (COT) control to achieve fast transient response, easy loop stabilization, and low output voltage ripple.

The device is available in a SOT563 package.

## Features


- VIN: 2.3V to 5.5V
- Output Voltage (VOUT): 0.6V to 3.6V
- 1A Continuous Output Current
- 0.6V ± 2% Reference Voltage
- 15µA Low Quiescent Current (Pulse Frequency Modulation)
- 2.2MHz Switching Frequency (VIN = 5V, VOUT = 1.8V)
- Up to 89% Efficiency at 5mA Light Load
- Programmable Operation Mode Through EN
- Pulse Frequency Modulation
- Pulse Width Modulation Regardless of Output Load
- Power-Good Indicator
- AP61102
- Protection Circuitry
- Undervoltage Lockout (UVLO)
- VIN Overvoltage Protection (OVP)
- Peak Current Limit
- Valley Current Limit
- Thermal Shutdown
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. <u>https://www.diodes.com/quality/productdefinitions/</u>
- An Automotive-Compliant Part is Available Under Separate
   Datasheet (<u>AP61100Q/AP61102Q</u>)

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

## Pin Assignments



### Applications

- 5V distributed power bus supplies
- White goods and small home appliances
- FPGA, DSP, and ASIC supplies
- Network video cameras
- Wireless routers
- Consumer electronics
- General purpose point of loads



## **Typical Application Circuit**




Figure 1. Typical AP61100 Application Circuit




Figure 2. Typical AP61102 (AP61100 OUT as NC) Application Circuit





Figure 3. PFM Efficiency vs. Output Current







## **Pin Descriptions**

Pin Name	Pin Number	Function
FB	1	Feedback sensing terminal for the output voltage. Connect this pin to the resistive divider of the output.
ГБ	1	See Setting the Output Voltage section for more details.
GND	2	Power Ground.
		Power Input. VIN supplies the power to the IC as well as the step-down converter power MOSFETs. Drive VIN with a
VIN	3	2.3V to 5.5V power source. Bypass VIN to GND with a suitably large capacitor to eliminate noise due to the switching
		of the IC. See Input Capacitor section for more details.
SW	4	Power Switching Output. SW is the switching node that supplies power to the output. Connect the output LC filter
310	4	from SW to the output load.
		Enable Input. EN is a digital input that turns the regulator on or off. Drive EN high to turn on the regulator and low to
EN	5	turn it off. EN is used to program the Operation Mode (PFM or PWM).
		See Enable section for more details.
OUT		Output Voltage Power Rail. Connect OUT to the output load in Figure 1 and do not tie OUT to GND. OUT pin is also
(AP61100)	6	allow for no connect, then C3 must be install as in Figure 2.
PG	0	Power-Good. Open drain power-good output that is pull to GND when the output voltage is out of its regulation limits
(AP61102)		or during soft-start.



## **Functional Block Diagram**




Figure 5. Functional Block Diagram



Symbol	Parameter	Rating	Unit
VIN		-0.3 to +6.5 (DC)	V
VIIN	Supply Pin Voltage	-0.3 to +7.0 (400ms)	v
Vfb	Feedback Pin Voltage	-0.3 to VIN + 0.3	V
Mary	Vsw Switch Pin Voltage	-1.0 to VIN + 0.3 (DC)	N/
Vsw	Switch Pin Voltage	-2.5 to VIN + 2.0 (20ns)	- V
V <sub>EN</sub>	Enable Pin Voltage	-0.3 to VIN + 0.3	V
VOUT (AP61100)	Output Pin Voltage	-0.3 to +6.0 (DC)	V
V <sub>PG</sub> (AP61102)	Power-Good Pin Voltage	-0.3 to +6.0 (DC)	V
T <sub>ST</sub>	Storage Temperature	-65 to +150	°C
TJ	Junction Temperature	+160	°C
T∟	Lead Temperature	+260	°C
D Susceptibility	Note 5)		•
HBM	Human Body Model	±6000	V
CDM	Charged Device Model	±1500	V

## Absolute Maximum Ratings (Note 4) (@ TA = +25°C, unless otherwise specified.)

Notes: 4. Stresses greater than the *Absolute Maximum Ratings* specified above can cause permanent damage to the device. These are stress ratings only; functional operation of the device at these or any other conditions exceeding those indicated in this specification is not implied. Device reliability can be affected by exposure to absolute maximum rating conditions for extended periods of time.

5. Semiconductor devices are ESD sensitive and can be damaged by exposure to ESD events. Suitable ESD precautions should be taken when handling and transporting these devices.

## Thermal Resistance (Note 6)

Symbol	Parameter	Rat	ing	Unit
θја	Junction to Ambient	SOT563	141	°C/W
θJC	Junction to Case	SOT563	33	°C/W

Note: 6. Test condition for SOT563: Device mounted on FR-4 substrate, two-layer PCB, 2oz copper, with minimum recommended pad layout.

## Recommended Operating Conditions (Note 7) (@ T<sub>A</sub> = +25°C, unless otherwise specified.)

Symbol	Parameter	Min	Max	Unit
VIN	Supply Voltage	2.3	5.5	V
VOUT	Output Voltage	0.6	3.6	V
TA	Operating Ambient Temperature	-40	+85	°C
TJ	Operating Junction Temperature	-40	+125	°C

Note: 7. The device function is not guaranteed outside of the recommended operating conditions.

## AP61100/AP61102




**Electrical Characteristics** (@ T<sub>J</sub> = +25°C, VIN = 5V, unless otherwise specified. Min/Max limits apply across the recommended operating junction temperature range, -40°C to +125°C, and input voltage range, 2.3V to 5.5V, unless otherwise specified.)

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
ISHDN	Shutdown Supply Current	$V_{EN} = 0V$	_	0.1	_	μA
1-	Quiessent Supply Current	PFM, V <sub>FB</sub> = 0.65V	_	15	_	μA
la	Quiescent Supply Current	PWM, V <sub>FB</sub> = 0.65V		620	_	μA
POR	VIN Power-on Reset Rising Threshold	—	—	2.00	2.25	V
UVLO	VIN Undervoltage Lockout Falling Threshold	—	_	1.84	—	V
OVPVIN	VIN Overvoltage Rising Threshold	—	—	6.3	—	V
OVP <sub>VIN_HYS</sub>	VIN Overvoltage Hysteresis	—	—	300	—	mV
R <sub>DS(ON)1</sub>	High-Side Power MOSFET On-Resistance (Note 8)	—	_	110	_	mΩ
R <sub>DS(ON)2</sub>	Low-Side Power MOSFET On-Resistance (Note 8)	—		80	_	mΩ
IPEAK_LIMIT	HS Peak Current Limit (Note 8)	From Source to Drain	1.7	2.5	—	А
IVALLEY_LIMIT	LS Valley Current Limit (Note 8)	From Source to Drain	_	1.9	_	А
fsw	Oscillator Frequency	VOUT = 1.8V, CCM	1.7	2.2	2.7	MHz
ton_min	Minimum On-Time	—	_	70	_	ns
toff_min	Minimum Off-Time	—	_	70	_	ns
VFB	Feedback Voltage	ССМ	0.588	0.600	0.612	V
V <sub>EN_H</sub>	EN Logic High Threshold	—	—	0.91	—	V
Ven_L	EN Logic Low Threshold	—	_	0.83	_	V
tss	Soft-Start Time	—	_	0.5	_	ms
PGuv_fall	Undervoltage Falling Threshold	AP61102, Percent of Output Regulation, Fault	_	90	_	%
PG <sub>UV_RISE</sub>	Undervoltage Rising Threshold	AP61102, Percent of Output Regulation, Good	_	95	_	%
PG <sub>OV_RISE</sub>	Overvoltage Rising Threshold	AP61102, Percent of Output Regulation, Fault	_	110	_	%
PGov_fall	Overvoltage Falling Threshold	AP61102, Percent of Output Regulation, Good	_	105	_	%
t <sub>PG_RD</sub>	Power-Good Rise Delay Time	AP61102		55	—	μs
Vpg_ol	Power-Good Output Logic Low	AP61102, I <sub>PG</sub> = -1mA	_	_	0.4	V
Rpg	Power-Good Pull-Up Resistor	AP61102	_	5	—	mΩ
Tsd	Thermal Shutdown (Note 8)	—	_	+160	—	°C
T <sub>Hys</sub>	Thermal Shutdown Hysteresis (Note 8)	—	_	+30	—	°C

Note: 8. Compliance to the datasheet limits is assured by one or more methods: production test, characterization, and/or design.



## **Typical Performance Characteristics** (AP61100/AP61102 @ $T_A = +25^{\circ}C$ , VIN = 5V, VOUT = 1.8V, unless otherwise specified.)








Figure 8. ISHDN vs. Temperature




Figure 7. VFB vs. Temperature




Figure 9. VIN Power-On Reset and UVLO vs. Temperature



## **Typical Performance Characteristics** (AP61100/AP61102 @ T<sub>A</sub> = +25°C, VIN = 5V, VOUT = 1.8V, PFM, unless otherwise specified.) (continued)





Figure 10. Efficiency vs. Output Current, VIN = 3.3V








Figure 14. Io vs. Temperature




Figure 11. Efficiency vs. Output Current, VIN = 5V




Figure 13. Load Regulation




Figure 15. fsw vs. Load

## **Typical Performance Characteristics** (AP61100/AP61102 @ T<sub>A</sub> = +25°C, VIN = 5V, VOUT = 1.8V, PFM, unless otherwise specified.) (continued)




Figure 16. Output Voltage Ripple, IOUT = 50mA




Figure 18. Load Transient, IOUT = 50mA to 500mA to 50mA




Figure 20. Load Transient, IOUT = 50mA to 1A to 50mA




Figure 17. Output Voltage Ripple, IOUT = 1A




Figure 19. Load Transient, IOUT = 500mA to 1A to 500mA



## **Typical Performance Characteristics** (AP61100/AP61102 @ T<sub>A</sub> = +25°C, VIN = 5V, VOUT = 1.8V, PWM, unless otherwise specified.) (continued)






Figure 21. Efficiency vs. Output Current, VIN = 3.3V








Figure 25. Io vs. Temperature




Figure 22. Efficiency vs. Output Current, VIN = 5V




Figure 24. Load Regulation




Figure 26. fsw vs. Temperature, IOUT = 0A

# **Typical Performance Characteristics** (AP61100/AP61102 @ T<sub>A</sub> = +25°C, VIN = 5V, VOUT = 1.8V, PWM, unless otherwise specified.) (continued)




Figure 27. fsw vs. Load




Figure 29. Output Voltage Ripple, IOUT = 1A




Figure 31. Load Transient, IOUT = 500mA to 1A to 500mA




Figure 28. Output Voltage Ripple, IOUT = 50mA




Figure 30. Load Transient, IOUT = 50mA to 500mA to 50mA




Figure 32. Load Transient, IOUT = 50mA to 1A to 50mA



**Typical Performance Characteristics** (AP61100 @ T<sub>A</sub> = +25°C, VIN = 5V, VOUT = 1.8V, unless otherwise specified.) (continued)




Figure 35. Output Short Protection, IOUT = 1A

Figure 36. Output Short Recovery, IOUT = 1A



# **Typical Performance Characteristics** (AP61102 @ T<sub>A</sub> = +25°C, VIN = 5V, VOUT = 1.8V, unless otherwise specified.) (continued)




Figure 39. Output Short Protection, IOUT = 1A

Figure 40. Output Short Recovery, IOUT = 1A



## **Application Information**

#### 1 Pulse Width Modulation (PWM) Operation

The AP61100/AP61102 device is a 2.3V-to-5.5V input, 1A output, fully integrated synchronous buck converter. Refer to the block diagram in Figure 5. The device employs constant on-time control to provide fast transient response and easy loop stabilization. At the beginning of each cycle, the one-shot pulse turns on the high-side power MOSFET, Q1, for a fixed on-time, t<sub>ON</sub>. This one-shot on-pulse timing is calculated by the converter's input voltage and output voltage to maintain a pseudo-fixed frequency over the input voltage range. When Q1 is on, the inductor current rises linearly and the device charges the output capacitor. Q1 turns off after the fixed on-time expires, and the low-side power MOSFET, Q2, turns on. Once the output voltage drops below the output regulation, Q2 turns off. The one-shot timer is then reset and Q1 turns on again. The on-time is inversely proportional to the input voltage and directly proportional to the output voltage. It is calculated by the following equation:

$$t_{ON} = \frac{VOUT}{VIN \cdot f_{sw}}$$
 Eq. 1

Where:

- VIN is the input voltage
- VOUT is the output voltage
- f<sub>SW</sub> is the switching frequency

The off-time duration is t<sub>OFF</sub> and starts after the on-time expires. The off-time expires when the feedback voltage decreases below the reference voltage, which then triggers the on-time duration to start again. The minimum off-time is 70ns typical.

#### 2 Pulse Frequency Modulation (PFM) Operation

The AP61100/AP61102 can be programmed to enter PFM operation at light load conditions for high efficiency. During light load conditions, the regulator automatically reduces the switching frequency. As the output current decreases, so too does the inductor current. The inductor current,  $I_L$ , eventually reaches 0A, marking the boundary between Continuous Conduction Mode (CCM) and Discontinuous Condition Mode (DCM). During this time, both Q1 and Q2 are off, and the load current is provided only by the output capacitor. When V<sub>FB</sub> becomes lower than 0.6V, the next cycle begins, and Q1 turns on. Because the AP61100/AP61102 can work in PFM during light load conditions, it can achieve power efficiency of up to 89% at a 5mA load condition.

Likewise, as the output load increases from light load to heavy load, the switching frequency increases to maintain the regulation of the output voltage. The transition point between light and heavy load conditions can be calculated using the following equation:

$$I_{LOAD} = \left(\frac{VIN - VOUT}{2L}\right) \cdot t_{ON}$$
 Eq. 2

Where:

L is the inductor value

The quiescent current of AP61100/AP61102 is 15µA typical under a no-load, non-switching condition.

#### 3 Enable

When disabled, the device shutdown supply current is only 0.1µA. When applying a voltage greater than the EN logic high threshold (typical 0.91V, rising), the AP61100/AP61102 enables all functions and the device initiates the soft-start phase. The AP61100/AP61102 has a built-in 0.5ms soft-start time to prevent output voltage overshoot and inrush current. When the EN voltage falls below its logic low threshold (typical 0.83V, falling), the internal SS voltage discharges to ground and device operation disables.

The device operates in PFM when a logic high voltage is applied to the EN pin greater than VIN - 200mV. The device operates in PWM regardless of output load when a logic high voltage is applied to the EN pin less than VIN - 200mV.



#### 4 Power-Good (PG) Indicator (AP61102)

The PG pin of AP61102 is an open-drain output that is actively held low during the soft-start period until the output voltage reaches 95% of its target value. When the output voltage is outside of its regulation by  $\pm 10\%$ , PG pulls low until the output returns within 5% of its set value. The PG rising edge transition is delayed by 55µs. The PG pin is connected to VIN through an internal 5MΩ pull-up resistor.

#### 5 Undervoltage Lockout (UVLO) and Input Overvoltage Protection (OVP)

Undervoltage lockout is implemented to protect the IC from insufficient input voltages. The AP61100/AP61102 disables if the input voltage falls below 1.84V. In this UVLO event, both the high-side and low-side power MOSFETs turn off and the  $1k\Omega$  active discharge enables to discharge the output voltage to ground.

Similarly, input overvoltage protection is implemented to protect the IC from excess input voltages. The AP61100/AP61102 disables if the input voltage rises above 6.3V. In this OVP event, both the high-side and low-side power MOSFETs turn off and the  $1k\Omega$  active discharge enables to discharge the output voltage to ground.

#### 6 Overcurrent Protection (OCP)

The AP61100/AP61102 has cycle-by-cycle valley current limit protection by sensing the current through the internal low-side power MOSFET, Q2. While Q2 is on, the internal sensing circuitry monitors its conduction current. The overcurrent limit has a corresponding voltage limit,  $V_{LIMIT}$ . When the voltage between GND and SW is lower than  $V_{LIMIT}$  due to excessive current through Q2, the OCP triggers, and the controller turns off Q2. During this time, both Q1 and Q2 remain off. A new switching cycle begins only when the voltage between GND and SW rises above  $V_{LIMIT}$ . If Q2 consistently hits the valley current limit for 0.6ms, the buck converter enters hiccup mode and shuts down. After 3.4ms of down time, the buck converter restarts powering up. Hiccup mode reduces the power dissipation in the overcurrent condition.

The AP61100/AP61102 also has cycle-by-cycle peak current limit protection by sensing the current through the internal high-side power MOSFET, Q1, through a similar mechanism as the cycle-by-cycle valley current limit protection.

Because the R<sub>DS(ON)</sub> values of the power MOSFETs increase with temperature, V<sub>LIMIT</sub> has a temperature coefficient of 0.4%/°C to compensate for the temperature dependency of R<sub>DS(ON)</sub>.

#### 7 Thermal Shutdown (TSD)

If the junction temperature of the device reaches the thermal shutdown limit of +160°C, the AP61100/AP61102 shuts down both its high-side and low-side power MOSFETs. When the junction temperature reduces to the required level (+130°C typical), the device initiates a normal power-up cycle with soft-start.



#### 8 Power Derating Characteristics

To prevent the regulator from exceeding the maximum recommended operating junction temperature, some thermal analysis is required. The regulator's temperature rise is given by:

$$T_{RISE} = PD \cdot (\theta_{IA})$$
 Eq. 3

Where:

- PD is the power dissipated by the regulator
- $\theta_{JA}$  is the thermal resistance from the junction of the die to the ambient temperature

The junction temperature, T<sub>J</sub>, is given by:

$$T_{J} = T_{A} + T_{RISE}$$
 Eq. 4

Where:

• TA is the ambient temperature of the environment

For the SOT563 package, the  $\theta_{JA}$  is 141°C/W. The actual junction temperature should not exceed the maximum recommended operating junction temperature of +125°C when considering the thermal design. Figure 41 shows a typical derating curve versus ambient temperature.




Figure 41. Output Current Derating Curve vs. Ambient Temperature, VIN = 5V



#### 9 Setting the Output Voltage

The AP61100/AP61102 has adjustable output voltages starting from 0.6V using an external resistive divider. The resistor values of the feedback network are selected based on a design trade-off between efficiency and output voltage accuracy. There is less current consumption in the feedback network for high resistor values, which improves efficiency at light loads. However, values too high cause the device to be more susceptible to noise affecting its output voltage accuracy. R2 can be determined by the following equation:

$$R2 = \frac{0.6 \cdot R1}{VOUT - 0.6V}$$
 Eq. 5

Table 1 shows a list of recommended component selections for common AP61100/AP61102 output voltages referencing Figure 1 and Figure 2.

Table 1. Recommended Component Selections

AP61100/AP61102							
Output Voltage (V)	B4 (kO)	R2 (kΩ)		C1 (µF)	C2 (UE)	C3 (pF)	
Output voltage (v)	R1 (kΩ)	NZ (N32)	L (µH)		οι (μr)	C2 (µF)	AP61100
1.0	200.0	301.0	1.0	10	10	OPEN	33
1.2	200.0	200.0	1.0	10	10	OPEN	33
1.5	200.0	133.0	1.0	10	10	OPEN	33
1.8	200.0	100.0	1.0	10	10	OPEN	33
2.5	200.0	63.2	1.0	10	10	OPEN	33
3.3	200.0	44.2	1.0	10	10	OPEN	33

#### 10 Inductor

Calculating the inductor value is a critical factor in designing a buck converter. For most designs, the following equation can be used to calculate the inductor value:

$$\mathbf{L} = \frac{\mathbf{VOUT} \cdot (\mathbf{VIN} - \mathbf{VOUT})}{\mathbf{VIN} \cdot \Delta \mathbf{I}_{L} \cdot \mathbf{f}_{sw}}$$
Eq. 6

Where:

- $\Delta I_L$  is the inductor current ripple
- fsw is the buck converter switching frequency

For AP61100/AP61102, choose  $\Delta I_L$  to be 30% to 50% of the maximum load current of 1A.

The inductor peak current is calculated by:

$$I_{L_{PEAK}} = I_{LOAD} + \frac{\Delta I_L}{2}$$
 Eq. 7

Peak current determines the required saturation current rating, which influences the size of the inductor. Saturating the inductor decreases the converter efficiency while increasing the temperatures of the inductor and the internal power MOSFETs. Therefore, choosing an inductor with the appropriate saturation current rating is important. For most applications, it is recommended to select an inductor of approximately  $1.0\mu$ H to  $1.5\mu$ H with a DC current rating of at least 35% higher than the maximum load current. For highest efficiency, the inductor's DC resistance should be less than 50m $\Omega$ . Use a larger inductance for improved efficiency under light load conditions.



#### 11 Input Capacitor

The input capacitor reduces both the surge current drawn from the input supply as well as the switching noise from the device. The input capacitor must sustain the ripple current produced during the on-time of Q1. It must have a low ESR to minimize power dissipation due to the RMS input current.

The RMS current rating of the input capacitor is a critical parameter and must be higher than the RMS input current. As a rule of thumb, select an input capacitor with an RMS current rating greater than half of the maximum load current.

Due to large dl/dt through the input capacitor, electrolytic or ceramic capacitors with low ESR should be used. If using a tantalum capacitor, it must be surge protected or else capacitor failure could occur. Using a ceramic capacitor of 10µF or greater is sufficient for most applications.

#### 12 Output Capacitor

The output capacitor keeps the output voltage ripple small, ensures feedback loop stability, and reduces both the overshoots and undershoots of the output voltage during load transients. During the first few microseconds of an increasing load transient, the converter recognizes the change from steady-state and sets the off-time to minimum to supply more current to the load. However, the inductor limits the change to increasing current depending on its inductance. Therefore, the output capacitor supplies the difference in current to the load during this time. Likewise, during the first few microseconds of a decreasing load transient, the converter recognizes the change from steady-state and increases the off-time to reduce the current supplied to the load. However, the inductor limits the change in decreasing current as well. Therefore, the output capacitor absorbs the excess current from the inductor during this time.

The effective output capacitance, COUT, requirements can be calculated from the equations below.

The ESR of the output capacitor dominates the output voltage ripple. The amount of ripple can be calculated by:

$$VOUT_{Ripple} = \Delta I_{L} \cdot \left( ESR + \frac{1}{8 \cdot f_{sw} \cdot COUT} \right)$$
 Eq. 8

An output capacitor with large capacitance and low ESR is the best option. For most applications, a  $10\mu$ F to  $22\mu$ F ceramic capacitor is sufficient. To meet the load transient requirements, the calculated COUT should satisfy the following inequality:

$$COUT > max \left( \frac{L \cdot I_{Trans}^{2}}{\Delta V_{Overshoot} \cdot VOUT}, \frac{L \cdot I_{Trans}^{2}}{\Delta V_{Undershoot} \cdot (VIN - VOUT)} \right)$$
Eq. 9

Where:

- ITrans is the load transient
- $\Delta V_{Overshoot}$  is the maximum output overshoot voltage
- $\Delta V_{Undershoot}$  is the maximum output undershoot voltage



## Layout

#### PCB Layout

- 1. The AP61100/AP61102 works at 1A load current so heat dissipation is a major concern in the layout of the PCB. 2oz copper for both the top and bottom layers is recommended.
- 2. Place the input capacitors as closely across VIN and GND as possible.
- 3. Place the inductor as close to SW as possible.
- 4. Place the output capacitors as close to GND as possible.
- 5. Place the feedback components as close to FB as possible.
- 6. If using four or more layers, use at least the 2<sup>nd</sup> and 3<sup>rd</sup> layers as GND to maximize thermal performance.
- 7. Add as many vias as possible around both the GND pin and under the GND plane for heat dissipation to all the GND layers.
- 8. Add as many vias as possible around both the VIN pin and under the VIN plane for heat dissipation to all the VIN layers.
- 9. See Figure 42 and Figure 43 for more details.




Figure 42. Recommended AP61100 PCB Layout





Figure 43. Recommended AP61102 PCB Layout




## **Ordering Information**



Part Number	Function	Package Code	Packing		
Fait Number	Function	Fackage Coue	Quantity	Carrier	
AP61100Z6-7	—	Z6	3000	7" Tape & Reel	
AP61102Z6-7	PG	Z6	3000	7" Tape & Reel	

## **Marking Information**

SOT563




Part Number	Package	Identification Code
AP61100Z6-7	SOT563	HJ
AP61102Z6-7	SOT563	НК



## **Package Outline Dimensions**


Please see http://www.diodes.com/package-outlines.html for the latest version.



	SOT563					
Dim	Min	Max	Тур			
Α	0.55	0.60				
b	0.15	0.30	0.20			
C	0.10	0.18	0.11			
D	1.50	1.70	1.60			
Е	1.55	1.70	1.60			
E1	1.10	1.25	1.20			
е			0.50			
e1	0.90	1.10	1.00			
L	0.10	0.30	0.20			
а	8°	9°	7°			
All	Dimens	sions in	mm			

## Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



Dimensions	Value (in mm)
C	
ل د	0.500
C1	1.270
G	0.600
Х	0.300
X1	1.300
Y	0.670
Y1	1.940

## **Mechanical Data**

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208
- Weight: 0.003 grams (Approximate)

## e see http://www.diodes.com/package-o

SOT563



#### IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

Diodes' products are provided subject Diodes' Standard Terms and Conditions of 5. to Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at <a href="https://www.diodes.com/about/company/terms-and-conditions/important-notice">https://www.diodes.com/about/company/terms-and-conditions/important-notice</a>

DIODES is a trademark of Diodes Incorporated in the United States and other countries. The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. © 2022 Diodes Incorporated. All Rights Reserved.

#### www.diodes.com