



#### **High-Performance Differential Fanout Buffer**

#### **Features**

- 10 Differential Outputs with Two Banks
- User Configurable Output Signaling Standard for Each Bank:
   LVDS or LVPECL or HCSL
- LVCMOS Reference Output up to 200MHz
- Up to 1.5GHz Output Frequency for Differential Outputs
- Ultra-Low Additive Phase Jitter:
  - <0.02ps (typ) (Differential 156.25MHz, 12KHz to 20MHz Integration Range)
  - <0.01ps (typ) (Differential 156.25MHz, 10kHz to 1MHz Integration Range)
- Selectable Reference Inputs Support Either Single-Ended or Differential or Xtal
- Low Skew Between Outputs within Banks (<40ps)
- Low Delay from Input to Output (Tpd typ. <0.9ns)
- Separate Input Output Supply Voltage for Level Shifting
- 2.5V/3.3V Power Supply
- Industrial Temperature Support
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative.

https://www.diodes.com/quality/product-definitions/

- Packaging (Pb-free & Green):
  - 48-Pin, TQFN (ZD)


# **Applications**

- Networking Systems Including Switches and Routers
- High-Frequency Backplane Based Computing and Telecom Platforms

#### Description

The DIODES™ PI6C49S1510B is a high-performance fanout buffer device which supports up to 1.5GHz frequency. It also integrates a unique feature with user-configurable output signaling standards on per bank basis, which provides great flexibility to users. The device also uses Diodes' proprietary input detection technique to make sure illegal input conditions are detected and reflected by output states. This device is ideal for systems that must distribute low jitter clock signals to multiple destinations.

#### **Block Diagram**



#### Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.


DIODES is a trademark of Diodes Incorporated in the United States and other countries.

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.





# **Pin Configuration**



# **Pin Description**

Pin #	Pin Name	r	Гуре	Description
1, 2	QA0+ QA0-	Output		Bank A differential output pair 0. Pin selectable LVPECL/LVDS/HCSL interface levels.
3, 4	QA1+	C	utput	Bank A differential output pair 1. Pin selectable LVPECL/LVDS/HCSL interface levels.
5, 8, 29, 32, 45	QA1- VDDO	F	Power	Power supply pins for IO
6, 7	QA2+	- C	utput	Bank A differential output pair 2.
	QA2-			Pin selectable LVPECL/LVDS/HCSL interface levels.
9, 10	QA3+ QA3-		utput	Bank A differential output pair 3. Pin selectable LVPECL/LVDS/HCSL interface levels.
11 12	QA4+			Bank A differential output pair 4.
11, 12	QA4-		utput	Pin selectable LVPECL/LVDS/HCSL interface levels.
13, 18, 24, 37, 43, 48	GND	F	ower	Power supply ground
14, 47	OPMODEA	Input	Pulldown	Output mode select for Bank A. See Table 2 for functions, LVCMOS/LVTTL interface levels
15, 42	$V_{DD}$	Power		Power supply pins
16	X1	]	nput	XTAL input, can also be used as single ended input pin
17	X2	C	utput	XTAL output. If X1 is used as a single ended input pin, X2 is to be left open





## Pin Description Cont.

Pin #	Pin Name	r	Гуре	Description		
19, 22	IN_SEL	Input	Pulldown	Input clock select. See Table 1 for function. LVCMOS/LVTTL interface levels.		
20	IN0+	Input	Pulldown	Reference input 0, internal bias to $0.33V_{\text{DD}}$		
21	INO-	Input	Pullup/ Pulldown	Inverted reference input 0, internal bias to $0.42V_{\mathrm{DD}}$		
23, 39	OPMODEB	Input	Pulldown	Output mode select for Bank B. See Table 2 for functions, LVCMOS/LVTTL interface levels		
26. 25	QB4+			Bank B differential output pair 4.		
26, 25	QB4-		Output	Pin selectable LVPECL/LVDS/HCSL interface levels.		
20. 27	QB3+			Bank B differential output pair 3.		
28, 27	QB3-		utput	Pin selectable LVPECL/LVDS/HCSL interface levels.		
31, 30	QB2+		tm.i.t	Bank B differential output pair 2.		
31, 30	QB2-		utput	Pin selectable LVPECL/LVDS/HCSL interface levels.		
34, 33	QB1+		utput	Bank B differential output pair 1.		
34, 33	QB1-			Pin selectable LVPECL/LVDS/HCSL interface levels.		
36, 35	QB0+		Output	Bank B differential output pair 0.		
30, 33	QB0-			Pin selectable LVPECL/LVDS/HCSL interface levels.		
38	NC		_	Do not connect		
40	IN1-	Input	Pullup/ Pulldown	Inverted reference input, internal bias to $0.42 V_{\text{DD}}$		
41	IN1+	Input	Pulldown	Reference input 1, internal bias to $0.33V_{\text{DD}}$		
44	Ref_Out	С	utput	Reference output, CMOS		
46	Sync_OE	Input	Pulldown	Synchronous output enable for Ref_Out. See Table 3 for functions.		





#### **Function Table**

#### **Table 1: Input Select Function**

IN_SEL [1] IN_SEL [0]		Function
0	0	IN0 is the selected reference input
0	1	IN1 is the selected reference input
1	X	XTAL is the selected input

#### **Table 2: Output Mode Select Function**

OPMODEA/B [1]	OPMODEA/B [0]	Output Bank A/Bank B Mode
0	0	LVPECL
0	1	LVDS
1	0	HCSL
1	1	Hi-Z

#### **Table 3: Reference Output Enable Function**

Sync_OE	Ref_Out
0	Hi-Z
1	Output Enabled

#### **Table 4: Illegal Input Level Function**

Input Illegal Status	Output Status
Input Open	Logic Low
Input Both High	Logic Low
Input Both Low	Logic Low





## **Maximum Ratings**

(Above which the useful life may be impaired. For user guidelines, not tested.)

Storage Temperature55°C to +150°C
Supply Voltage to Ground Potential (V $_{\rm DD}, V_{\rm DDO})$ -0.5V to +4.6V
Inputs (Referenced to GND)0.5V to $V_{\mbox{\scriptsize DD}} + 0.5 V$
Clock Output (Referenced to GND)0.5V to $V_{\mbox{\tiny DD}} + 0.5 V$
Latch up200mA
ESD Protection (Input)2000V min (HBM)
Junction Temperature 150°C max

#### Note:

Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

#### **Power Supply Characteristics and Operating Conditions**

Symbol	Parameter	Test Condition	Min.	Тур.	Max.	Units
$V_{DD}$	Core Supply Voltage	_	2.375	_	3.465	V
$V_{ m DDO}$	Output Supply Voltage	_	2.375	_	3.465	V
$I_{DD}$	Core Power Supply Current	_	_	90	120	
$I_{ m DDO}$	Output Power Supply Current	All LVPECL outputs unloaded	_	150	190	mA
		All LVDS outputs loaded	_	110	130	] 11121
		All HCSL outputs unloaded	_	80	140	
$T_A$	Ambient Operating Temperature <sup>(1)</sup>	_	-40	_	85	°C
T <sub>B</sub>	PCB Operating Temperature <sup>(1)</sup>	_	-40	_	105	°C

Note 1: Either  $T_A$  or  $T_B$  used as operating condition.

#### **DC Electrical Specifications - Differential Inputs**

Symbol	Parameter	<b>Test Condition</b>	Min.	Тур.	Max.	Units
$I_{IH}$	Input High Current	$Input = V_{DD}$	_	_	150	μΑ
$I_{\rm IL}$	Input Low Current	Input = GND	-150	_	_	μΑ
C <sub>IN</sub>	Input Capacitance	_	_	3	_	pF
$V_{IH}$	Input High Voltage	_	_	_	V <sub>DD</sub> +0.3	V
$V_{IL}$	Input Low Voltage	_	-0.3	_	_	V
$V_{\text{ID}}$	Input Differential Amplitude PK-PK	_	0.15	_	1.3	V
$V_{CM}$	Common Model Input Voltage	_	0.25	_	V <sub>DD</sub> -1.2	V
ISO <sub>MUX</sub>	MUX Isolation	_	_	-89	_	dBc





**DC Electrical Specifications - LVCMOS Inputs** 

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
$I_{IH}$	Input High Current	Input = V <sub>DD</sub>	_	_	150	μΑ
I <sub>IL</sub>	Input Low Current	Input = GND	-150	_	_	μΑ
$V_{IH}$	Input High Voltage	$V_{DD}$ =3.3 $V$	2.0	_	V <sub>DD</sub> +0.3	V
$V_{IL}$	Input Low Voltage	$V_{DD}=3.3V$	-0.3	_	0.8	V
$V_{IH}$	Input High Voltage	$V_{DD}=2.5V$	1.7	_	V <sub>DD</sub> +0.3	V
$V_{IL}$	Input Low Voltage	V <sub>DD</sub> =2.5V	-0.3	_	0.7	V

**DC Electrical Specifications - LVPECL Outputs** 

Parameter	Description	Conditions	Min.	Тур.	Max.	Units
V <sub>OH</sub>	Output High Voltage	_	V <sub>DDO</sub> -1.4	_	V <sub>DDO</sub> -0.9	V
V <sub>OL</sub>	Output Low Voltage	_	V <sub>DDO</sub> -2.2	_	V <sub>DDO</sub> -1.7	V

## **DC Electrical Specifications - LVDS Outputs**

Parameter	Description	Conditions	Min.	Тур.	Max.	Units
$V_{OH}$	Output High Voltage	_	_	1.43	_	V
$V_{OL}$	Output Low Voltage	_	_	1.0	_	V
Vocm	Output Commode Voltage	_	_	1.25	_	V
DVocm	Change in Vocm Between Completely Output States	_	_	_	50	mV
Ro	Output Impedance	_	85	_	140	W

# **DC Electrical Specifications – HCSL Outputs**

Parameter	Description	Conditions	Min.	Тур.	Max.	Units
V <sub>OH</sub> Output H	Ontrod III als Walts as	2.5V	480	_	900	mV
	Output High Voltage	3.3V	600	850	1050	mV
V <sub>OL</sub>	Output Low Voltage	_	-150	_	150	mV





# **DC Electrical Specifications – LVCMOS Outputs**

Parameter	Description	Conditions	Min.	Тур.	Max.	Units
7.7	Output High Voltage	$V_{\rm DDO}$ =3.3V ±5%, $I_{\rm OH=}$ 8mA	2.3	_	_	V
$V_{OH}$		$V_{\rm DDO}$ =2.5V ±5%, $I_{\rm OH=}8mA$	1.5	_	_	V
37	Output Low Voltage	$V_{\rm DDO}$ =3.3V ±5%, $I_{\rm OL}$ = -8mA	_	_	0.5	V
$V_{OL}$		$V_{\rm DDO}$ =2.5V ±5%, $I_{\rm OL=}$ -8mA	_	_	0.4	V
3.7		$V_{\rm DDO}$ =3.3V ±5%, $I_{\rm OH=}$ 24mA	2.1	_	_	V
$V_{OH}$	Output High Voltage	$V_{\rm DDO}$ =2.5V ±5%, $I_{\rm OH=}$ 16mA	1.5	_	_	V
3.7	0 ( 1 1 1 1	$V_{\rm DDO}$ =3.3V ±5%, $I_{\rm OL=}$ -24mA	_	_	1	V
$V_{OL}$	Output Low Voltage	$V_{\rm DDO}$ =2.5V ±5%, $I_{\rm OL=}$ -16mA	_	_	0.8	V
R <sub>IUT</sub>	Output Impedance	$V_{\rm DDO} = 3.3 V \pm 5\%$	_	17	_	Ω
		$V_{\rm DDO} = 2.5 V \pm 5\%$	_	22	_	Ω

# **AC Electrical Specifications – Differential Outputs**

Parameter	Description	Conditions		Min.	Тур.	Max.	Units
Е	Clark Outrat Farmers	LVPECL, LVDS	_	_	_	1500	MHz
F <sub>OUT</sub>	Clock Output Frequency	HCSL	_	_	_	250	MITZ
			LVPECL	120	150	300	
T <sub>r</sub>	Output Rise Time	From 20% to 80%	LVDS	120	150	300	ps
			HCSL	300	_	700	
			LVPECL	120	150	300	
$T_{\rm f}$	Output Fall Time	From 80% to 20%	LVDS	120	150	300	ps
			HCSL	300	_	700	
	Output Duty Cycle	Frequency <650MHz, $V_{ID} \ge 400 \text{mV}$	LVPECL, HCSL (<250MHz)	48	_	52	
			LVDS	47	_	53	
_		Frequency <1GHz,	LVPECL	45	_	55	
$T_{ODC}$		$V_{\rm ID} \geq 400 mV$	LVDS	45	_	55	%
		Frequency <1.5GHz, $V_{ID} \ge 400 \text{mV}$	LVDS	40	_	60	
		Frequency <1.5GHz, $V_{ID} \ge 400 \text{mV}$	LVPECL	40	_	60	
V.		LVPECL Outputs @ <1GHz		500	_	1100	
	Output Swing Single-Ended	LVPECL Outputs @ >1GHz		400	_	1000	mV
$V_{pp}$		LVDS Outputs @ <1GHz		250	_	600	
		LVDS Outputs @ >1Gl	Hz	250	_	550	





## AC Electrical Specifications - Differential Outputs Cont.

Parameter	Description	Conditions	Min.	Тур.	Max.	Units
T	D	156.25MHz, 12kHz to 20MHz	_	0.02	_	ps
$T_{j}$	Buffer Additive Jitter RMS	156.25MHz, 10kHz to 1MHz	_	0.01	_	ps
V <sub>CROSS</sub>	Absolute Crossing Voltage	HCSL	_	460	_	mV
DV <sub>CROSS</sub>	Total Variation of Crossing Voltage	HCSL	_	_	140	mV
$T_{sK}$	Output Skew	10 outputs devices, outputs in same bank with same load at DUT	_	15	40	ps
T	Propagation Delay	LVPECL, LVDS @ 3.3V, 100MHz	_	570	_	ps
T <sub>PD</sub>		HCSL @ 3.3V, 100MHz	_	900	_	ps
T <sub>OD</sub>	Valid to HiZ		_	_	80	ns
T <sub>OE</sub>	HiZ to valid		_	_	80	ns
T <sub>P2P Skew</sub>	Part-to-Part Skew <sup>(1)</sup>		_	80	120	ps

# **AC Electrical Specifications – CMOS**

Parameter	Description	Conditions	Min.	Тур.	Max.	Units
T.	D. C. C. I	XTAL input	10	_	50	MHz
F <sub>OUT</sub>	Ref_Out Frequency	Reference input	_	_	200	MHz
T <sub>j</sub>	D., C., A 11:4: I:44 DMC	XTAL input	_	0.3	_	ps
	Buffer Additive Jitter RMS	Reference input	_	0.03	_	ps
$t_{\rm r}/t_{\rm f}$	Rise Time, Fall Time	$C_L = 10pF$	_	1.5	_	ns
$T_{\text{ODC}}$	Output Duty Cycle	$C_L = 10pF$	45	_	55	%
$t_{PD}$	Propagation Delay	3.3V, 25MHz	_	2200	_	ps
$t_S$	Setup Time	_	300	_	_	ps
$t_{SOD}$	Clock Edge to Output Disable	Ref_Out	2	_	4	cycles
t <sub>SOE</sub>	Clock Edge to Output Enable	Ref_Out	2	_	4	cycles

Notes:

<sup>1.</sup> This parameter is guaranteed by design.





## **Crystal Characteristics**

Parameter	Min.	Тур.	Max.	Units
Mode of Oscillation		Fundamental		
Frequency Range	10	_	50	MHz
Equivalent Series Resistance (ESR)	_	_	70	Ω
Shunt Capacitance	_	_	7	pF
Load Capacitance	10	_	18	pF
Drive Level	_	_	500	μW

9

# **Recommended Crystals**


Diodes recommends:

- a) GC2500003 XTAL 49S/SMD(4.0 mm), 25M, CL=18pF, ±30ppm
- b) FY2500091, SMD 5x3.2(4P), 25M, CL=18pF, ±30ppm
- c) FL2500047, SMD 3.2x2.5(4P), 25M, CL=18pF, ±20ppm







## Propagation Delay (TPD)



## Output Skew (Tsk)




#### Part-to-Part Skew









## LVPECL/LVDS Output Swing vs Frequency







# **Propagation Delay vs Temperature**




#### 1.5GHz LVPECL/LVDS Waveform




2.5V LVPECL Waveform



2.5V LVDS Waveform



3.3V LVPECL Waveform



3.3V LVDS Waveform







#### **Phase Noise and Additive Jitter**

Output Phase Noise (Dark Blue) vs Input Phase Noise (Light Blue)


Additive jitter is calculated at 156.25MHz ~ 27fs RMS (12kHz to 20MHz). Additive jitter =  $\sqrt{\text{Output jitter}^2 - \text{Input jitter}^2}$ .



#### Total Phase Jitter with 25MHz XTAL ~ 264fs RMS (12kHz ~ 20MHz)




#### Configuration Test Load Board Termination for LVPECL/LVDS Outputs








## **Configuration Test Load Board Termination for HCSL Outputs**



# **Configuration Test Load Board Termination for LVCMOS Outputs**







## **Application Information**

#### Wiring the Differential Input to Accept Single-Ended Levels

Figure 1 shows how the differential input can be wired to accept single-ended levels. The reference voltage  $V_REF = V_{DD}/2$  is generated by the bias resistors R1, R2, and C1. This bias circuit should be located as close as possible to the input pin. The ratio of R1 and R2 might require to be adjusted to position the  $V_REF$  in the center of the input voltage swing. For example, if the input clock swing is only 2.5V,  $V_{DD} = 3.3V$ ,  $V_REF$  should be 1.25V and R2/R1 = 0.609.





Figure 1. Single-Ended Input to Differential Input Device

#### **Power Supply Filtering Techniques**


As in any high-speed analog circuitry, the power supply pins are vulnerable to random noise. To achieve optimum jitter performance, power supply isolation is required. All power pins should be individually connected to the power supply plane through vias, and  $0.1\mu F$  and  $1\mu F$  bypass capacitors should be used for each pin.









#### Single-Ended Input, AC Couple




#### **Single-Ended Input, AC Couple**




## **Single-Ended Input, DC Couple**



# **Single-Ended Input, DC Couple**




#### **Driving X1 with a Single-Ended Input**









#### LVPECL, AC Couple, Thevenin Equivalent




# LVPECL, DC Couple, Thevenin Equivalent




## **LVDS DC Couple**




# LVDS AC Couple at Load



#### **LVDS AC Couple with Internal Termination**




# Single-Ended LVPECL, DC Couple









# Single-Ended LVPECL, DC Couple, Thevenin Equivalent




# Single-Ended LVPECL, AC Couple, Thevenin Equivalent



#### **Clock IC Crystal Input Guide**




#### LVPECL/LVDS AC and DC Input







#### Clock IC Crystal Loading Cap. Design Guide



CL =crystal spec. loading cap.

 $C_{in}/out = (3pF \sim 5pF)$  of IC pin cap.

 $Cb = PCB \text{ trace } (2pF \sim 4pF)$ 

C1,C2 = load cap. of design

 $Rd = 50\Omega$  to  $100\Omega$  drive level limit

Design guide:  $C1 = C2 = 2 \times CL - (Cb + C_in/out)$  to meet target  $\pm ppm < 20ppm$ 

Example 1: Select CL = 18pF crystal,  $C1 = C2 = 2 \times (18pF) - (4pF + 5pF) = 27pF$ . Check datasheet.

Example 2: For higher frequency crystal (= >20MHz), the following formula can be used: C1 = C2 = 2 × (CL - 6). A fine tune of C1, C2 can be used for more accurate ppm if necessary.

#### **Thermal Information**

Symbol	Description	Condition	_
$\Theta_{ m JA}$	Junction-to-Ambient Thermal Resistance	Still air	23.65°C/W
$\Theta_{ m JC}$	Junction-to-Case Thermal Resistance	_	9.1°C/W

# **Part Marking**

PI6C49S **1510BZDIE**  $YYWWX\overline{X}$ 

YY: Year

18

WW: Workweek


1st X : Assembly Site Code 2nd X: Wafer Site Code





#### **Packaging Mechanical**

#### 48-TQFN (ZD)



# For latest package information:

 $See \ http://www.diodes.com/design/support/packaging/pericom-packaging/packaging-mechanicals-and-thermal-characteristics/.$ 

## **Ordering Information**

Ordering Code	Package Code	Package Type	<b>Operating Temperature</b>
PI6C49S1510BZDIEX	ZD	48-Contact, Very Thin Quad Flat No-Lead (TQFN)	-40°C to 85°C

#### Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. I = Industrial
- 5. E = Pb-free and Green
- 6. X suffix = Tape/Reel





#### **IMPORTANT NOTICE**

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2022 Diodes Incorporated

www.diodes.com

PI6C49S1510B

Document Number DS41795 Rev 4-2