



4.2V TO 18V INPUT, 3A LOW IQ SYNCHRONOUS BUCK CONVERTER

Description

The AP62300/AP62301/AP62300T is a 3A, synchronous buck converter with a wide input voltage range of 4.2V to 18V. The device fully integrates a $75m\Omega$ high-side power MOSFET and a $45m\Omega$ low-side power MOSFET to provide high-efficiency step-down DC-DC conversion.

The AP62300/AP62301/AP62300T device is easily used by minimizing the external component count due to its adoption of Constant On-Time (COT) control to achieve fast transient response, easy loop stabilization, and low output-voltage ripple.


The AP62300/AP62301/AP62300T design is optimized for Electromagnetic Interference (EMI) reduction. The device has a proprietary gate driver scheme to resist switching node ringing without sacrificing MOSFET turn-on and turn-off times, which reduces high-frequency radiated EMI noise caused by MOSFET switching.

The AP62300/AP62301 is available in SOT563 (Standard) and TSOT26 (Standard) packages. The AP62300T is available in a TSOT26 (Standard) package.

Features

- VIN: 4.2V to 18V
- Output Voltage (VOUT): 0.8V to 7V
- 3A Continuous Output Current
- 0.8V ± 1% Reference Voltage (T_A = +25°C)
 - AP62300 and AP62301
- 0.763V ± 1% Reference Voltage (T_A = +25°C)
 - AP62300T
- 155µA Low Quiescent Current (Pulse Frequency Modulation)
- 750kHz Switching Frequency (VIN = 12V, VOUT = 5V)
- Up to 83% Efficiency at 5mA Light Load
- Proprietary Gate Driver Design for Best EMI Reduction
- Protection Circuitry
 - Undervoltage Lockout (UVLO)
 - Cycle-by-Cycle Valley Current Limit
 - Output Undervoltage Protection
 - Thermal Shutdown
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

Pin Assignments



Applications

- 5V and 12V distributed power bus supplies
- Flat screen TV sets and monitors
- White goods and small home appliances
- FPGA, DSP, and ASIC supplies
- Home audios
- Network systems
- Gaming consoles
- Consumer electronics
- General purpose point of loads

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



Typical Application Circuit




Figure 1. Typical Application Circuit




Figure 2. Efficiency vs. Output Current, AP62300/AP62300T




Figure 3. Efficiency vs. Output Current, AP62301



Pin Descriptions

Pin	Pin Nu	ımber	
Name	SOT563	TSOT26	Function
Name	(Standard)	(Standard)	
			Power Input. VIN supplies the power to the IC as well as the step-down converter power MOSFETs. Drive VIN
VIN	1	3	with a 4.2V to 18V power source. Bypass VIN to GND with a suitably large capacitor to eliminate noise due to
			the switching of the IC. See Input Capacitor section for more details.
SW	2	2	Power Switching Output. SW is the switching node that supplies power to the output. Connect the output LC filter
Svv	2	2	from SW to the output load.
GND	3	1	Power Ground.
BST	4	6	High-Side Gate Drive Boost Input. BST supplies the drive for the high-side N-Channel MOSFET. A 100nF
БЭТ	4	O	capacitor or higher is recommended from BST to SW to power the high-side driver.
			Enable Input. EN is a digital input that turns the regulator on or off. Drive EN high to turn on the regulator and
EN	5	5	low to turn it off. Leave floating for automatic startup. The EN has a precision threshold of 1.2V for programing
			the UVLO. See Enable section for more details.
FB	6	4	Feedback sensing terminal for the output voltage. Connect this pin to the resistive divider of the output. See
ГБ	0	4	Setting the Output Voltage section for more details.

Functional Block Diagram




Figure 4. Functional Block Diagram



Absolute Maximum Ratings (Note 4) (@ TA = +25°C, unless otherwise specified.)

Symbol	Parameter	Rating	Unit
VIN	Supply Pin Voltage	-0.3 to +20.0 (DC)	V
VIIN	Supply Fill Vollage	-0.3 to +22.0 (400ms)	7 v
V _{SW}	Switch Pin Voltage	-1.0 to VIN + 0.3 (DC)	V
VSW	Switch Fill Voltage	-2.5 to VIN + 2.0 (20ns)	"
V _{BST}	Bootstrap Pin Voltage	V _{SW} - 0.3 to V _{SW} + 6.0	V
V _{EN}	Enable/UVLO Pin Voltage	-0.3 to +8.0	V
V _{FB}	Feedback Pin Voltage	-0.3 to +6.0	V
Tst	Storage Temperature	-65 to +150	°C
TJ	Junction Temperature	+160	°C
T _L	Lead Temperature	+260	°C
ESD Susceptibility	(Note 5)		•
HBM	Human Body Model	±2000	V
CDM	Charged Device Model	±500	V

Notes:

Thermal Resistance (Note 6)

Symbol	Parameter	Rat	ing	Unit
Δ.,	Junction to Ambient	SOT563 (Standard)	110	°C/W
θμα		TSOT26 (Standard)	70	
θјс	Junction to Case	SOT563 (Standard)	8	°C/W
		TSOT26 (Standard)	12	C/VV

Note:

Recommended Operating Conditions (Note 7) (@ TA = +25°C, unless otherwise specified.)

Symbol	Parameter	Min	Max	Unit
VIN	Supply Voltage	4.2	18.0	V
VOUT	Output Voltage	0.8	7.0	V
TA	Operating Ambient Temperature	-40	+85	°C
TJ	Operating Junction Temperature	-40	+125	°C

Note:

7. The device function is not guaranteed outside of the recommended operating conditions.

^{4.} Stresses greater than the *Absolute Maximum Ratings* specified above can cause permanent damage to the device. These are stress ratings only; functional operation of the device at these or any other conditions exceeding those indicated in this specification is not implied. Device reliability can be affected by exposure to absolute maximum rating conditions for extended periods of time.

^{5.} Semiconductor devices are ESD sensitive and can be damaged by exposure to ESD events. Suitable ESD precautions should be taken when handling and transporting these devices.

^{6.} Test condition for SOT563 (Standard)/TSOT26 (Standard): Device mounted on FR-4 substrate, two-layer PCB, 2oz copper, with minimum recommended pad layout.




Electrical Characteristics (@ $T_J = +25^{\circ}C$, VIN = 12V, unless otherwise specified. Min/Max limits apply across the recommended operating junction temperature range, -40°C to +125°C, and input voltage range, 4.2V to 18V, unless otherwise specified.)

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Ishdn	Shutdown Supply Current	VEN = 0V	_	1.5	_	μΑ
IQ	Quiescent Supply Current	AP62300/AP62300T: V _{FB} = 0.85V	_	155	_	μΑ
		AP62301: V _{FB} = 0.85V	_	275	_	μΑ
POR	VIN Power-On Reset Rising Threshold	_	_	3.90	4.15	V
UVLO	VIN Undervoltage Lockout Falling Threshold	_	_	3.6	_	V
RDS(ON)1	High-Side Power MOSFET On-Resistance (Note 8)	<u> </u>	_	75	_	mΩ
RDS(ON)2	Low-Side Power MOSFET On-Resistance (Note 8)	_	_	45	_	mΩ
IVALLEY_LIMIT	LS Valley Current Limit (Note 8)	From Source to Drain	3.2	3.7	4.2	Α
f _{SW}	Oscillator Frequency	VOUT = 5V, CCM	_	750	_	kHz
t _{ON_MIN}	Minimum On-Time	_	_	90	_	ns
toff_min	Minimum Off-Time	_	_	220	_	ns
		AP62300/AP62301: T _A = +25°C, CCM	0.792	0.800	0.808	V
\/	Feedback Voltage	AP62300/AP62301: CCM	0.784	0.800	0.816	V
V _{FB}	reedback voltage	AP62300T: T _A = +25°C, CCM	0.755	0.763	0.770	V
		AP62300T: CCM	0.747	0.763	0.778	V
V _{EN_H}	EN Logic High Threshold	_	_	1.20	1.25	V
V _{EN_L}	EN Logic Low Threshold	_	1.04	1.10	_	V
len	EN Input Current	V _{EN} = 1.5V	_	7.0	_	μΑ
IEN	EN Input Current	VEN = 1V	1.0	1.5	2.0	μA
tss	Soft-Start Time	_	_	2.5	_	ms
T _{SD}	Thermal Shutdown (Note 8)	_	_	+160	_	°C
T _{Hys}	Thermal Shutdown Hysteresis (Note 8)	_		+20	_	°C

Note: 8. Compliance to the datasheet limits is assured by one or more methods: production test, characterization, and/or design.



Typical Performance Characteristics (AP62300/AP62301/AP62300T @ T_A = +25°C, VIN = 12V, VOUT = 5V, BOM = Table 1, unless otherwise specified.)







Figure 5. Power MOSFET RDS(ON) vs. Temperature

Figure 6. Feedback Voltage vs. Temperature, AP62300/AP62301






Figure 7. Feedback Voltage vs. Temperature, AP62300T

Figure 8. I_{SHDN} vs. Temperature





Figure 9. VIN Power-On Reset and UVLO vs. Temperature



Vsw (10V/div)

Typical Performance Characteristics (AP62300/AP62301/AP62300T @ T_A = +25°C, VIN = 12V, VOUT = 5V, BOM = Table 1, unless otherwise specified.) (continued)



I_L (5A/div)


Vsw (10V/div)

Figure 12. Output Short Protection, IOUT = 3A

Figure 13. Output Short Recovery, IOUT = 3A




Typical Performance Characteristics (AP62300/AP62300T @ T_A = +25°C, VIN = 12V, VOUT = 5V, BOM = Table 1, unless otherwise specified.)



IOUT = 0A IOUT = 1A IOUT = 2A IOUT = 3A 5.50 5.25 5.00 4.75 4.75 4.50 4.25 4.00 3.75 4.00 3.75 3.50 3.25 3.00 4 6 8 10 12 14 16 18 20 VIN (V)

Figure 14. Efficiency vs. Output Current, VIN = 12V









Figure 16. Load Regulation

Figure 17. I_Q vs. Temperature






Figure 18. fsw vs. Load

Figure 19. Output Voltage Ripple, VOUT = 5V, IOUT = 50mA




Typical Performance Characteristics (AP62300/AP62300T @ TA = +25°C, VIN = 12V, VOUT = 5V, BOM = Table 1, unless otherwise specified.) (continued)



Figure 25. Load Transient, IOUT = 50mA to 3A to 50mA



Typical Performance Characteristics (AP62301 @ T_A = +25°C, VIN = 12V, VOUT = 5V, BOM = Table 1, unless otherwise specified.)







Figure 26. Efficiency vs. Output Current, VIN = 12V









Figure 28. Load Regulation

Figure 29. IQ vs. Temperature







Figure 30. fsw vs. Temperature, IOUT = 0A

Figure 31. fsw vs. Load



Vsw (10V/div)

Typical Performance Characteristics (AP62301 @ T_A = +25°C, VIN = 12V, VOUT = 5V, BOM = Table 1, unless otherwise specified.) (continued)



Vsw (10V/div)

2μs/div
Figure 34. Output Voltage Ripple, VOUT = 3.3V, IOUT = 50mA

Figure 35. Output Voltage Ripple, VOUT = 3.3V, IOUT = 3A



Typical Performance Characteristics (AP62301 @ T_A = +25°C, VIN = 12V, VOUT = 5V, BOM = Table 1, unless otherwise specified.) (continued)




Figure 36. Load Transient, IOUT = 50mA to 500mA to 50mA

Figure 37. Load Transient, IOUT = 2A to 3A to 2A




Figure 38. Load Transient, IOUT = 50mA to 3A to 50mA



Application Information

1 Pulse Width Modulation (PWM) Operation

The AP62300/AP62301/AP62300T device is a 4.2V-to-18V input, 3A output, EMI friendly, fully integrated synchronous buck converter. Refer to the block diagram in Figure 4. The device employs constant on-time control to provide fast transient response and easy loop stabilization. At the beginning of each cycle, the one-shot pulse turns on the high-side power MOSFET, Q1, for a fixed on-time, ton. This one-shot on-pulse timing is calculated by the converter's input voltage and output voltage to maintain a pseudo-fixed frequency over the input voltage range. When Q1 is on, the inductor current rises linearly and the device charges the output capacitor. Q1 turns off after the fixed on-time expires, and the low-side power MOSFET, Q2, turns on. Once the output voltage drops below the output regulation, Q2 turns off. The one-shot timer is then reset and Q1 turns on again. The on-time is inversely proportional to the input voltage and directly proportional to the output voltage. It is calculated by the following equation:

$$\mathbf{t_{ON}} = \frac{\mathbf{VOUT}}{\mathbf{VIN} \cdot \mathbf{f_{SW}}}$$
 Eq. 1

Where:

- VIN is the input voltage
- VOUT is the output voltage
- fsw is the switching frequency

The off-time duration is t_{OFF} and starts after the on-time expires. The off-time expires when the feedback voltage decreases below the reference voltage, which then triggers the on-time duration to start again. The minimum off-time is 220ns typical.

In order to provide a small output ripple during light load conditions, the AP62301 operates in PWM regardless of output load.

2 Pulse Frequency Modulation (PFM) Operation

The AP62300/AP62300T enters PFM operation at light load conditions for high efficiency. During light load conditions, the regulator automatically reduces the switching frequency. As the output current decreases, so too does the inductor current. The inductor current, I_L, eventually reaches 0A, marking the boundary between Continuous Conduction Mode (CCM) and Discontinuous Condition Mode (DCM). During this time, both Q1 and Q2 are off, and the load current is provided only by the output capacitor. When V_{FB} becomes lower than 0.8V for AP62300 or 0.763V for AP62300T, the next cycle begins, and Q1 turns on. Because the AP62300/AP62300T works in PFM during light load conditions, it can achieve power efficiency of up to 83% at a 5mA load condition.

Likewise, as the output load increases from light load to heavy load, the switching frequency increases to maintain the regulation of the output voltage. The transition point between light and heavy load conditions can be calculated using the following equation:

$$I_{LOAD} = \left(\frac{VIN - VOUT}{2L}\right) \cdot t_{ON} \tag{Eq. 2}$$

Where:

• L is the inductor value

The quiescent current of AP62300/AP62300T is 155µA typical under a no-load, non-switching condition.

3 Enable

When disabled, the device shutdown supply current is only 1.5µA. When applying a voltage greater than the EN logic high threshold (typical 1.2V, rising), the AP62300/AP62301/AP62300T enables all functions and the device initiates the soft-start phase. An internal 1.5µA pull-up current source connected from the internal LDO-regulated VCC to the EN pin guarantees that if EN is left floating, the device still automatically enables once the voltage reaches the EN logic high threshold. The AP62300/AP62301/AP62300T has a built-in 2.5ms soft-start time to prevent output voltage overshoot and inrush current. When the EN voltage falls below its logic low threshold (typical 1.1V, falling), the internal SS voltage discharges to ground and device operation disables.

The EN pin can also be used to program the undervoltage lockout thresholds. See Undervoltage Lockout (UVLO) section for more details.



3 Enable (continued)

Alternatively, a small ceramic capacitor can be added from EN to GND. When EN is not driven externally, this capacitor increases the time needed for the EN pin voltage to reach its logic high threshold, which delays the startup of the output voltage. This is useful when sequencing multiple power rails to minimize input inrush current. When the EN pin voltage starts from 0V, the amount of capacitance for a given delay time is approximated by:

$$C_d[nF] \approx 0.278 \cdot t_d[ms]$$
 Eq. 3

Where:

- C_d is the time delay capacitance in nF
- t_d is the delay time in ms

4 Electromagnetic Interference (EMI) Reduction with Ringing-Free Switching Node

In some applications, the system must meet EMI standards. In relation to high frequency radiation EMI noise, the switching node's (SW's) ringing amplitude is especially critical. To dampen high frequency radiated EMI noise, the AP62300/AP62301/AP62300T device implements a proprietary, multi-level gate driver scheme that achieves a ringing-free switching node without sacrificing the switching node's rise and fall slew rates as well as the converter's power efficiency.

5 Adjusting Undervoltage Lockout (UVLO)

Undervoltage lockout is implemented to prevent the IC from insufficient input voltages. The AP62300/AP62301/AP62300T device has a UVLO comparator that monitors the input voltage and the internal bandgap reference. The AP62300/AP62301/AP62300T disables if the input voltage falls below 3.6V. In this UVLO event, both the high-side and low-side power MOSFETs turn off.

Some applications may desire higher VIN UVLO threshold voltages than is provided by the default setup. A 5.5µA hysteresis pull-up current source on the EN pin along with an external resistive divider (R3 and R4) configures the VIN UVLO threshold voltages as shown in Figure 39.




Figure 39. Programming UVLO

The resistive divider resistor values are calculated by:

$$R3 = \frac{0.917 \cdot V_{ON} - V_{OFF}}{5.625 \mu A}$$
 Eq. 4

$$R4 = \frac{1.1 \cdot R3}{V_{OFF} - 1.1V + 7\mu A \cdot R3} \label{eq:R4}$$
 Eq. 5

Where:

- V_{ON} is the rising edge VIN voltage to enable the regulator and is greater than 4.15V
- Voff is the falling edge VIN voltage to disable the regulator and is greater than 3.85V



6 Overcurrent Protection (OCP)

The AP62300/AP62301/AP62300T has cycle-by-cycle valley current limit protection by sensing the current through the internal low-side power MOSFET, Q2. While Q2 is on, the internal sensing circuitry monitors its conduction current. The overcurrent limit has a corresponding voltage limit, V_{LIMIT}. When the voltage between GND and SW is lower than V_{LIMIT} due to excessive current through Q2, the OCP triggers, and the controller turns off Q2. During this time, both Q1 and Q2 remain off. A new switching cycle begins only when the voltage between GND and SW rises above V_{LIMIT}. If Q2 consistently hits the valley current limit for 2.5ms or the VFB is less than 495mV (UVP threshold), the buck converter enters hiccup mode and shuts down. After 20ms of down time, the buck converter restarts powering up. Hiccup mode reduces the power dissipation in the overcurrent condition.

Because the R_{DS(ON)} values of the power MOSFETs increase with temperature, V_{LIMIT} has a temperature coefficient of 0.4%/°C to compensate for the temperature dependency of R_{DS(ON)}.

7 Thermal Shutdown (TSD)

If the junction temperature of the device reaches the thermal shutdown limit of +160°C, the AP62300/AP62301/AP62300T shuts down both its high-side and low-side power MOSFETs. When the junction temperature reduces to the required level (+140°C typical), the device initiates a normal power-up cycle with soft-start.

8 Power Derating Characteristics

To prevent the regulator from exceeding the maximum recommended operating junction temperature, some thermal analysis is required. The regulator's temperature rise is given by:

$$T_{RISE} = PD \cdot (\theta_{IA})$$
 Eq. 6

Where:

- PD is the power dissipated by the regulator
- θ_{JA} is the thermal resistance from the junction of the die to the ambient temperature

The junction temperature, T_J , is given by:

$$T_{J} = T_{A} + T_{RISE}$$
 Eq. 7

Where:

T_A is the ambient temperature of the environment



8 Power Derating Characteristics (continued)

For the SOT563 (Standard) and TSOT26 (Standard) packages, the θ_{JA} is 110°C/W and 70°C/W, respectively. The actual junction temperature should not exceed the maximum recommended operating junction temperature of +125°C when considering the thermal design. Figure 40 and Figure 41 show typical derating curves versus ambient temperature.




Figure 40. Output Current Derating Curve vs. Ambient Temperature, SOT563 (Standard) Package, VIN = 12V




Figure 41. Output Current Derating Curve vs. Ambient Temperature, TSOT26 (Standard) Package, VIN = 12V



9 Setting the Output Voltage

The AP62300/AP62301/AP62300T has adjustable output voltages, starting from 0.8V for AP62300/AP62301 and 0.763V for AP62300T, using an external resistive divider. The resistor values of the feedback network are selected based on a design trade-off between efficiency and output voltage accuracy. There is less current consumption in the feedback network for high resistor values, which improves efficiency at light loads. However, values too high cause the device to be more susceptible to noise affecting its output voltage accuracy. R1 can be determined by the following equation:

$$ext{R1} = ext{R2} \cdot \left(rac{ ext{VOUT}}{ ext{V}_{ ext{FB}}} - 1
ight)$$
 Eq. 8

Where:

V_{FB} is the feedback voltage

Table 1 shows a list of recommended component selections for common AP62300/AP62301/AP62300T output voltages referencing Figure 1. Consult Diodes Incorporated for other output voltage requirements.

	Table 1. Recommended Component Celections							
	AP62300/AP62301/AP62300T							
Output Voltage (V)	AP62300/AP62301 R1 (kΩ)	AP62300T R1 (kΩ)	R2 (kΩ)	L (µH)	C1 (µF)	C2 (µF)	C5 (pF) (Optional)	C6 (nF)
1.2	4.99	5.76	10	1.5	10	2 x 22	Open	100
1.5	8.66	9.76	10	1.5	10	2 x 22	Open	100
1.8	12.4	13.7	10	2.2	10	2 x 22	10 - 100	100
2.5	21.5	22.6	10	2.2	10	2 x 22	10 - 100	100 - 220
3.3	31.6	33.2	10	3.3	10	2 x 22	10 - 100	100 - 330
5.0	52.3	56.2	10	3.3	10	2 x 22	10 - 100	100 - 330

Table 1. Recommended Component Selections

10 Inductor

Calculating the inductor value is a critical factor in designing a buck converter. For most designs, the following equation can be used to calculate the inductor value:

$$L = \frac{VOUT \cdot (VIN - VOUT)}{VIN \cdot \Delta I_L \cdot f_{SW}} \label{eq:loss}$$
 Eq. 9

Where:

- ΔI_L is the inductor current ripple
- fsw is the buck converter switching frequency

For AP62300/AP62301/AP62300T, choose ΔI_L to be 30% to 50% of the maximum load current of 3A.

The inductor peak current is calculated by:

$$I_{L_{PEAK}} = I_{LOAD} + rac{\Delta I_L}{2}$$
 Eq. 10

Peak current determines the required saturation current rating, which influences the size of the inductor. Saturating the inductor decreases the converter efficiency while increasing the temperatures of the inductor and the internal power MOSFETs. Therefore, choosing an inductor with the appropriate saturation current rating is important. For most applications, it is recommended to select an inductor of approximately $1.2\mu H$ to $4.7\mu H$ with a DC current rating of at least 35% higher than the maximum load current. For highest efficiency, the inductor's DC resistance should be less than $30m\Omega$. Use a larger inductance for improved efficiency under light load conditions.



11 Input Capacitor

The input capacitor reduces both the surge current drawn from the input supply as well as the switching noise from the device. The input capacitor must sustain the ripple current produced during the on-time of Q1. It must have a low ESR to minimize power dissipation due to the RMS input current.

The RMS current rating of the input capacitor is a critical parameter and must be higher than the RMS input current. As a rule of thumb, select an input capacitor with an RMS current rating greater than half of the maximum load current.

Due to large dl/dt through the input capacitor, electrolytic or ceramic capacitors with low ESR should be used. If using a tantalum capacitor, it must be surge protected or else capacitor failure could occur. Using a ceramic capacitor of 10µF or greater is sufficient for most applications.

12 Output Capacitor

The output capacitor keeps the output voltage ripple small, ensures feedback loop stability, and reduces both the overshoots and undershoots of the output voltage during load transients. During the first few microseconds of an increasing load transient, the converter recognizes the change from steady-state and sets the off-time to minimum to supply more current to the load. However, the inductor limits the change to increasing current depending on its inductance. Therefore, the output capacitor supplies the difference in current to the load during this time. Likewise, during the first few microseconds of a decreasing load transient, the converter recognizes the change from steady-state and increases the off-time to reduce the current supplied to the load. However, the inductor limits the change in decreasing current as well. Therefore, the output capacitor absorbs the excess current from the inductor during this time.

The effective output capacitance, COUT, requirements can be calculated from the equations below.

The ESR of the output capacitor dominates the output voltage ripple. The amount of ripple can be calculated by:

$$VOUT_{Ripple} = \Delta I_{L} \cdot \left(ESR + \frac{1}{8 \cdot f_{SW} \cdot COUT}\right)$$
 Eq. 11

An output capacitor with large capacitance and low ESR is the best option. For most applications, a 22µF to 68µF ceramic capacitor is sufficient. To meet the load transient requirements, the calculated COUT should satisfy the following inequality:

$$COUT > max \left(\frac{L \cdot I_{Trans}^2}{\Delta V_{Overshoot} \cdot VOUT}, \frac{L \cdot I_{Trans}^2}{\Delta V_{Undershoot} \cdot (VIN - VOUT)} \right)$$
 Eq. 12

Where:

- ITrans is the load transient
- ΔV_{Overshoot} is the maximum output overshoot voltage
- ΔV_{Undershoot} is the maximum output undershoot voltage

13 Bootstrap Capacitor


To ensure proper operation, a ceramic capacitor must be connected between the BST and SW pins to supply the drive voltage for the high-side power MOSFET. A 100nF ceramic capacitor is sufficient for most applications. In the cases where output voltage is higher than 2.5V, a higher capacitance recommended to help maintain stable voltage from BST to SW.



Layout

PCB Layout

- The AP62300/AP62301/AP62300T works at 3A load current so heat dissipation is a major concern in the layout of the PCB. 2oz copper for both the top and bottom layers is recommended.
- Place the input capacitors as closely across VIN and GND as possible.
- 3. Place the inductor as close to SW as possible.
- Place the output capacitors as close to GND as possible. 4.
- 5. Place the feedback components as close to FB as possible.
- If using four or more layers, use at least the 2nd and 3rd layers as GND to maximize thermal performance. 6.
- Add as many vias as possible around both the GND pin and under the GND plane for heat dissipation to all the GND layers. 7.
- Add as many vias as possible around both the VIN pin and under the VIN plane for heat dissipation to all the VIN layers. 8.
- See Figure 42 and Figure 43 for more details.







Figure 42. Recommended PCB Layout, SOT563 (Standard)

Figure 43. Recommended PCB Layout, TSOT26 (Standard)



Ordering Information



0T : AP62300T

Part Number	Operation Mode V _{FB} (V)	Backaga Coda	Tape and Reel		
Part Number		VFB (V)	Package Code	Quantity	Part Number Suffix
AP62300Z6-7	PFM/PWM	0.800	Z6	3000	-7
AP62300WU-7	PFM/PWM	0.800	WU	3000	-7
AP62301Z6-7	PWM Only	0.800	Z6	3000	-7
AP62301WU-7	PWM Only	0.800	WU	3000	-7
AP62300TWU-7	PFM/PWM	0.763	WU	3000	-7

Marking Information

SOT563 (Standard)/TSOT26 (Standard)



6 5 4 <u>XX Y W X</u>
•
1 2 3

XX : Identification Code

 $\overline{\underline{Y}}$: Year 0~9

 $\overline{\underline{W}}$: Week: A~Z: 1~26 week;

a~z: 27~52 week; z represents

52 and 53 week \underline{X} : Internal Code


Part Number	Package	Identification Code
AP62300Z6-7	SOT563 (Standard)	HE
AP62300WU-7	TSOT26 (Standard)	HF
AP62301Z6-7	SOT563 (Standard)	HX
AP62301WU-7	TSOT26 (Standard)	HY
AP62300TWU-7	TSOT26 (Standard)	TP



Package Outline Dimensions


Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT563 (Standard)





SOT563 (Standard)				
Dim	Min	Max	Тур	
Α	0.53	0.60	_	
b	0.15	0.30	0.20	
С	0.10	0.18	0.11	
D	1.50	1.70	1.60	
Е	1.50	1.70	1.60	
E1	1.10	1.30	1.20	
е	0.50 BSC			
L	0.10	0.30	0.20	
All Dimensions in mm				

TSOT26 (Standard)



TS	TSOT26 (Standard)				
Dim	Min	Max	Тур		
Α	_	1.00			
A1	0.00	0.10			
A2	0.75	0.90	0.80		
D	2.70	3.10	2.90		
Е	2.60	3.00	2.80		
E1	1.50	1.70	1.60		
b	0.30	0.50	0.44		
С	0.11	0.20	0.16		
е	().95 BS()		
L	0.30	0.50	0.40		
L2	0.25 BSC				
θ	0°	8°	4°		
All	Dimens	ions in	mm		






OPTION A (SIDE VIEW) OPTION B (SIDE VIEW)



Suggested Pad Layout


Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT563 (Standard)



Dimensions	Value (in mm)
С	0.500
C1	1.270
G	0.600
Х	0.300
X1	1.300
Y	0.670
Y1	1.940

TSOT26 (Standard)



Dimensions	Value (in mm)
С	0.950
Х	0.700
Υ	1.000
Y1	3 200

Mechanical Data

SOT563 (Standard)

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208@3
- Weight: 0.003 grams (Approximate)

TSOT26 (Standard)

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.013 grams (Approximate)



IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners.

© 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com